




thermOweld®

thermOcap® PC

thermOcap® PC



thermOweld's  thermOcap® PC covers are designed to cover your cathodic protection wire connections on metal pipe and tanks.

- Thick outer shell designed to resist puncture.
- Folds in plastic allow the cap to conform easier to the pipe.
- Butyl rubber filled dome for added corrosion protection for the weld area.
- Superior resistance to aging shown through accelerated aging testing.
- Adheres to Ductile Iron, Steel, Stainless Steel, Copper, Aluminum, PVC, PP, PE, FBE powder coating, natural and synthetic rubbers, and Epoxy.
- Outstanding shelf life, resistant to dry rot and cracking.
- Packaged in boxes of 20 with immediate delivery available.
- Works with exothermic and brazed connections.
-  thermOcap® PC cover is designed to adhere without spray primer. *"Simply peel and stick!"*

99-5048-03 08-2018

 BURNDY®

The Contractors Choice

www.thermOweld.com



thermOcap® PC Specifications

PROPERTIES		CI THERMOCAP PC
Part Number		38-6687-02
Dimensions	Overall	4" x 4" (102 mm x 102 mm)
	Dome	1.75" Dia. 0.75" tall (44.5 mm Dia. 19 mm tall)
	Elastomeric Adhesive	0.125" thick (3.2 mm thick)
	Plastic Backing	0.021" thick (0.5 mm thick)
Primer Required		NO
Application Temperature		35 °F to 150 °F (2 °C to 66 °C)
Service Temperature		-20 °F to 180 °F (-29 °C to 82 °C)
*Adhesion to Steel		15 lb/in (26 N/cm)

*Determined per ASTM D1000/IEC 6045-2, testing method with minor deviations.

Information contained in this document is for reference only. Customers are responsible for determination of this product's suitability for their application. No liability for any loss related to the use or misuse of the material contained herein is accepted.