

*No matter what your need,
Hubbell will always be inREACH™!*

Hubbell's redesigned inREACH™ Industrial and Industrial Weatherproof Cord Reels enhance user safety and maximize efficiency by managing cord and power in a safe and organized manner, while also meeting the demands of tough industrial environments.

inREACH™ Industrial and Industrial Weatherproof Cord Reels are listed to UL 355 and CSA, C22.2 No. 308 with a durable, lightweight low profile cast aluminum construction. inREACH™ reels also feature an improved mounting plate that allows customers to upgrade existing installations or use Hubbell's innovative mounting bracket for a quick, easy installation on any surface.

FEATURES

inREACH™ Industrial & Industrial Weatherproof Cord Reels

- Durable, corrosion resistant cast aluminum construction
- Yellow or white powder coat finish
- Movable guide arm can be mounted in two positions
- Positive latch mechanism automatically maintains desired cord length
- Ratchet lock can be disengaged in field for constant tension applications
- 16-10AWG, 3 & 4 conductor cord for greater current carrying capacity
- 10AWG fully rated at 30 amps
- Available in 25ft, 35ft and 45ft lengths

inREACH™ Industrial Cord Reels

- UL Type 1
- 250V AC, SJO Type Cable
- Plug-in 5ft long power cord requires no electrical wiring

inREACH™ Industrial Weatherproof Cord Reels

- UL Type 4
- 600V AC, SOW Type Cable
- 3/4 NPT conduit hub



inREACH™ MOUNTING BRACKET

Labor Savings are inREACH™!

The inREACH™ mounting bracket allows you to decrease or eliminate the additional labor associated with installing reels at the end of the job. By starting the installation during the earlier stages of the project when there are fewer time constraints, the inREACH™ mounting bracket reduces trim-out to a fraction of the time.



Step 1
Secure the inREACH™ mounting bracket during the rough-in process.



Step 2
Remove two of the hex bolts from the bracket. Slide the reel into the mounting bracket.



Step 3
Replace two hex bolts and secure screws to complete the job.



inREACH™ Industrial Weatherproof Cord Reels

Description	Amps	Voltage	Cable Length ft. (m)	Cable Type	Weight lbs. (kg)	Catalog Number
Yellow Weatherproof Industrial Reel	10 A	600V AC	45 (13.7)	16/3 SOW	23.6 (10.7)	HBLW45163
				16/4 SOW	25.6 (11.6)	HBLW45164
Yellow Weatherproof Industrial Reel	15 A	600V AC	45 (13.7)	14/3 SOW	28.2 (12.8)	HBLW45143
				14/4 SOW	30.0 (13.6)	HBLW45144
Yellow Weatherproof Industrial Reel	20 A	600V AC	45 (13.7)	12/3 SOW	31.3 (14.2)	HBLW45123
				12/4 SOW	32.2 (14.6)	HBLW40124
Yellow Weatherproof Industrial Reel	30 A	600V AC	40 (12.2)	10/3 SOW	33.3 (15.1)	HBLW40103
				10/4 SOW	34.2 (15.5)	HBLW35104

Note: For shorter cable lengths, modify length indication in catalog number (i.e. HBLWXX); 35ft & 25ft lengths are available.
For white reel, add 'W' suffix to catalog number



inREACH™ Industrial Cord Reels

Description	Amps	Voltage	Cable Length ft (m)	Cable Type	Weight lbs. (kg)	Catalog Number	
White Industrial Reel without end effectors	10A	250V AC	45 (13.7)	16/3 SJO	22.9 (10.4)	HBLI45163	
				16/4 SJO	23.6 (10.7)	HBLI45164	
	15A	250V AC	45 (13.7)	14/3 SJO	24.0 (10.9)	HBLI45143	
				14/4 SJO	25.4 (11.5)	HBLI45144	
	20A	250V AC	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123	
				12/4 SJO	29.8 (13.5)	HBLI45124	
	30A	250V AC	45 (13.7)	10/3 SJO	32.4 (14.7)	HBLI45103	
				10/4 SJO	33.7 (15.3)	HBLI40104	
White Industrial Reel	with HBL5269C	15A	125V AC	45 (13.7)	14/3 SJO	24.0 (10.9)	HBLI45143C15
	with HBL5369C with HBL2313	20A	125V AC	45 (13.7)	12/3 SJO	26.5 (12.0) 26.5 (12.0)	HBLI45123C20 HBLI45123TL20
White Industrial Reel with Yellow Portable Outlet Box	(1) 15A Duplex Receptacle (2) 15A Duplex Receptacles	15A	125V AC	45 (13.7)	14/3 SJO	24.0 (10.9) 24.0 (10.9)	HBLI45143R15 HBLI45143R215
	GFCI Module and (1) 15A Duplex Receptacle GFCI Module and (2) 15A Duplex Receptacles	15A	125V AC	45 (13.7)	14/3 SJO	24.0 (10.9) 24.0 (10.9)	HBLI45143GF15 HBLI45143GF215
White Industrial Reel with Black Portable Outlet Box	(1) 15A Duplex Receptacle (2) 15A Duplex Receptacles	15A	125V AC	45 (13.7)	14/3 SJO	24.0 (10.9) 24.0 (10.9)	HBLI45143R15M1 HBLI45143R215M1
	GFCI Module and (2) 15A Duplex Receptacles	15A	125V AC	45 (13.7)	14/3 SJO	24.0 (10.9)	HBLI45143GF215M1
White Industrial Reel with Yellow Portable Outlet Box	(1) 20A Duplex Receptacle (2) 20A Duplex Receptacles	20A	125V AC	45 (13.7)	12/3 SJO	26.5 (12.0) 26.5 (12.0)	HBLI45123R20 HBLI45123R220
	GFCI Module and (1) 20A Duplex Receptacle GFCI Module and (2) 20A Duplex Receptacles	20A	125V AC	45 (13.7)	12/3 SJO	26.5 (12.0) 26.5 (12.0)	HBLI45123GF20 HBLI45123GF220
White Industrial Reel with Black Portable Outlet Box	(1) 20A Duplex Receptacle (2) 20A Duplex Receptacles	20A	125V AC	45 (13.7)	12/3 SJO	26.5 (12.0) 26.5 (12.0)	HBLI45123R20M1 HBLI45123R220M1
	GFCI Module and (2) 20A Duplex Receptacles	20A	125V AC	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123GF220M1

Note: 15A reels are supplied with HBL5266C on the power supply cord. 20A reels are supplied with HBL5366C on the power supply cord.
For shorter cable lengths, modify length indication in catalog number (i.e. HBLIXX); 35ft & 25ft lengths are available.
For yellow reel, add 'Y' suffix to catalog number.



inREACH™ Industrial Lighted Cord Reels

Description	Cable ft (m)	Cable Type	Watts (Max)	Amps	Voltage	Weight lbs. (kg)	Catalog Number	
White Industrial Reel	with LED hand lamp, with end light	45 (13.7)	16/3 SJO	8+1	0.07A	120V AC	22.9 (10.4)	HBLI45163LED
	with fluorescent hand lamp	45 (13.7)	16/3 SJO	13	0.3A	120V AC	22.9 (10.4)	HBLI45163FL
	with incandescent hand lamp	45 (13.7)	16/3 SJO	100	0.8A	125V AC	22.9 (10.4)	HBLI45163IN

Note: 15A reels are supplied with HBL5266C on the power supply cord. | For shorter cable lengths, modify length indication in catalog number (i.e. HBLIXX); 35ft & 25ft lengths are available. | For yellow reel, add 'Y' suffix to catalog number.



inREACH™ Mounting Accessories

Description	Weight lbs. (kg)	Catalog Number
Mounting bracket 340° pivot base	2.5 (1.1)	HBLIMB
	3.5 (1.6)	HBLI340PB

inREACH™ Replacement Parts

Description	Weight lbs. (kg)	Cable Type	Catalog Number
Replacement stop	0.2 (.09)	16AWG	HBLI16BS
		14AWG	HBLI14BS
		12AWG	HBLI12BS
		10AWG	HBLI10BS

