

EU Declaration of Conformity

We hereby declare that the products listed below comply with the requirements of the ATEX Directive 2014/34/EU and have been type approved by an EU Notified Body as listed.

The products included on this Declaration of Conformity have been designed and manufactured in compliance with the international harmonised standards listed below:

We can declare that all products (where applicable) have been assessed against the following harmonised standards. No significant technical changes have occurred which affect any of the products listed, and we therefore declare conformance to the following harmonised standards where they apply to the products.

Hawke International
Oxford Street West
Ashton-under-Lyne
Lancashire OL7 0NA UK
T: +44 (0)161 830 6695
F: +44 (0)161 830 6698
E: sales@ehawke.com
www.ehawke.com

Hawke International is a
UK Trading Division of Hubbell Ltd

Registered Office:
Cannon Place
78 Cannon Street
London EC4N 6AF UK
Registered No: 669157

VAT Registration: GB 129910853

EN 60079-0:2018	Explosive atmospheres. Equipment. General Requirements.
EN 60079-1:2014	Explosive atmospheres. Equipment protection by flameproof enclosures "d"
EN 60079-7:2015+A1:2018	Explosive atmospheres. Equipment protection by increased safety "e"
EN 60079-11:2012	Explosive atmospheres. Equipment protection by intrinsic safety "i"
EN 60079-15:2019	Explosive atmospheres. Equipment protection by type of protection "n"
EN 60079-31:2014	explosive atmospheres. Equipment dust ignition protection by enclosure "t"

Signed for and on behalf of: Hawke International
Date of Issue: 12th Nov 2020
Name: Andrew Reid
Position: Technical Manager
Signature:



Harsh & Hazardous

Cable Glands			
Product Type	Applicable Standards	Notified Body	ATEX Certificate(s)
501/414	EN 60079-0:2018 EN 60079-1:2014 EN 60079-7:2015 EN 60079-31:2014	CML B.V. Amsterdam, 1101 BA, NLD; 2776	CML 19ATEX1167X
501/421			
501/423			
501/453/RAC			
501/453/RAC/L			
PSG/421			
PSG/553/RAC			
SB474			
CSB/656/N			
501/453/UNIV			
710	EN 60079-0:2018 EN 60079-1:2014 EN 60079-7:2015 EN IEC 60079-15:2019 EN 60079-31:2014	CML B.V. Amsterdam, 1101 BA, NLD; 2776	CML 18ATEX1268X CML 19ATEX4507X
711			
753			
ICG/653/UNIV			
ICG/653/UNIV/L			
321	EN 60079-0:2018 EN 60079-7:2015 EN 60079-31:2014	CML B.V. Amsterdam, 1101 BA, NLD; 2776	CML 19ATEX3164X
321/R			
653/UNIV	EN 60079-0:2018 EN 60079-1:2014 EN 60079-7:2015	CML B.V. Amsterdam, 1101 BA, NLD; 2776	CML 19ATEX1169X CML 19ATEX1165X CML 19ATEX1166X
453/RAC			
453/UNIV			
501/321	EN 60079-0:2018 EN 60079-7:2015 EN 60079-31:2014	CESI S.p.A., I-20134 Milano, Italy, 0722	CESI 19ATEX038X
501/455/USG			
501/453 Oversize	EN 60079-0:2012+A11:2013 EN 60079-1:2014 EN 60079-7:2015 EN 60079-31:2014	SGS Fimko, FI-00211, Helsinki, Finland; 0598	Baseefa 06ATEX0056X
CSB/656			
CSB/656			Baseefa 06ATEX0058X

Connectors			
Product Type	Applicable Standards	Notified Body	ATEX Certificate(s)
ControlEx	EN 60079-0:2018 EN 60079-1:2014 EN 60079-31:2014	SGS Fimko, FI-00211, Helsinki, Finland; 0598	Baseefa 12ATEX0014X
PowerEx			Baseefa 06ATEX0062X
InstrumEx	EN 60079-0:2012+A11:2013 EN 60079-1:2014 EN 60079-7:2015 EN 60079-31:2014		Baseefa 06ATEX0061X
FibreEx	EN 60079-0:2012+A11:2013 EN 60079-1:2014 EN 60079-7:2015 EN 60079-28:2007 EN 60079-31:2014		Baseefa 16ATEX0030X



Harsh & Hazardous

Fittings			
Product Type	Applicable Standards	Notified Body	ATEX Certificate(s)
375	EN 60079-0:2012+A11:2013 EN 60079-7:2015 EN 60079-31:2014		Baseefa 12ATEX0095X
383			Baseefa 11ATEX0152X
387			Baseefa 06ATEX0118U
390			Baseefa 11ATEX0157X
389	EN 60079-0:2018 EN 60079-7:2015 EN 60079-31:2014		Baseefa 11ATEX0153X
470			Baseefa 08ATEX0333U
483			
484			
481			
482			
475	EN 60079-0:2018 EN 60079-1:2014 EN 60079-31:2014		Baseefa 10ATEX0262X
477			
476	EN 60079-0:2012+A11:2013 EN 60079-1:2014		Baseefa 11ATEX0067 Baseefa 12ATEX0207X
478			
479	EN 60079-0:2012+A11:2013 EN 60079-1:2014 EN 60079-7:2015 EN 60079-31:2014		Baseefa 11ATEX0150U Baseefa 11ATEX0149X Baseefa 11ATEX0014U Baseefa 11ATEX0154X
480			
487 & 487/RFID			
494			
495			
496			
489	EN 60079-0:2012+A11:2013 EN 60079-1:2014 EN 60079-31:2014	SIRA CSA?	Sira 11ATEX1347U
490	EN 60079-0:2012+A11:2013 EN 60079-1:2014 EN 60079-7:2015 EN 60079-31:2014		
491			
492			
493			

Enclosures			
Product Type	Applicable Standards	Notified Body	ATEX Certificate(s)
PL5 & ZPL5 Series	EN 60079-0:2018 EN 60079-7:2015 EN 60079-31:2014	SGS Fimko, FI-00211, Helsinki, Finland; 0598	Baseefa 14ATEX0248U Baseefa 14ATEX0268X
PL6 & ZPL6 Series	EN 60079-0:2018 EN 60079-7:2015 EN 60079-11: 2012 EN 60079-31:2014		Baseefa 06ATEX0116U Baseefa 06ATEX0117X
PL7 & ZPL7 Series			Baseefa 06ATEX0271U Baseefa 06ATEX0272X
S, SM, ZS and ZSM Series			Baseefa 06ATEX0207U Baseefa 08ATEX0208X
EJB, EJB, ZEJB & ZEJBM Series			Baseefa 14ATEX0300X
EA or ZEA Series			
HOF PL Series			
HOF S Series			EN 60079-0: 2012 EN 60079-7:2007 EN 60079-28: 2007

Terminals			
Product Type	Applicable Standards	Notified Body	ATEX Certificate(s)
ES10 & IES10	EN 60079-0:2012+A11:2013 EN 60079-7:2015 EN 60079-31:2014	SGS Fimko, FI-00211, Helsinki, Finland; 0598	Baseefa 09ATEX0039U
HTB Range	EN 60079-0:2012+A11:2013 EN 60079-7:2015		Baseefa 08ATEX0266
PET5	EN 60079-0:2012+A11:2013 EN 60079-7:2015		Baseefa 09ATEX0035U



Harsh & Hazardous