



The **Cirrus** LED highbay is perfectly suited for the food processing industry due to its robust construction and well-sealed IP66 rating.

There are a variety of non-glass lenses that can be utilised, depending on the application and desired appearance, which will provide an equivalent performance to traditional high-power metal halide luminaires.

## Mounting Options

- Pendant
- Medium Bay
- Low Bay

International Approvals

CE

## Standard Specification

### Cirrus LED Highbay

Enclosure	White painted cast aluminium body with flat Acrylic P95 lens
Entry	Threaded conduit through rear of luminaire
Termination	At rear of luminaire using lever nuts
Installation	Pendant mounted, 3/4" NPS
Control Gear	Electronic Driver
Colour Temperature (CCT)	5000K (Cool White)
Maintenance	Optic chamber at front, Driver chamber at rear
Ingress Protection	IP66
Surge Protection	3kV
Electrical Supply	120-277V AC 50/60Hz

Chalmit®

**LED  
SOLUTIONS**

For Harsh & Hazardous Locations



## Features

- ◆ **Instant on** crisp white light output
- ◆ Highly **Energy Efficient**
- ◆ **120,000** maintenance free hours at 25°C
- ◆ **Lower power consumption** than HID lamps
- ◆ **Low temperature applications to -40°C**


Product design and specifications are subject to change without notice. Please check the Chalmit website for latest specifications. [www.chalmit.com](http://www.chalmit.com)

Std. Cat No.	Delivered Output	Power Consumption	Ambient °C	Weight
<b>CIRI/25L/LE</b>	24628 lm	220W	-40 to +40	17.3kg

Options - Suffix to Catalogue No.

<b>/SPC*</b>	Sag polycarbonate lens	<b>/DLR*</b>	Prismatic drop acrylic lens
<b>/CDL*</b>	Prismatic conical drop acrylic lens	<b>/4K</b>	4000K (Neutral White) LED strips

\*Lenses are ordered in place of the flat Acrylic P95 lens



**LED SOLUTIONS**  
 For Harsh & Hazardous Locations



Chalmit PO BOX 5575 Glasgow G52 9AP  
 Tel: +44(0) 141 882 5555 Fax: +44(0) 141 883 3704 Email: [info@chalmit.com](mailto:info@chalmit.com)  
[www.chalmit.com](http://www.chalmit.com)