

Hubbell® BANANA BOX™ are designed to provide the fastest and easiest installation in the industry, with the greatest amount of versatility. Each box incorporates many labor-saving features. A genuine Hubbell® BANANA BOX™ is molded from a high heat and impact resistant resin, and is distinguished by its bright yellow color, providing high visibility when installing and wiring in low light levels.

The **New Ceiling BANANA BOX™** is launched under the **2028 series**, and features a larger cubic capacity of 28.1 Cu. In. (460.5 mL). The metal ground strap runs from one fixture screw to the other for a safer installation and provides convenient access to both ground screws. The new 2028 series stays true to the BANANA BOX™ ease of installation.



Certified to support 23 kg (50 lb.)

Flush Metal Ground strap provides easy access to ground screws



Flat Tabs provide a flush installation for LED lights.



Nail / Screw Guides



2 Ground Screws and 2 Device Screws included




Installs in double drywall (2028R):

- a) Breakable tabs
- b) Depth markings at 1"



Exclusive Design Features

- Two and Three Gang Device Boxes - The New **2022** and **2023 series** feature partition slots for optional low voltage barrier, **center marks** for quick height positioning, **nail / screw guides** as well as inside and **external mounting holes** for faster and more flexible installation.
- Stove/Dryer/Junction Boxes - The New **2026 series** offer $\frac{1}{2}$ " and $\frac{3}{4}$ " **knockouts**, **NMD self clamp tabs**, large cubic capacity of **58.5 In.** (958 mL) and **inside mounting holes** which provide flexible installation options. The Flanged version has additional external mounting holes.



Features and Benefits

Energy efficient vapour barrier flange models

- Provide superior energy savings
- Reduce air leakage through exterior walls
- Eliminate need for separate vapour / air barriers



Auto depth positioning

- All non-flanged boxes have breakable tabs, perfect for double drywall installation.
- Engraving at 1/2", 5/8" and 1" ensures box placement in accurate and consistent depths, while reducing the installation time
- The flanged boxes have a preset flange at 1/2" for fast positioning

Superior cubic capacity

- Additional volume makes termination easier
- Excellent for deeper body devices




Oversized nailing / screw bracket

- Better reach to mount on stud or joint
- High hammer impact resistant when nailing

Ergonomic

- Lightweight
- Bright yellow color helps to locate wires in low light levels



Cat No.	Description	Volume Cu. In. (mL)	Flange Dimension W x H (In.)	NMD90 Self Clamp Tabs	Knock-out	CSA Cable Range NMD-90	UL Cable Range NM-B	Std Pack	
1 Gang, 2-13/16" D x 2-1/4" W x 3-47/64" H									
2001R	Standard	18 (295)	-	4	-	14/2, 14/3, 12/3, 12/2 or 10/2		50	
2011FBAR	Flanged with Vapour Barrier		3-39/64 x 5-5/64						
2 Gang, 2-3/4" D x 4" W x 3-29/32" H									
2022R	Standard	35.2 (576.8)	-	8	-	14/2, 14/3, 12/3, 12/2 or 10/2	10/2	50	
2022FBAR	Flanged with Vapour Barrier		5-11/32 x 5-17/64						
3 Gang, 2-3/4" D x 4" W x 3-29/32" H									
2023R	Standard	52.6 (862)	-	12	-	14/2, 14/3, 12/3, 12/2 or 10/2	10/2	25	
2023FBAR	Flanged with Vapour Barrier		7-1/4 x 5-17/64						
Stove/Dryer/Junction Box, 3" D x 4-19/32" W x 4-19/32" H									
2026R	Standard	58.5 (958.6)	-	2	3/4"(1), 1/2"(1)	10/3 or 8/3		20	
2026FBAR	Flanged with Vapour Barrier		6-3/32 x 6-3/32						
Ceiling Box, 2-5/8" D x 4" W x 4" H									
2028R	Standard	28.1 (460.5)	-	4	-	14/2, 14/3, 12/3, 12/2 or 10/2		40	
2028FBAR	Flanged with Vapour Barrier		5-1/4 OD						
Low Voltage Partition, 3-3/4" W x 2-5/8" H									
2000P	Use with 2022 & 2023 Series								25



tradeSELECT™

www.hubbell.ca/wiring

HUBBELL®
Hubbell Canada