

## **Single Pole Devices**

Temporary Power Connectors for the Most Demanding Environments







# Series 15 and 16 - 150, 300 and 400 Amps, 600V AC/250V DC

Hubbell Wiring Device–Kellems offers a full line of innovative, high quality, Series 15 and Series 16 single pole plugs, receptacles and accessories for the most demanding environments.

Single pole devices are the right choice for supplying temporary electrical power distribution for entertainment, theme parks, carnival equipment, concerts, movie making and numerous other applications requiring temporary power.

Single pole devices have been designed with ease of assembly and disassembly in mind, no special tools are required. A high strength non-conductive retaining screw is all that is needed to securely lock the contacts to the insulated sleeve.

• UL Enclosure Types 3R, 4X and 12 Rating suitable for use in almost any environment





### Housing Design

- Insulgrip<sup>®</sup> style housing for superior gripping conforms to the user's hand making it easy to connect and disconnect, even with gloves on
- Easily identifiable cable cut off points for secure fit allows you to easily customize and cut the housing to the required/correct cable size
- Accommodates wide range of cables



### Safety

- Rounded corners reduce the possibility of catching or snagging on structures or equipment
- Non-conductive retaining screw locks contacts in place and allows for easy installation; prevents contact movement within housing
- Recessed mounting screw minimizes screwdriver slippage



### Identification

- Lock symbol aids in the mating of devices and provides a clear indication that the devices are properly connected
- With lock indicator symbol making mating clear and simple; devices can lock 180° to prevent unintended disconnects



### Contacts

- Provides high contact pressure and vibration resistant connection, which helps reduce operating temperatures and extends product life
- High conductivity brass contact provides improved performance by helping to reduce operating temperatures and extends life



### Assembly

- Special screw thread requires fewer turns than most competitors and reduces the risk of a conductive screw being substituted
- Extra long non-conductive inner sleeve reduces force required to install housing over contacts; easier to rotate contact in body for installing retaining screw



### Installation

- Engineered body design makes installation simple with no need for additional tools and the non-metallic retaining screw helps to make operation safe for all involved
- Strip gauge molded into every plug and receptacle housing; simplifies installation and saves time



## Series 15 - 150 Amps, 600V AC/250V DC

- Enclosure Types 3R, 4X, 12
- Combo Head, Non-Metallic Safety Retaining Screw
- Insulgrip Body Design
- Accepts #8 AWG #2 AWG Wire
- UL and cUL Listed



### 150A Plugs, Male

Description	Color	Male Plug	
Thermoplastic	Black	HBL15MBK	
elastomer,	White	HBL15MW	
cable size	Green	HBL15MGN	
#8 - #2 AWG.	Red	HBL15MR	
	Blue	HBL15MBL	
	Brown	HBL15MBN	
	Orange	HBL15MO	
	Yellow	HBL15MY	
	Gray	HBL15MGY	

### 150A Receptacles, Stud Type <sup>11</sup>/<sub>16</sub>" x <sup>3</sup>/<sub>4</sub>"

Description	Color	Female	Male
Panel Mount,	Black	HBL15FRSBK	HBL15MRSBK
thermoplastic,	White	HBL15FRSW	HBL15MRSW
cable size	Green	HBL15FRSGN	HBL15MRSGN
#8 - #2 AWG.	Red	HBL15FRSR	HBL15MRSR
	Blue	HBL15FRSBL	HBL15MRSBL
	Brown	HBL15FRSBN	HBL15MRSBN
	Orange	HBL15FRSO	HBL15MRSO
	Yellow	HBL15FRSY	HBL15MRSY
	Gray*	-	-

Note: \*Gray is available upon request. Contact factory.



### **Protective Caps**

Description	Color	Fits Male Devices	Fits Female Devices
Fits 150 amp plugs and receptacles.	Black White Green Red Blue **	HBL15MCAPBK HBL15MCAPW HBL15MCAPGN HBL15MCAPR HBL15MCAPBL —	HBL15FCAPBK HBL15FCAPW HBL15FCAPGN HBL15FCAPR HBL15FCAPBL –

Note: \*\*Additional colors are available upon request. Contact factory.





HBL15FO

HBL15FY

HBL15FGY

## Yellow Gray 150A Receptacles,

Orange


cable size

Double Set Screw		C		
Description	Color	Female	Male	
Panel Mount,	Black	HBL15FRBK	HBL15MRBK	
thermoplastic,	White	HBL15FRW	HBL15MRW	
cable size #8 - #2 AWG.	Green Red	HBL15FRGN HBL15FRR	HBL15MRGN HBL15MRR	
#o - #2 AVVG.	Blue	HBL15FRBL	HBL15MRBL	
	Brown	HBL15FRBN	HBL15MRBN	
	Orange	HBL15FRO	HBL15MRO	
	Yellow	HBL15FRY	HBL15MRY	
	Gray	HBL15FRGY	HBL15MRGY	

### **Weather Protective Covers**

Description	Color	Catalog Number
Use with stud type or double set screw receptacles.	Clear Black White Green Red Blue	HBL15NCC HBL15NCBK HBL15NCW HBL15NCGN HBL15NCR HBL15NCBL
	**	_





## Series 15 - 150 Amps, 600V AC/250V DC

Tees		
Color	Tapping Tee (Female-Female-Male)	Paralleling Tee (Female-Male-Male)
Black White Green Red Blue	HBL15TBK HBL15TW HBL15TGN HBL15TR HBL15TBL	HBL15PTBK HBL15PTW HBL15PTGN HBL15PTR HBL15PTBL

Gender Reversing Devices		1 1 2
	Double Male	Double Female
Color	(Male-Male)	(Female-Female)
Black	HBL15DMBK*	HBL15DFBK*
White	HBL15DMW	HBL15DFW
Green	HBL15DMGN	HBL15DFGN
Red	HBL15DMR*	HBL15DFR*
Blue	HBL15DMBL*	HBL15DFBL*

Note: \*Not UL listed, consult factory for availability.

Replacement Bodies (25 Pack)	200	5° 11 0000
Color	Male Body	Female Body
Black White Green Red Blue	HBL15MBBK HBL15MBW HBL15MBGN HBL15MBR HBL15MBBL	HBL15FBBK HBL15FBW HBL15FBGN HBL15FBR HBL15FBBL
**	_	_

Replacement Contacts (25 Pack)	and a second	a ser
Description	Male Pin	Female Sleeve
Contact, 150 amp	HBL15RCM	HBL15RCF

Note: \*\*Additional colors are available upon request. Contact factory.

Description	Catalog Number
Accessory Kit, retaining screw, copper foil, terminal screws and brass wire.	HBL15PK
Replacement retaining screw (100 pack).	HBL15RS
Copper foil (100 pack).	HBL15CF
Brass wire (100 pack).	HBL15BW
Terminal screw - inline (100 pack).	HBL15TS25
Terminal screw - panel mount (100 pack).	HBL15TS375
Ferrule #2 AWG (100 pack).	HBL15F2
Ferrule #4 AWG (100 pack).	HBL15F4





## Series 15 - 150 Amps, 600V AC/250V DC

### **Specifications**

Electrical	Series 15
Voltage Ratings	600V AC Maximum
	250V DC Maximum
Amperage Rating	150A Maximum
Mechanical	Series 15
Terminal	Plug: #8 AWG to #2 AWG
Accommodation	Receptacle: #8 AWG to #2 AWG
Product ID	Ratings are a permanent part of device
Base Compound	Plug: Thermoplastic Elastomer (TPE)
	Receptacle: Polybutylene Terephthalate (PBT)
Contact Material	Brass
Retaining Screw Material	Nylon

### **Certification / Environmental**

Series 15
UL and cUL listed
UL Enclosure Types 3R, 4X, 12
UL 1691 standard for single pole locking-type separable connectors
National Electric Code (NEC <sup>®</sup> ), ANSI/NFPA 70
Flammability: HB per UL94 or CSA 22.2. 0.17

### Conductor Ampacity Chart (Type SC/PPC Wire)


Cable Size	Ampacity•	
#8	80	
#6	105	
#4	140	
#2	190	


Note: •90°C column NEC Table 400.5(A)(2).

### **Dimensions** Inches (mm)

In I	_ine Plugs				
		A	В	С	D
Series 15	Male	4.54" (115.3)		.86" (21.8)	3.22" (81.7)
Ser	Female	4.60" (116.8)			3.28" (83.2)

#### Weatherproof Cover A В С 15 Cover 2.03" 1.14" 1.49" Series (37.9) (51.5) (29.0)





### Panel Mount Receptacles

	ici mount neoc									
	Threaded Stud	А	В	С	D	E	F	G	Mounting Hole	Termination
	Male	1.86" (47.2)	1.37" (34.8)	N/A	2.82" (71.6)	.86" (22.0)	.80" (20.4)	1.20" (30.5)	Through 3x Ø .20"	5/16-18 Threaded stud
es 15	Female	1.86" (47.2)	1.37" (34.8)	N/A	2.88" (73.1)	.86" (22.0)	.80" (20.4)	1.26" (32.0)	Through 3x Ø .20"	5/16-18 Threaded stud
erie	Double Set Screw	А	В	С	D	E	F	G	Mounting Hole	Termination
Š	Male	1.86" (47.2)	1.37" (34.8)	N/A	2.90" (73.6)	.86" (22.0)	.88" (22.2)	1.20" (30.5)	Through 3x Ø .20"	(2) 5/32 Socket Head set screws
	Female	1.86" (47.2)	1.37" (34.8)	N/A	2.95" (74.9)	.86" (22.0)	.87" (22.2)	1.26" (32.0)	Through 3x Ø .20"	(2) 5/32 Socket Head set screws

### Toos

Ie	es			
		А	В	С
ies 15	Tapping Tee		4.28" (108.7)	.865" (21.9)
Ser	Paralleling Tee		4.22" (107.2)	.865" (21.9)

### **Gender Reversing Devices**


		A	В	С
ies 15	Double Male	4.22" (107.2)	.86" (21.8)	_
Ser	Double Female	4.22" (107.2)	1.05" (26.7)	.68" (17.3)


Gender Reversing - Double Male

♦ 1 < </p>

### Tapping Tee

Paralleling Tee







NEC® is a registered trademark of the National Fire Protection Association (NFPA).


ċ

ŧ






### Weatherproof Cover




### Threaded Stud (Male Shown)



Mounting Holes


#### Double Set Screw (Male Shown)



### Mounting Holes

в

#### Gender Reversing - Double Female



5



## Series 16 - 300 and 400 Amps, 600V AC/250V DC

- Enclosure Types 3R, 4X, 12
- Non-Metallic Safety Retaining Screw
- Insulgrip Body Design
- Accepts #6 AWG 4/0 Wire
- UL and cUL Listed

300A Plugs

• Colors available: Black, Blue, Brown, Green, Gray, Orange, Red, White and Yellow



Description	Color	Male Plug	Female Plug
Thermoplastic elastomer, cable size #6 - 2/0 AWG.	Black White Green Red Blue Brown Orange Yellow Grav*	HBL300MBK HBL300MW HBL300MGN HBL300MR HBL300MBL HBL300MBN HBL300MO HBL300MY	HBL300FBK HBL300FW HBL300FGN HBL300FR HBL300FBL HBL300FBN HBL300FO HBL300FY




Description	Color	Male Plug	Female Plug
hermoplastic	Black	HBL400MBK	HBL400FBK
astomer,	White	HBL400MW	HBL400FW
able size	Green	HBL400MGN	HBL400FGN
/0 - 4/0 AWG.	Red	HBL400MR	HBL400FR
	Blue	HBL400MBL	HBL400FBL
	Brown	HBL400MBN	HBL400FBN
	Orange	HBL400MO	HBL400FO
	Yellow	HBL400MY	HBL400FY
	Gray	HBL400MGY	HBL400FGY

Note: \*Gray is available upon request. Contact factory.

### Receptacles, Stud Type



olua iypo			
		Through	Hole Mounting
Description	Color	Female	Male
400 amp	Black	HBLFRSBK	HBLMRSBK
Panel Mount,	White	HBLFRSW	HBLMRSW
thermoplastic	Green	HBLFRSGN	HBLMRSGN
elastomer,	Red	HBLFRSR	HBLMRSR
mates with 300	Blue	HBLFRSBL	HBLMRSBL
and 400 amp	Brown	HBLFRSBN	HBLMRSBN
plugs.	Orange	HBLFRSO	HBLMRSO
	Yellow	HBLFRSY	HBLMRSY
		ACCORDED 1	



Orange Yellow HBLFRSCO

HBLFRSCY

HBLMRSCO

HBLMRSCY

**Receptacles**,

Stud Type

plugs.

### Angled Receptacles, Stud Type

Description	Color	Female	Male
400 amp Panel Mount, thermoplastic elastomer, mates with 300	Black White Green Red Blue	HBLFRASBK HBLFRASW HBLFRASGN HBLFRASR HBLFRASBL	HBLMRASBK HBLMRASW HBLMRASGN HBLMRASR HBLMRASBL
and 400 amp plugs.	Brown Orange Yellow	HBLFRASBN HBLFRASO HBLFRASY	HBLMRASBN HBLMRASO HBLMRASY



## Series 16 - 300 and 400 Amps, 600V AC/250V DC

### Receptacles, Double Set Screw



Description	Color	Female	Male
400 amp	Black	HBLFRBK	HBLMRBK
Panel Mount,	White	HBLFRW	HBLMRW
thermoplastic	Green	HBLFRGN	HBLMRGN
elastomer, cable	Red	HBLFRR	HBLMRR
size #4 - 4/0 AWG, mates with 300	Blue	HBLFRBL	HBLMRBL
and 400 amp	Brown	HBLFRBN	HBLMRBN
plugs.	Orange	HBLFRO	HBLMRO
plago.	Yellow	HBLFRY	HBLMRY
	Gray	HBLFRGY	HBLMRGY

### Angled Receptacles, Double Set Screw

Angled Receptacles,

**Bus Bar Mount** 

Description

400 amp

elastomer,

plugs.

Panel Mount,

thermoplastic

mates with 300

and 400 amp



Male

HBLMRABBK

HBLMRABGN

HBLMRABW

HBLMRABR

HBLMRABN

**HBLMRABO** 

HBLMRABY

HBLMRABBL

Description	Color	Female	Male
400 amp	Black	HBLFRABK	HBLMRABK
Panel Mount,	White	HBLFRAW	HBLMRAW
thermoplastic	Green	HBLFRASGN	HBLMRAGN
elastomer, cable	Red	HBLFRAR	HBLMRAR
size #4 - 4/0 AWG,	Blue	HBLFRABL	HBLMRABL
mates with 300	Brown	HBLFRABN	HBLMRABN
and 400 amp	Orange	HBLFRAO	HBLMRAO
plugs.	Yellow	HBLFRAY	HBLMRAY
	Gray*	_	-

Female

HBLFRABBK

HBLFRABGN

HBLFRABW

HBLFRABR

HBLFRABN

**HBLFRABO** 

HBLFRABY

HBLFRABBL

Note: \*Gray is available upon request. Contact factory.

Color

Black

White

Green


Red

Blue

Brown

Orange

Yellow




# Terminals,



<b>Offset Straig</b>	nt Style		
Description	Color	Female	Male
400 amp	Black	HBLFOSBK	HBLMOSBK
Panel Mount,	White	HBLFOSW	HBLMOSW
thermoplastic	Green	HBLFOSGN	HBLMOSGN
elastomer,	Red	HBLFOSR	HBLMOSR
mates with 300	Blue	HBLFOSBL	HBLMOSBL
and 400 amp	Brown	HBLFOSBN	HBLMOSBN
plugs.	Orange	HBLFOSO	HBLMOSO
	Yellow	HBLFOSY	HBLMOSY

Note: Terminals are UL Type 1 only.



Description	Color	Female	Male
400 amp Mount,	Black	HBLFOABK	HBLMOABK
thermoplastic	White	HBLFOAW	HBLMOAW
elastomer,	Green	HBLFOAGN	HBLMOAGN
mates with 300	Red	HBLFOAR	HBLMOAR
and 400 amp	Blue	HBLFOABL	HBLMOABL
plugs.	Brown	HBLFOABN	HBLMOABN
	Orange	HBLFOAO	HBLMOAO
	Yellow	HBLFOAY	HBLMOAY

Note: Angled terminals are UL Type 1 only.





## Series 16 - 300 and 400 Amps, 600V AC/250V DC

### **Tees and 3-Fers**

Color	Tapping Tee (Female-Female-Male)	Paralleling Tee (Female-Male-Male)	3-Fer (Male-Female- Female-Female)	3-Fer (Female-Male- Male-Male)	Soft 3-Fer (Male- Female-Female-Female)	Color	(1-Male, 6-Females)
Black White Green	HBLTBK HBLTW HBLTGN	HBLPTBK HBLPTW HBLPTGN	HBLM3FBK HBLM3FW HBLM3FGN	HBLF3MBK HBLF3MW HBLF3MGN	HBLM3FSBK (Black only)	Black White Green	HBL7DBBK HBL7DBW HBL7DBGN
Red Blue	HBLTR HBLTBL	HBLPTR	HBLM3FR HBLM3FBL	HBLF3MR HBLF3MBL	Soft 3-Fer (Female- Male-Male-Male)	Red Blue	HBL7DBR HBL7DBBL
Brown Orange Yellow	HBLTBN HBLTO HBLTY	HBLPTBN HBLPTO HBLPTY	HBLM3FBN HBLM3FO HBLM3FY	HBLF3MBN HBLF3MO HBLF3MY	HBLF3MSGN (Green only)	Brown Orange Yellow	HBL7DBBN HBL7DBO HBL7DBY

### **Gender Reversing Devices**

		- Autom
	Double Male	Double Female
Color	(Male-Male)	(Female-Female)
Black	HBLDMBK	HBLDFBK
White	HBLDMW	HBLDFW
Green	HBLDMGN	HBLDFGN
Red	HBLDMR	HBLDFR
Blue	HBLDMBL	HBLDFBL
Brown	HBLDMBN	HBLDFBN
Orange	HBLDMO	HBLDFO
Yellow	HBLDMY	HBLDFY

### **Protective Caps**

Fits Female Devices	Fits Male Devices
HBLFCAPBK HBLFCAPW HBLFCAPGN HBLFCAPR HBLFCAPBL HBLFCAPBN HBLFCAPO HBLFCAPY	HBLMCAPBK HBLMCAPW HBLMCAPGN HBLMCAPR HBLMCAPBL HBLMCAPBN HBLMCAPO HBLMCAPY

### Snap Back Covers (3R Only)

	- Hilling	
Color	Male Body	Female Body
Black	HBLMBBK	HBLFBBK
White	HBLMBW	HBLFBW
Green	HBLMBGN	HBLFBGN
Red	HBLMBR	HBLFBR
Blue	HBLMBBL	HBLFBBL
Brown	HBLMBBN	HBLFBBN
Orange	HBLMBO	HBLFBO
Yellow	HBLMBY	HBLFBY

Replacement Bodies (10 Pack)

# Tł

69	
Through Hole	Threaded
Mounting	Mounting Holes
HBLSCBK	HBLSCCBK
HBLSCW	HBLSCCW
HBLSCGN	HBLSCCGN
HBLSCR	HBLSCCR
HBLSCBL	HBLSCCBL
HBLSCBN	HBLSCCBN
HBLSCO	HBLSCCO
HBLSCY	HBLSCCY

### **Distribution Block**

olor (1-Male, 6-Females) ack HBL7DBBK hite HBL7DBW reen HBL7DBGN ed HBL7DBR ue HBL7DBBL rown HBL7DBBN range HBL7DBO HBL7DBY		Sales
hite HBL7DBW reen HBL7DBGN ed HBL7DBR ue HBL7DBBL rown HBL7DBBN range HBL7DBO	olor	(1-Male, 6-Females)
	hite reen ed ue rown range	HBL7DBW HBL7DBGN HBL7DBR HBL7DBBL HBL7DBBN HBL7DBO

### Weather Protective Lift Covers

Color	Catalog Number	All One Color Caps and Bodies
Clear	–	HBLNCC
Black	HBLNCBK	HBLNCABK
White	HBLNCW	HBLNCAW
Green	HBLNCGN	HBLNCAGN
Red	HBLNCR	HBLNCAR
Blue	HBLNCBL	HBLNCABL
Brown	HBLNCO	HBLNCABN
Orange	HBLNCO	HBLNCAO
Yellow	HBLNCY	HBLNCAY

### Replacement Contacts (20 Pack)

6	and and	1
Description	Male Pin	Female Sleeve
Contact, 300 amp	HBL300RCM	HBL300RCF
Contact, 400 amp	HBL400RCM	HBL400RCF

### Accessories

Description	Catalog Number
Accessory Kit, retaining screw, copper foil, terminal screws and brass wire.	HBLPK
Replacement retaining screw (500 pack).	HBLRS
Copper foil (500 pack).	HBLCF

### Accessories

Description	Catalog Number	
Brass wire (500 pack).	HBLBW	
Terminal screw - panel mount (500 pack).	HBLTSR	
Terminal screw - in line (500 pack).	HBLTS	
		_



## Series 16 - Specifications and Dimensions

### **Specifications**

Electrical	Series 16			
Voltage Ratings	600V AC Maximum 250V DC Maximum			
Amperage Rating	400A Maximum	-		
Mechanical	300A	400A		
Terminal Accommodation	Plug: #6 to 2/0 AWG	Plug: 2/0 to 4/0 AWG Recept.: #4 to 4/0 AWG		

Accommodation		
Product ID	Ratings are a permane	ent part of device
Base Compound	Thermoplastic Elaston	ner (TPE)
Contact Material	Brass	
Retaining Screw Material	Nylon	

### Dimensions Inches (mm)

In I	Line Plug	js				In Line Plug (Male Shown)	Weatherproo
		А	В	С	D	A	I <del>-</del> B−
ies 16	Male	7.01" (178.0)	1.38" (35.1)	1.48" (37.6)	4.78" (121.4)		
Ser	Female	7.10" (180.5)	1.44" (36.6)	1.06" (27.0)	4.90" (121.3)		A M

	Threaded Stud	А	В	С	D	E	F	G	Mounting Hole	Termination
	Male & Female with through hole mounting	2.20" (55.9)	2.20" (55.9)	1.50" (38.1)	4.10" (104.3)	1.48" (47.4)	1.25" (31.7)	1.74" (44.2)	Through 4x Ø .20"	1/2-13 UNC-2A Threaded stud
	Male & Female with threaded mounting holes	2.20" (55.9)	2.20" (55.9)	1.50" (38.1)	3.67" (93.2)	1.48" (47.4)	1.11" (28.2)	1.55" (39.4)	Threaded 4x #10-32	1/2-13 UNC-2A Threaded stud
	Double Set Screw	А	В	С	D	E	F	G	Mounting Hole	Termination
16	Male & Female with threaded mounting holes	2.20" (55.9)	2.20" (55.9)	1.50" (38.1)	4.10" (104.3)	1.48" (47.4)	1.36" (34.5)	1.74" (44.2)	Threaded 4x #10-32	(2) 7/32 Socket Head set screws
6	Busbar Type	А	В	С	D	E	F	G	Mounting Hole	Termination
Serie	Male & Female with threaded mounting holes	2.20" (55.9)	2.20" (55.9)	1.50" (38.1)	3.57" (90.7)	1.48" (37.6)	1.01" (25.7)	1.55" (39.4)	Threaded 4x #10-32	(1) 5/16-18 UNC-2B Threaded hole
	Offset Terminals	А	В	С	D	E	F		Mounting Hole	Termination
	Male terminal straight style	Ø1.48" [37.6]	1.00" (25.4)	.38" (9.5)	3.89" (98.8)	1.75" (44.5)	2.14" (54.4)		Through .50" (12.7)	_
	Female terminal straight style	Ø1.48" [37.6]	1.00" (25.4)	.38" (9.5)	3.68" (93.3)	1.75" (44.5)	1.93" (48.9)		Through .50" (12.7)	_
	Male terminal angled style	Ø1.48" [37.6]	1.00" (25.4)	.38" (9.5)	3.98" (101.1)	2.06" (52.2)	2.14" (54.4)		Through .50" (12.7)	-
	Female terminal angled style	Ø1.48" [37.6]	1.00" (25.4)	.38" (9.5)	3.76" (95.6)	2.06" (52.2)	1.93" (48.9)		Through .50" (12.7)	_

(	Cov	vers			
		Description	A	В	С
	es 16	Weatherproof Cover	2.20" (55.88)	1.16" (29.44)	2.03" (51.5)
	Seri	Snap Back Cover to be used with receptacles		2.37" (60.2)	_

Ge	nder Revei	rsing De	evices	
9	Description	А	В	С
ies 1	Double Male	4.65" (118.1)	1.48" (37.6)	-
Ser	Double Female	4.84" (122.9)	1.44" (36.6)	1.06" (27.0)

### **Certification / Environmental**

Series 16 UL and cUL listed UL Enclosure Types 3R, 4X, 12 UL 1691 standard for single pole locking-type separable connectors National Electric Code (NEC®), ANSI/NFPA 70 Flammability: HB per UL94 or CSA 22.2. 0.17

### Conductor Ampacity Chart (Type SC/PPC Wire)

Cable Size	Ampacity•	Cable Size	Ampacity	
#6	105	2/0	300	
#4	140	4/0	405	
#2	190			

Note: •90°C column NEC Table 400.5(A)(2).

of Cover


Gender Reversing - Double Male

- A


\$ â  $\Rightarrow$ 

В


- B -




Mounting Holes Double Set Screw (Male Shown)




-Mounting Holes Busbar Type (Male Shown)




Offset Terminals (Male Shown) Straight Style





HUBBELL

Snap Back Cover



NEC® is a registered trademark of the National Fire Protection Association (NFPA).



## Series 18 - 300 and 400 Amps, 600V AC/250V DC

Hubbell Wiring Device–Kellems Series 18, Ball Nose, Single Pole plugs and connectors are cULus listed for use in USA and Canada, and are compatible with all competitive products.

Series 18 Single Pole is a popular solution for welding connections and at shipyards. They are also widely used in the Canadian Broadcasting Industry.

- UL Type 4X environmental rating suitable for extreme outdoor conditions
- Replacement bodies available



HBL18300MBK





### Housing Design

- Ribbed thermoplastic elastomer body for a greater hold when plugging and unplugging the device
- Accommodates wide range of cables



### Contacts

- One piece brass contact design
- Double set screw for the highest performance and coolest running connection



### Safety

- Non-metallic retaining screw for user safety
- Recessed mounting screw minimizes
   screwdriver slippage



### Assembly

- Keyed nylon interior for ease of assembly
- Special screw thread requires fewer turns than most competitors and reduces the risk of a conductive screw being substituted



## Series 18 - 300 and 400 Amps, 600V AC/250V DC

300A Plugs		<b>)</b>	
Description	Color	Male Plug	Female Plug
Thermoplastic	Black	HBL18300MBK	HBL18300FBK
elastomer,	White	HBL18300MW	HBL18300FW
cable size	Green	HBL18300MGN	HBL18300FGN
#2 - 2/0 AWG.	Red	HBL18300MR	HBL18300FR
	Blue	HBL18300MBL	HBL18300FBL
	Brown	HBL18300MBN	HBL18300FBN
	Orange	HBL18300MO	HBL18300FO
	Yellow	HBL18300MY	HBL18300FY

400A Plugs	(	3)	
Description	Color	Male Plug	Female Plug
Thermoplastic elastomer, cable size 3/0 - 4/0 AWG.	Black White Green Red Blue Brown Orange Yellow	HBL18400MBK HBL18400MW HBL18400MGN HBL18400MR HBL18400MBL HBL18400MBN HBL18400MO HBL18400MY	HBL18400FBK HBL18400FW HBL18400FGN HBL18400FR HBL18400FBL HBL18400FBN HBL18400FO HBL18400FY



Bodies (10 Pa			
Description	Color	Male Plug	Female Plug
Thermoplastic elastomer.	Black White Green Red Blue Brown Orange Yellow	HBL18MBBK HBL18MBW HBL18MBGN HBL18MBR HBL18MBBL HBL18MBBN HBL18MBO HBL18MBY	HBL18FBBK HBL18FBW HBL18FBGN HBL18FBR HBL18FBBL HBL18FBBN HBL18FBBN HBL18FBO HBL18FBY

### **Specifications**

Replacement

Electrical	Series 18
Voltage Ratings	600V AC Maximum
	250V DC Maximum
Amperage Rating	400A Maximum

Mechanical	300A	400A
Terminal	Plug: #2 to 2/0 AWG	Plug: 3/0 to 4/0 AWG
Accommodation		
Product ID	Ratings are a permanent p	part of device
Base Compound	Thermoplastic Elastomer (	(TPE)
Contact Material	Brass	
Retaining Screw	Nylon	
Material		

### **Certification / Environmental**

Accessories
Description

Series 18, replacement retaining screw (500 pack).


Series 18	
UL and cULus listed	
UL Enclosure Types	3R, 4X, 12
	r single pole locking-type separable connectors
National Electric Coc	le (NEC), ANSI/NFPA 70
Flammability: HB per	UL94 or CSA 22.2. 0.17

Cable Size Ampacity					
	Ampaony				
#2	190				
2/0	300				
3/0	350				
4/0	405				


Note: •90°C column NEC Table 400.5(A)(2).

### Dimensions

In Line Plugs								
Description	А	В	С	D	E	F		
Male	6.77"	2.06"	1.61"	1.85"	.73"	.38" (TYP)		
	(172.0)	(52.3)	(40.9)	(47.0)	(18.5)	(9.7)		
Female	6.21"	1.50"	1.61"	1.85"	.73"	.38" (TYP)		
	(157.7)	(38.1)	(40.9)	(47.0)	(18.5)	(9.7)		



### In Line Plug (Female)







Catalog Number

## Wiring Device-Kellems Single Pole Devices

### Temporary Power Designed for the Most Demanding Environments

## More Industry Products from Hubbell

STRAIGHT BLADE DEVICES



Insulgrip<sup>®</sup> Plugs, Connectors, Receptacles and Inlets - the widest range of singularly rated NEMA devices available. Insulgrip products are synonymous with Hubbell's ongoing commitment to producing high quality electric products. TWIST-LOCK® DEVICES



Twist-Lock<sup>®</sup> Insulgrip<sup>®</sup> Plugs, Connectors, Receptacles and Inlets - the widest range of singularly rated NEMA devices available. Designed to last from engineered thermoplastic materials and high performing alloys. **IEC PIN & SLEEVE DEVICES** 




HUBBELI

IEC Watertight Devices provide safe and dependable performance in the most demanding environments. Heavy duty nonconductive nylon construction provides impact and corrosion protection.

## Available Literature

Hubbell offers an extensive literature library for product support. Downloadable PDFs are available online at *www.hubbell-wiring.com*.





Insulgrip<sup>®</sup> Wiring Devices Application Guide



Hubbell Slide Charts







Kellems® Mesh Grips

## Website Support

The Hubbell Wiring Systems website offers fast convenient information with our online virtual catalog, technical support, literature support and more. The website also offers landing pages for vertical markets and sustainable building. Visit www.hubbell-wiring.com.





www.hubbell-wiring.com



 Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

 Phone (800) 288-6000 • FAX (800) 255-1031

 Printed in U.S.A. Specifications subject to change without notice. (\*) is registered trademark of Hubbell Incorporated.
 WLBSP002 5/17