


STARLINE II



Mounting Options

- Pole/Column
- Post Top/Slip Fitter
- Side Entry Spigot
- Wall Mount



The Starline II LED perfectly combines innovations in heat management, optical performance and energy saving in a sleek exterior.

The ultimate solution to replace traditional HID sources with versatility and reliability. High power LEDs minimise energy and operating costs, while the low profile appearance and low weight allow the Starline II to be safely installed on new and existing infrastructure.

Standard Specification

Starline II LED Streetlight

Enclosure	Die cast aluminum alloy with white polyester powder coat paint	
Entry	Side entry as standard	
Termination	Pre-installed flying leads	
Installation	Spigot entry	
Control Gear	Electronic driver	
Colour Temperature (CCT)	5000K (Cool White)	
Maintenance	Underside access, secured by socket heads	
Ingress Protection	IP66	
Surge Protection	6kV	
Electrical Supply	120 - 277V AC 50/60Hz	









Features


- Slim, elegant design
- Highly Energy Efficient
- Lightweight and low windage
- Dark sky friendly, no upward light






Std. Cat No.	Delivered Output	Power Consumption	Ambient °C	Weight
SL2I/05L/LE	4835 lm	40W	-40 to +55	5.0kg
SL2I/09L/LE	8923 lm	75W	-40 to +55	5.0kg
SL2I/13L/LE	13226 lm	120W	-40 to +55	6.0kg
SL2I/17L/LE	17355 lm	150W	-40 to +55	6.5kg
SL2I/24L/LE	24318 lm	200W	-40 to +55	8.0kg

Options - Suffix to Catalogue No.						
/SF	Slip Fitter mount	/WM	Wall mount			



L (mm)
392.9
392.9
443.8
494.8
601.3



are subject to change without www.chalmit.com





