



We are pleased to announce the addition of a family of Heavy Duty Insulated Multi-tap and In-Line splicer/reducers to our current offering of UNITAP™ connectors. This expansion includes 8 tap configurations and in-line splicer/reducers in both clear and UV-rated black and accommodate wire sizes from #2 - 750 kcmil. Each conductor port contains 2 set screws to increase the strength and performance of the connector, and will provide a reliable and robust connection in the most demanding applications.

[Click here to view the introductory video on UNITAP™ Heavy Duty Series](#)

Useful Links

Product Information

[UNITAP™ Heavy Duty Series - Introduction Document](#)

[UNITAP™ Heavy Duty Series - Cut Sheet](#)

[UNITAP™ Heavy Duty Series - Press Release](#)

Markets & Application

Commercial & Industrial

Solar

Utility

MRO

Features and Benefits

600 Volt Rated

Fully insulated aluminum 6061-T6 connector body saves time and lowers installation costs by eliminating taping

Listed to UL 486A-B, File E9498

Dual Rated for use with copper and aluminum conductors

Range taking designs accommodate wire sizes from #2 - 750 kcmil

Configurations include Double-Side Entry Taps in 2 to 12 ports and In-Line Splicer/Reducers

Available in UV-Rated Black or Clear Plasticsol Insulation

Operating temperature range from -40°C to 135°C

Conductor ports are pre-filled with oxide inhibitor

Screw Port and Conductor Port caps provided to protect against contamination and accidental contact of energized parts