


Nylon 12 UV Black Cable Ties

UNIRAP™ Nylon 12 Cable Ties

Type CTNT

Nylon 12 cable ties provide excellent UV, chemical and moisture resistance. The ties feature inside serrations and a bent tail for quick and easy installation. Manufactured from polyamide 12 the ties also have a smooth edge to prevent bundle damage. The hygroscopic property of Nylon 12 make them especially suitable in high moisture, corrosive (zinc chloride and dilute acids) environments or where low temperatures are a factor. Suitable for both indoor and outdoor applications.



Std Pkg Catalog Number	Color	Max. Bundle Dia. In. [mm]	Min. Tensile Strength (lb)	Length	Width	Installation Tooling	Bulk Pkg Catalog Number
				in [mm]	in [mm]	Tool	
Nylon 12 UNIRAP - 50 Lb. Tensile Strength							
CTNT50200C0	UV Black	2.00 [50]	50	7.50 [190]	0.19 [4.8]	MK9 CTT50	CTNT50200D0
CTNT50275C0	UV Black	2.75 [70]		11.00 [280]			CTNT50275D0
CTNT50350C0	UV Black	3.50 [90]		13.78 [350]			CTNT50350D0
CTNT50400C0	UV Black	4.00 [102]		15.00 [380]			CTNT50400D0
CTNT50500C0	UV Black	5.12 [130]		18.10 [460]			CTNT50500D0
CNTN50575C0	UV Black	5.90 [150]		19.69 [500]			CTNT50575D0
CTNT50650C0	UV Black	6.70 [170]		23.62 [600]			CTNT50650D0
CTNT50725C0	UV Black	7.30 [185]		25.60 [650]			CTNT50725D0
CTNT50750C0	UV Black	7.50 [190]		27.60 [700]			CTNT50750D0