

1214, 1315, 1416 & 1517 Style Steel Service Punch Tee Installation Instructions

Threaded Inlet x Metallic Pipe (Conductive) Compression Outlet

1. Before installing the service tee, confirm the punch is rated for the steel pipe to be tapped.
 - 3/8" tip punches are rated for 0.280" maximum wall thickness and 70 ksi maximum yield strength.
 - 1/4", 1/2", 3/4" & 1" tip punches are rated for 0.250" maximum wall thickness and 65 ksi maximum yield strength.

IMPORTANT

Pressure Rating: 300 psig MAOP

Operating Temperature: -20 to 140° F

Material: Carbon Steel

2. Verify that the outlet on the service tee is the correct size for the service line.
3. Apply thread sealant to the inlet threads of the tee.
4. Screw the tee into the mating female pipe thread.
5. Make the service connection. See other side for outlet assembly instructions.
6. To assure proper assembly and to comply with 49 CFR 192 Subpart J—Test Requirements, the joint shall be leak tested.
7. **Lubricant must be applied to the punch threads and punch tip.** Acceptable lubricants include thread cutting oil, tapping fluid or tapping grease.
8. Insert punch in service tee and turn clockwise by hand to avoid cross threading.
9. Use a ratchet wrench with Continental drive key and bushing to make the tap.
 - For 1/2" body tees, use 23-3691-00 Hex Drive Key, Bushing & Socket Adapter
 - For 3/4" body tees, use 23-3692-00 Hex Drive Key, Bushing & Socket Adapter
 - For 1" body tees, use 23-0941-00 Square Drive Key, Bushing & Socket Adapter
 - For 1 1/4" body tees, use 23-0940-00 Square Drive Key, Bushing & Socket Adapter

IMPORTANT: To insure retention of the coupon - coupon retaining punches should be run all the way down until the punch seats on the main.

10. To allow gas to the service line, back punch up until it is flush with the top of the tee.

11. Apply thread sealant and install pipe cap leak tight.

NOTE: If desirable at a later date, the service may be interrupted by running the punch valve down until it seats on the main.

ECN 2620 REV "D" 07/23/14

Compression Outlets — 1/2" OD & 5/8" OD Lock Type Conductive

1. Clean metallic pipe ends thoroughly. Remove any coatings, dirt, etc.
2. Loosen compression nut and insert pipe until it bottoms in outlet.
3. Tighten compression nut until it bottoms on shoulder (metal to metal).

Size	Metallic Pipe Pullout Resistance
1/2" OD	500 lbs
5/8" OD	2,000 lbs

NOTE: The conductive compression outlet is not a full restraint joint. WHERE PIPE PULLOUT COULD OCCUR, THE PIPE JOINT MUST BE ANCHORED.

Compression Outlets — 3/4" IPS & Larger Non-Lock Type Conductive

1. Clean metallic pipe ends thoroughly. Remove any coatings, dirt, etc.
2. Loosen compression nut and insert pipe until it bottoms in outlet. Pipe misalignment shall be no more than 3 ½°.
3. Tighten compression nut to the torque values listed.

Size	Torque Ftlbs	Metallic Pipe Pullout Resistance
3/4" IPS	120-140	575 lbs
1" IPS	120-140	900 lbs
1 1/4" IPS	280-300	1,000 lbs

NOTE: The conductive compression outlet is not a full restraint joint. WHERE PIPE PULLOUT COULD OCCUR, THE PIPE JOINT MUST BE ANCHORED.