

Cord Reels



HUBBELL[®]

inREACH™ Industrial & Weatherproof Cord Reels

Hubbell's redesigned inREACH™ Industrial and Industrial Weatherproof Cord Reels enhance user safety and maximize efficiency by managing cord and power in a safe and organized manner, while also meeting the demands of tough industrial environments.

inREACH™ Industrial and Industrial Weatherproof Cord Reels are listed to UL 355 and CSA, C22.2 No. 308 with a durable, lightweight low profile cast aluminum construction. inREACH™ reels also feature an improved mounting plate that allows customers to upgrade existing installations or use Hubbell's innovative mounting bracket for a quick, easy installation on any surface.

inREACH™ *No matter what your need, Hubbell will always be inREACH™!*

inREACH™ Industrial Reels are built to provide safe, convenient power for demanding commercial and industrial applications and environments. These reels feature a 250V rating and can be ceiling, wall or bench mounted. They are available with incandescent, fluorescent or LED hand lamps, as well as a variety of Hubbell 15 and 20 amp connectors and portable outlet boxes.

inREACH™ Industrial Weatherproof Reels are made for outdoor and washdown environments, with a 600V rating and UL Type 4 enclosure rating. They are designed for use with 15, 20 and 30 amp industrial products, such as portable outlet boxes, Insulgrip® and Twist-Lock® devices.

inREACH™ Industrial & Industrial Weatherproof Cord Reels

- » Durable, corrosion resistant cast aluminum construction
- » Yellow or white powder coat finish
- » Movable guide arm can be mounted in two positions
- » Positive latch mechanism automatically maintains desired cord length
- » Ratchet lock can be disengaged in field for constant tension applications
- » 16-10AWG, 3 & 4 conductor cord for greater current carrying capacity
- » 10AWG is fully rated at 30 amps
- » Available in 25ft, 35ft and 45ft lengths

inREACH™ Industrial Cord Reels

- » UL Type 1
- » 250V AC, SJO Type Cable
- » Plug-in 5ft long power cord requires no electrical wiring

inREACH™ Industrial Weatherproof Cord Reels

- » UL Type 4
- » 600V AC, SOW Type Cable
- » 3/4 NPT conduit hub



Laboratory



Manufacturing



Data Center



inREACH™ Category 6 Data Reel

inREACH™ Category 6 Data Reels offer flexible ethernet connectivity while maintaining the durable and installation-efficient design of the inREACH cord reel family. inREACH Category 6 Data Reels ensure excellent performance and minimal electrical noise, making them perfect for schools, universities or retail.

inREACH™ Category 6 Data Reels


- » 50ft cord length, 4ft input pigtail; RJ45 plug on input and output cords
- » Special gold-on-gold slip ring maintains Ethernet communications with minimal electrical noise for unparalleled performance
- » 1000BASE-T (Gigabyte Ethernet) compatible plug-n-play Ethernet connection



inREACH™ Mounting Bracket

The inREACH™ mounting bracket allows you to decrease or eliminate the additional labor associated with installing reels at the end of the job. By starting the installation during the earlier stages of the project when there are fewer time constraints, the inREACH™ mounting bracket reduces trim-out to a fraction of the time.

Labor Savings are inREACH™!



Step 1

Secure the inREACH™ mounting bracket during the rough-in process.



Step 2

Remove two of the hex bolts from the bracket. Slide the reel into the bracket.



Step 3

Replace two hex bolts and secure screws to complete the job.



Quality is inREACH™

inREACH™ cord reels are supplied with best in class Hubbell products to service all your needs!

- » HBL5266C
- » HBL5366C
- » HBL5269C
- » HBL5369C
- » HBL2313
- » HBLPOB1
- » GFM20

Heavy Duty Industrial Weatherproof Cord Reels

Heavy Duty Industrial Weatherproof Reels are made for the most abusive and demanding environments, with a 600V rating and UL Type 4 enclosure rating. They are designed for use with 15, 20 and 30 amp industrial products such as portable outlet boxes, Insulgrip® and Twist-Lock® devices and pendant push-button stations.

Heavy Duty Industrial Weatherproof Cord Reels

- » Powder coated, solid US steel construction
- » Ratchet lock can be disengaged in field for constant tension application
- » UL Type 4 enclosure protects spring motor, junction box, slip ring assembly and cable entrance from hosedown and corrosion
- » Not supplied with end effectors
- » 3/4 NPT conduit hub



Manufacturing



Outdoor Locations




Government

Stainless Steel Cord Reels

Stainless steel cord reels are suited for applications where corrosion or sanitation is a concern, such as food processing, pharmaceuticals, and water treatment facilities.

Stainless Steel Cord Reels

- » Heavy gauge 304L stainless steel provides corrosion resistance
- » Compact design minimizes required installation space
- » Cam latching system for quieter, smoother retraction
- » Not supplied with end effectors



Commercial Cord Reels

Commercial Cord Reels are designed for the less demanding requirements of commercial and light industrial environments. UL Listed, these reels feature a steel or non-metallic construction and a 125V rating with SJT type cord to provide power and lighting for all your needs.

Steel Commercial Cord Reels

- » Compact, durable steel construction
- » Flexible mounting options for ceiling, wall or bench
- » Automatic ratchet lock maintains desired cord length and easy, smooth retraction

Non-Metallic Commercial Cord Reels

- » Durable lightweight non-metallic housing
- » 40 ft of 12/3 cord for greater current carrying capacity
- » Triple tap outlet with supplemental overcurrent protection




Air/Water Hose Reels

Air/Water Hose Reels are highly versatile and ideal for tight spaces. The full flow shafts and swivels assure maximum product delivery.

Air/Water Hose Reels

- » Constructed of rugged steel with baked polyester finish components
- » Multi-position four roller guide and adjustable hose stop
- » Spring rewind and ratchet lock



Static Discharge Reels

Static Discharge Reel ground portable equipment operating in hazardous environments. When properly clamped to ground, the static discharge reel will prevent the build up of static electricity and reduce the chance of sparking, which may cause an explosion.

Static Discharge Reels

- » Steel construction available with steel or nylon coated steel cable
- » Compact design minimizes required installation space
- » Large grounding jaw clamp provides low resistance ground termination



Cord & Hose Reels

inREACH™ Industrial Weatherproof Cord Reels

Description	Amps	Voltage	Cable Length ft. (m)	Cable Type	Weight lbs. (kg)	Catalog Number
Yellow Weatherproof Industrial Reel	10A	600V AC	45 (13.7)	16/3 SOW	23.6 (10.7)	HBLW45163
				16/4 SOW	25.6 (11.6)	HBLW45164
Yellow Weatherproof Industrial Reel	15A	600V AC	45 (13.7)	14/3 SOW	28.2 (12.8)	HBLW45143
				14/4 SOW	30.0 (13.6)	HBLW45144
Yellow Weatherproof Industrial Reel	20A	600V AC	45 (13.7)	12/3 SOW	31.3 (14.2)	HBLW45123
				12/4 SOW	32.2 (14.6)	HBLW40124
Yellow Weatherproof Industrial Reel	30A	600V AC	40 (12.2)	10/3 SOW	33.3 (15.1)	HBLW40103
				10/4 SOW	34.2 (15.5)	HBLW35104

All industrial weatherproof cord reels are supplied with wire leads and 3/4" NPT hub feed. Power supply cable not supplied. For shorter cable lengths, modify length indication in catalog number (i.e. HBLWXX); 35ft & 25ft lengths are available. For white reel, add 'W' suffix to catalog number



inREACH™ Industrial Cord Reels

Description	Amps	Voltage	Cable Length ft (m)	Cable Type	Weight lbs. (kg)	Catalog Number
White Industrial Reel without end effectors	10A	250V AC	45 (13.7)	16/3 SJO	22.9 (10.4)	HBLI45163
				16/4 SJO	23.6 (10.7)	HBLI45164
	15A	250V AC	45 (13.7)	14/3 SJO	24.0 (10.9)	HBLI45143
				14/4 SJO	25.4 (11.5)	HBLI45144
	20A	250V AC	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123
				12/4 SJO	29.8 (13.5)	HBLI45124
	30A	250V AC	45 (13.7)	10/3 SJO	32.4 (14.7)	HBLI45103
				10/4 SJO	33.7 (15.3)	HBLI40104
Industrial Reel without end effectors	20A	250V AC	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLIWC45123
						HBLI45123BLK
White Industrial Reel	15A	125V AC	45 (13.7)	14/3 SJO	24.0 (10.9)	HBLI45143C15
						HBLI45143C15
White Industrial Reel with Yellow Portable Outlet Box	15A	125V AC	45 (13.7)	14/3 SJO	24.0 (10.9)	HBLI45143R15
						HBLI45143R215
White Industrial Reel with Black Portable Outlet Box	15A	125V AC	45 (13.7)	14/3 SJO	24.0 (10.9)	HBLI45143R15M1
						HBLI45143R215M1
White Industrial Reel with Yellow Portable Outlet Box	20A	125V AC	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123R20
						HBLI45123R220
White Industrial Reel with Black Portable Outlet Box	20A	125V AC	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123R20M1
						HBLI45123R220M1

15A reels are supplied with HBL5266C on the power supply cord. 20A reels are supplied with HBL5366C on the power supply cord. For shorter cable lengths, modify length indication in catalog number (i.e. HBLIXX); 35ft & 25ft lengths are available. For yellow reel, add 'Y' suffix to catalog number.



inREACH™ Category 6 Data Reels

Description	Cable Length ft (m)	Cable Type	Weight lbs. (kg)	Catalog Number
Black Data Reel with RJ45 Plugs	50 (15.2)	Cat 6	22.9 (10.4)	HBLI50CAT6

inREACH™ Industrial Lighted Cord Reels

Description	Cable ft (m)	Cable Type	Watts (Max)	Amps	Voltage	Weight lbs. (kg)	Catalog Number
White Industrial Reel	45 (13.7)	16/3 SJO	8+1	0.07A	120V AC	22.9 (10.4)	HBLI45163LED
			13	0.3A	120V AC	22.9 (10.4)	HBLI45163FL
			100	0.8A	125V AC	22.9 (10.4)	HBLI45163IN

15A reels are supplied with HBL5266C on the power supply cord. For shorter cable lengths, modify length indication in catalog number (i.e. HBLIXX); 35ft & 25ft lengths are available. For yellow reel, add 'Y' suffix to catalog number.



inREACH™ Mounting Accessories

Description	Weight lbs. (kg)	Catalog Number
Mounting bracket	2.5 (1.1)	HBLIMB
Mounting bracket with junction box mount	3.0 (1.4)	HBLIMBJ
340° pivot base	3.5 (1.6)	HBLI340PB
Plenum rated enclosure	30.0 (13.6)	HBLIPRBOX

inREACH™ Replacement Parts

Description	Weight lbs. (kg)	Cable Type	Catalog Number
Replacement stop	0.2 (.09)	16AWG	HBLI16BS
		14AWG	HBLI14BS
		12AWG	HBLI12BS
		10AWG	HBLI10BS



Heavy Duty Industrial Weatherproof Reels*

Description	Cable ft (m)	Cable Type	Amps	Volts AC	Weight lbs. (kg)	Catalog Number
14" yellow weatherproof reel	50 (15.2)	14/3 SOW-A	15	600	55 (24.9)	HBL501431W
16" weatherproof reel yellow housing white housing	50 (15.2)	12/3 SOW-A	20	600	80 (36.3)	HBL501232W HBL501232WM1
16" yellow weatherproof reel	50 (15.2)	12/4 SOW-A	16	600	86 (39.0)	HBL501242W
16" weatherproof reel yellow housing white housing	50 (15.2)	10/3 SOW-A	25	600	86 (39.0)	HBL501032W HBL501032WM1
16" yellow weatherproof reel	50 (15.2)	10/4 SOW-A	20	600	92 (41.7)	HBL501042W

Note: *All heavy duty industrial cord reels are supplied with wire leads and 3/4" NPT hub feed. Power supply cable not supplied.

Accessories for Heavy Duty Industrial Weatherproof Reels

14" Base	Weight lbs. (kg)	16" Base	Weight lbs. (kg)	Replacement Stop	Weight lbs. (kg)
HBL14PB	5 (2.3)	HBL16PB	13 (5.9)	HBLWPBS	.2 (.09)

Stainless Steel Cord Reels

Description	Cable ft (m)	Cable Type	Amps	Volts AC	Weight lbs. (kg)	Catalog Number
Stainless steel reel without cord ends	45 (13.7)	12/3 SJEO	20	125	30 (14)	HBLSS45123

Note: For indoor non-weathertight applications only.

Commercial Cord Reels

Description	Cable ft (m)	Cable Type	Watts (max)	Amps	Volts AC	Weight lbs. (kg)	Catalog Number
Black Reel with triple tap outlet with wire leads	40 (12.2)	12/3 SJTW	1,875	15	125	9.0 (4.1)	HBLC40123TT HBLC40123
White Reel with triple tap outlet and white cord	30 (9.1)	16/3 SJT	1,250	10	125	8.5 (3.9)	HBLC30163TT
Yellow Reel with Hubbell HBL5969VBLK connector with wire leads	25 (7.6)	16/3 SJT	1,250	10	125	8.5 (3.9)	HBLC25163C HBLC25163

Note: Commercial reels supplied with 2 ft. power supply cord and molded on straight blade 15A plug.

Commercial Lighted Cord Reels

Description	Cable ft (m)	Cable Type	Watts (Max)	Amps	Volts AC	Weight lbs. (kg)	Catalog Number
White Reel with LED hand lamp, with flashlight end	40 (12.2)	18/2 SJTOW	8+1	0.65	125	8.2 (3.7)	HBLC40182LED
White Reel with non-metallic incandescent hand lamp and automatic shut off switch	25 (7.6)	16/3 SJT	75	0.6	125	9.0 (4.1)	HBLC25163AIN*
Yellow Reel with metallic incandescent hand lamp with receptacle	25 (7.6)	14/3 SJT	1,625	13	125	9.5 (4.3)	HBLC25143IN
White Reel with fluorescent hand lamp and automatic shut off switch	40 (12.2)	18/2 SJTOW	13	0.3	120	8.2 (3.7)	HBLC40182AFL*
White Reel with fluorescent hand lamp and inline receptacle	40 (12.2)	16/3 SJT	1,200	10	120	9.0 (4.1)	HBLC40163FL

Note: *Automatic shut off switch allows electrical cord reel installation to conform to Article 511 of the NEC® concerning installation of electrical devices in commercial garages, repair facilities and storage locations by positioning the switch above the defined area where hazardous fumes may collect.

Air/Water Hose Reels

Description	Cable ft (m)	Max Pressure (PSI)	Frame Size	Input Hose Fitting (NPTF)	O.D. inch (mm)	Weight lbs. (kg)	Catalog Number
Low pressure 1/4" ID	35 (10.7)	300	A	1/4	0.51 (13.0)	24 (10.9)	HBLHR2535
	50 (15.2)		B			26 (11.8)	HBLHR2550
Low pressure 3/8" ID	25 (7.6)	300	A	3/8	0.65 (16.5)	23 (10.4)	HBLHR3825
	50 (15.2)		C			36 (16.3)	HBLHR3850
	70 (21.3)		E			50 (22.7)	HBLHR3870
Low pressure 1/2" ID	35 (10.7)	300	C	3/8	0.77 (19.6)	38 (17.2)	HBLHR5035
	50 (15.2)		E			44 (20.0)	HBLHR5050

Yellow Static Discharge Reels with 50' 3/32" Steel Cable

Cable Type	Weight lbs. (kg)	Catalog Number	Cable Type	Weight lbs. (kg)	Catalog Number	Cable Type	Weight lbs. (kg)	Catalog Number
Single	12 (5.4)	HBL50SD	Single Nylon Coated	13 (5.9)	HBL50SDN	Dual (Y)	13 (5.9)	HBL50YSD*

Note: *35 ft. (10.6m) + dual 15 ft. (4.5m) for "Y".



Time and Labor Savings are inREACH™!

The inREACH™ mounting bracket provides a quick and easy 3-step installation on any surface. Details on page 3.



Online Resources

The Hubbell Wiring Device-Kellems website offers fast and convenient information through our online catalog, technical support, videos and more. The website also features a landing page on energy savings. Visit www.hubbell.com/wiringdevice-kellems/en.

Literature Support

Hubbell offers an extensive literature library for product support. Downloadable PDFs are available online.



Hubbell Wiring Device-Kellems
Full Line Catalog



Hose and Cable
Protection Systems



Safety Product Guide

HUBBELL®
Wiring Device-Kellems

www.hubbell.com/wiringdevice-kellems/en

