



Catalog Number	Accommodates			Dimensions			Color Code Die Index
	Copper Conductor Class B,C (mm <sup>2</sup> )	Metric class 2 mm <sup>2</sup>	Navy	Outside Diameter (OD)	Overall Length (L)	Barrel Length (B)	
YS8CL	8 AWG (8.37) 8 AWG Class G,H,I,K,M 6 AWG Str/Sol (13.3)	10	23	.27 [7]	1.00 [25]	.44 [11]	RED 49
YS6CL	6 AWG STR/SOL (13.3)	--	--	.29 [7]	1.75 [44]	.81 [21]	BLUE 374 OR 7 OR 94
YS5CL	5 AWG (18.8)	--	30	.30 [8]	1.90 [48]	.81 [21]	BLUE 7 OR 94
YS4CL	4 AWG (21.2)	--	40	.34 [9]	1.75 [44]	.81 [21]	GRAY 346 OR 8 OR 95
YS3CL	3 AWG (26.7)	25	50	.38 [10]	2.05 [52]	.88 [22]	WHITE 9 OR 96
YS2CL	2 AWG (33.6)	35	60	.42 [11]	2.00 [51]	.88 [22]	BROWN 10 OR 97
YS1CL	1 AWG (42.4)	50	75	.46 [12]	2.06 [52]	.88 [22]	GREEN 375 OR 11 OR 98
YS25L	1/0 AWG (53.5)	--	100	.51 [13]	2.08 [53]	.88 [22]	PINK 348 OR 12 OR 99
YS26L	2/0 AWG (67.2)	70	125	.56 [14]	2.17 [55]	.94 [24]	BLACK 13 OR 100
YS27L	3/0 AWG (85)	--	150	.62 [16]	2.30 [58]	1.00 [25]	ORANGE 14 OR 101
YS28L	4/0 AWG (107)	--	200	.69 [18]	2.32 [59]	1.00 [25]	PURPLE 15
YS29L	250 kcmil (127)	--	250	.75 [19]	2.46 [62]	1.06 [27]	YELLOW 16
YS30L	300 kcmil (152)	150	300	.81 [21]	2.47 [63]	1.06 [27]	WHITE 298 OR 17
YS31L	350 kcmil (177)	185	350	.88 [22]	2.60 [66]	1.12 [28]	RED 324 OR 18
YS32L	400 kcmil (203)	--	400	.95 [24]	2.74 [70]	1.19 [30]	BLUE 470 OR 19

Catalog Number	Accommodates			Dimensions			Color Code Die Index	Wire Strip Length
	Copper Conductor Class B,C (mm <sup>2</sup> )	Metric class 2 mm <sup>2</sup>	Navy	Outside Diameter (OD)	Overall Length (L)	Barrel Length (B)		
YS33L	450 kcmil (228)	--	--	1.01 [26]	2.76 [70]	1.19 [30]	GRAY 326 OR 538	1.25 [32]
YS34L	500 kcmil (253)	240	--	1.06 [27]	3.15 [80]	1.38 [35]	BROWN 299 OR 20	1.44 [37]
YS35L	550 kcmil (278)	--	500	1.12 [28]	3.20 [81]	1.38 [35]	YELLOW 21	1.44 [37]
YS36L	600 kcmil (304)	300	--	1.18 [30]	3.22 [82]	1.38 [35]	GREEN 472 OR 22	1.44 [37]
YS37L	650 kcmil (329)	--	650	1.23 [31]	3.23 [82]	1.38 [35]	ORANGE 23	1.44 [37]
YS38L	700 kcmil (355)	--	--	1.25 [32]	3.22 [82]	1.38 [35]	PINK 400	1.44 [37]
YS39L	750 kcmil (380)	--	--	1.30 [33]	3.72 [94]	1.62 [41]	BLACK 24	1.69 [43]
YS40L	800 kcmil (405)	400	--	1.35 [34]	3.75 [95]	1.62 [41]	ORANGE 25	1.69 [43]
YS41L	850 kcmil (430)	--	800	1.38 [35]	3.76 [96]	1.62 [41]	GOLD 26	1.69 [43]
YS44L	1000 kcmil (507)	500	--	1.49 [38]	4.28 [109]	1.88 [48]	WHITE 27	1.94 [49]
YS45L	1250 kcmil (633)	--	--	1.69 [43]	4.60 [117]	2.00 [51]	YELLOW 29	2.06 [52]
YS453L	1300 kcmil (700)	--	1300	1.74 [44]	4.60 [117]	2.00 [51]	ORANGE 30	2.06 [52]
YS46L	1500 kcmil (760)	--	--	1.84 [47]	4.40 [112]	2.00 [51]	GREEN 31	2.06 [52]
YS47L	1750 kcmil (887)	--	--	1.98 [50]	5.00 [127]	2.19 [56]	GRAY 33	2.25 [57]
YS48L	2000 kcmil (1010)	1013	--	2.12 [54]	5.17 [131]	2.25 [57]	BROWN 34	2.31 [59]
YS486L	2500 kcmil (1215)	--	--	--	--	--	--	--




9




**NOTES:**

- CONNECTOR: TIN PLATED COPPER COMPRESSION SPLICES.
- CONNECTION: COMPRESSION CONNECTIONS MADE ARE IRREVERSIBLE AND MAINTENANCE FREE.
- APPLICABLE STANDARDS: CONNECTORS ARE ONLY UL LISTED AND CSA CERTIFIED WHEN INSTALLED WITH THE BURNDY ENGINEERED SYSTEM AND SELECT OTHER CRIMP TOOL MANUFACTURERS IN ACCORDANCE WITH ONE OR MORE UL CATEGORIES.
  - UL LISTED AND CSA CERTIFIED WIRE CONNECTORS PER UL 486A-486B, CSA 22.2 NO. 65.
- TEMPERATURE AND VOLTAGE RATING: 90°C UP TO 35KV.
- WIRE ACCOMMODATE TYPES (SEE TABLE):
  - COPPER CONDUCTOR: SOLID, CLASS B (CONCENTRIC, COMPRESS, COMPACT) OR CLASS C STRANDING.
- CONNECTOR FINISHES AND SUFFIX: SEE SECTION C OF THE BURNDY MASTER CATALOG FOR PLATING SERVICE TEMPERATURE RATINGS. A. NICKEL PLATED: APPLY SUFFIX "NK" TO A CATALOG NUMBER IN THE TABLE. B. SILVER PLATED: APPLY "SV" TO A CATALOG NUMBER IN THE TABLE. C. TIN ZINC: APPLY "TZ" TO A CATALOG NUMBER IN THE TABLE. D. BARE CONNECTOR: APPLY "BR" TO A CATALOG NUMBER MEANS NO PLATING.
- FEATURES:
  - TYPICAL INK BARREL MARKING COLOR CODE (AS SPACE PERMITS): CRIMP ZONE IS INDICATED BY COLOR BANDS, BURNDY CORPORATE NAME OR LOGO, UL LOGO (IF APPLICABLE), CSA LOGO (IF APPLICABLE), WIRE SIZE, DIE COLOR CODE, DIE INDEX NUMBER.
  - TYPICAL METAL STAMP MARKINGS (AS SPACE PERMITS): CRIMP ZONE IS INDICATED BY METAL KNURL BANDS, BURNDY CORPORATE NAME OR LOGO, UL LOGO (IF APPLICABLE), CSA LOGO (IF APPLICABLE), WIRE SIZE, DIE COLOR CODE, DIE INDEX NUMBER, AND INCLUDES AN INK COLOR CODE DOT MARKING.
  - BARREL DESIGN: BARREL END AT THE WIRE HAS AN INTERNAL CHAMFER, ALLOWING FOR A SMOOTH WIRE INSERTION, AND THE BARREL IS A STANDARD/SHORT LENGTH WHICH IS RECOMMENDED FOR INSTALLATIONS WITH LIMITED SPACE REQUIREMENTS.
  - BARREL IS DESIGNED WITH INDENT CABLE STOPS IN THE CENTER OF THE BARREL.
- INSTALLATION TOOLING AND DIES ARE CONSTANTLY BEING UPDATED. PLEASE SEE BURNDY MASTER CATALOG FOR THIS PRODUCT FAMILY, WHICH CAN BE FOUND ON THE BURNDY WEBSITE.
  - YS486L IS NOT UL LISTED OR CSA CERTIFIED

TO ORDER BURNDY® PRODUCTS CALL		STANDARD BARREL CODE SPLICES	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE CAT. NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		DRAWN BY: M.P. 08/24/1993 CHECKER: R.ROBICHEAU 07/01/1993 DSN APRVL: C.PALAGI 07/06/1993 MFG APRVL: -- QA APRVL: -- MKT APRVL: --	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>			
PROD FAM: C&I COMPRESSION		DRAWING NO	
PROJECT #: --		SIZE	
DOCUMENT TYPE: SALES		SD..022390-01	
REL LEVEL: Released		C	
		SHEET 1 OF 5	
		REV M	

CATALOG NUMBER DESIGNATION	WIRE SIZE ACCOMMODATES		Hydraulic Tools - Dies Required (# Crimps)					Hydraulic Tools - Dieless		Wire Strip Length
	Class B, C Conductor (CU Only)	Color Code and Die Index Number	MD6, 600, 500 Series	750, 35 Series	45 Series Use PT6515 with U Dies	46 Series Use PUADP1 with U Dies	60 Series	81K 4PC Series	644 444 Series	
YS8CL	8 AWG 6 AWG Sol.	RED 49	X8CRT (1) W8CRT (1) W8CVT (1)	U8CRT (1)	U8CRT (1)	U8CRT (1)	--	1 CRIMP	--	.50 [13]
YS6CL	6 AWG Str Sol	BLUE 7	X5CRT (1) W5CRT (1) W5CVT (1)	U5CRT (1)	U5CRT (1)	U5CRT (1)	--	1 CRIMP	--	.88 [22]
YS5CL	5 AWG	BLUE 7	X5CRT (1) W5CRT (1) W5CVT (1)	U5CRT (1)	U5CRT (1)	U5CRT (1)	--	1 CRIMP	--	.88 [22]
YS4CL	4 AWG	GRAY 8	X4CRT (1) W4CRT (1) W4CVT (1)	U4CRT (1)	U4CRT (1)	U4CRT (1)	--	1 CRIMP	1 CRIMP	.88 [22]
YS3CL	3 Str 2 Sol	WHITE 9	W3CRT (1)	U3CRT (1)	U3CRT (1)	U3CRT (1)	--	1 CRIMP	1 CRIMP	.94 [24]
YS2CL	2 AWG	BROWN 10	X2CRT (1) W2CRT (1) W2CVT (1)	U2CRT (1)	U2CRT (1)	U2CRT (1)	--	1 CRIMP	1 CRIMP	.94 [24]
YS1CL	1 AWG	GREEN 11	X1CRT1 (1) W1CRT1 (1) W1CVT (1)	U1CRT1 (1)	U1CRT1 (1)	U1CRT1 (1)	--	1 CRIMP	1 CRIMP	.94 [24]
YS25L	1/0 AWG	PINK 12	X25RT (2) W25RT (2) W25VT (2)	U25RT (1)	U25RT (1)	U25RT (1)	--	1 CRIMP	1 CRIMP	.94 [24]
YS26L	2/0 AWG	BLACK 13	X26RT (2) W26RT (2) W26VT (2)	U26RT (1)	U26RT (1)	U26RT (1)	--	1 CRIMP	1 CRIMP	1.00 [25]
YS27L	3/0 AWG	ORANGE 14	X27RT (3) W27RT (2) W27VT (2)	U27RT (1)	U27RT (1)	U27RT (1)	--	2 OVERLAPPING CRIMPS	1 CRIMP	1.06 [27]
YS28L	4/0 AWG	PURPLE 15	X28RT (3) W28RT (2) W28VT (2)	U28RT (1)	U28RT (1)	U28RT (1)	L28RT (1)	2 OVERLAPPING CRIMPS	1 CRIMP	1.06 [27]
YS29L	250 kcmil	YELLOW 16	X29RT (4) W29RT (2) W29VT (2)	U29RT (1)	U29RT (1)	U29RT (1)	L29RT (1)	2 OVERLAPPING CRIMPS	1 CRIMP	1.12 [28]
YS30L	300 kcmil	WHITE 17	W30RT (2) W30VT (2)	U30RT (2)	U30RT (2)	U30RT (2)	L30RT (1)	2 OVERLAPPING CRIMPS	1 CRIMP	1.12 [28]
YS31L	350 kcmil	RED 18	W31RT (2) W31VT (2)	U31RT (2)	U31RT (2)	U31RT (2)	L31RT (1)	2 OVERLAPPING CRIMPS	1 CRIMP	1.18 [30]
YS32L	400 kcmil	BLUE 19	W32RT (2) W32VT (2)	U32RT (2)	U32RT (2)	U32RT (2)	L32RT (1)	2 OVERLAPPING CRIMPS	1 CRIMP	1.25 [32]

TO ORDER BURNDY® PRODUCTS CALL		STANDARD BARREL CODE SPLICES	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: M.P. 08/24/1993	
	CHECKER: R.ROBICHEAU 07/01/1993	DSN APRVL: C.PALAGI 07/06/1993	
	MFG APRVL: --	QA APRVL: --	
	MKT APRVL: --	PROD FAM: C&I COMPRESSION	
		PROJECT #: --	
		DOCUMENT TYPE: SALES	DRAWING NO: SD..022390-01
		REL LEVEL: Released	SIZE: C
			REV: M
			SHEET 2 OF 5

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
M	04/10/2021	NEW DRAWING CREATION	211007013128	YR	WP


CATALOG NUMBER DESIGNATION	WIRE SIZE ACCOMMODATES	Color Code and Die Index Number	Hydraulic Tools - Dies Required (# Crimps)					Hydraulic Tools - Dieless		Wire Strip Length
	Class B, C Conductor (CU Only)		MD6, 600, 500 Series	750, 35 Series	45 Series Use PT6515 with U Dies	46 Series Use PUADP1 with U Dies	60 Series	81K 4PC Series	644 444 Series	
YS33L	450 kcmil	GRAY 326	W33RT (2) W33VT (2)	U33RT (2)	U33RT (2)	U33RT (2)	L33RT (1)	2 OVERLAPPING CRIMPS	1 CRIMP	1.25 [32]
YS34L	500 kcmil	BROWN 20	W34RT (2) W34VT (2)	U34RT (2)	U34RT (2)	U34RT (2)	L34RT (1)	2 OVERLAPPING CRIMPS	1 CRIMP	1.44 [37]
YS35L	550 kcmil	YELLOW 21	--	U35RT (2)	U35RT (2)	U35RT (2)	L35RT (1)	2 OVERLAPPING CRIMPS	1 CRIMP	1.44 [37]
YS36L	600 kcmil	GREEN 22	--	U36RT (2)	U36RT (2)	U36RT (2)	L36RT (1)	2 OVERLAPPING CRIMPS	1 CRIMP	1.44 [37]
YS37L	650 kcmil	ORANGE 23	--	U37RT (2)	U37RT (2)	U37RT (2)	L37RT (1)	3 OVERLAPPING CRIMPS	1 CRIMP	1.44 [37]
YS38L	700 kcmil	PINK 400	--	U38RT (2)	U38RT (2)	U38RT (2)	L38RT (1)	3 OVERLAPPING CRIMPS	1 CRIMP	1.44 [37]
YS39L	750 kcmil	BLACK 24	--	U39RT (2)	U39RT (2)	U39RT (2) P39RT (2)	L39RT (1)	3 OVERLAPPING CRIMPS	1 CRIMP	1.69 [43]
YS40L	800 kcmil	ORANGE 25	--	--	S40RT (3)	P40RT (3)	L40RT (1)	3 OVERLAPPING CRIMPS	1 CRIMP	1.69 [43]
YS41L	850 kcmil	GOLD 26	--	--	--	P41D with P44PR (1)	--	3 OVERLAPPING CRIMPS	1 CRIMP	1.69 [43]
YS44L	1000 kcmil	WHITE 27	--	--	S44RT (3)	P44RT (3)	L44RT (2)	3 OVERLAPPING CRIMPS	1 CRIMP	1.94 [49]
YS45L	1250 kcmil	YELLOW 29	--	--	S45RT (3)	P45RT (3)	L45RT (2)	--	--	2.06 [52]
YS453L	1300 kcmil	ORANGE 30	--	--	--	--	--	--	--	2.06 [52]
YS46L	1500 kcmil	GREEN 31	--	--	S46RT (3)	P46RT (3)	L46RT (2)	--	--	2.06 [52]
YS47L	1750 kcmil	GRAY 33	--	--	--	--	L47RT (2)	--	--	2.25 [57]
YS48L	2000 kcmil	BROWN 34	--	--	--	--	L48RT (2)	--	--	2.31 [59]
YS486L	--	--	--	--	--	--	--	--	--	--

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
M	04/10/2021	NEW DRAWING CREATION	211007013128	YR	WP

TO ORDER BURNDY® PRODUCTS CALL		STANDARD BARREL CODE SPLICES	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: M.P. 08/24/1993	
	CHECKER: R.ROBICHEAU 07/01/1993	DSN APRVL: C.PALAGI 07/06/1993	
	MFG APRVL: --	QA APRVL: --	
	MKT APRVL: --		
PROD FAM: C&I COMPRESSION	DRAWING NO	REV	
PROJECT #: --	SIZE	SD..022390-01	M
DOCUMENT TYPE: SALES	C	SHEET 3 OF 5	
REL LEVEL: Released			

CATALOG NUMBER DESIGNATION	WIRE SIZE ACCOMMODATES	Color Code and Die Index Number	Mechanical & Ratchet Dies Required (# Crimps)		Mechanical & Ratchet Dedicated Die Tools # Crimps				Wire Strip Length
	Class B, C Conductor (CU Only)		MD6 and MD7 Series <small>*Due to handle force not recommended</small>	OUR840 <small>*Due to handle force not recommended</small>	MY293 MY2911	MRC840	Y122CMR	Y1MRTC	
			X8CRT (1) W8CRT (1) W8CVT (1)	X8CRT (1) W8CRT (1) W8CVT (1)	1 CRIMP	1 CRIMP	1 CRIMP	1 CRIMP	
YS8CL	#8 AWG	RED 49	X8CRT (1) W8CRT (1) W8CVT (1)	X8CRT (1) W8CRT (1) W8CVT (1)	1 CRIMP	1 CRIMP	1 CRIMP	1 CRIMP	.50 [13]
YS6CL	#6 AWG Str Sol	BLUE 7	X5CRT (1) W5CRT (1) W5CVT (1)	X5CRT (1) W5CRT (1) W5CVT (1)	1 CRIMP	1 CRIMP	1 CRIMP	1 CRIMP	.88 [22]
YS5CL	#5 AWG	BLUE 7	X5CRT (1) W5CRT (1) W5CVT (1)	X5CRT (1) W5CRT (1) W5CVT (1)	1 CRIMP	1 CRIMP	1 CRIMP	1 CRIMP	.88 [22]
YS4CL	#4 AWG	GRAY 8	X4CRT (1) W4CRT (1) W4CVT (1)	X4CRT (1) W4CRT (1) W4CVT (1)	1 CRIMP	1 CRIMP	2 CRIMPS	2 CRIMPS	.88 [22]
YS3CL	#3 Str #2 Sol	WHITE 9	W3CRT (1)	W3CRT (1)	1 CRIMP	1 CRIMP	2 CRIMPS	2 CRIMPS	.94 [24]
YS2CL	#2 AWG	BROWN 10	X2CRT (1) W2CRT (1) W2CVT (1)	X2CRT (1) W2CRT (1) W2CVT (1)	1 CRIMP	1 CRIMP	2 CRIMPS	2 CRIMPS	.94 [24]
YS1CL	#1 AWG	GREEN 11	X1CRT1 (1) W1CRT1 (1) W1CVT (1)	X1CRT1 (1) W1CRT1 (1) W1CVT (1)	1 CRIMP	1 CRIMP	--	2 CRIMPS	.94 [24]
YS25L	1/0 AWG	PINK 12	X25RT (2) W25RT (2) W25VT (2)	X25RT (2) W25RT (2)* W25VT (2)*	1 CRIMP	2 CRIMPS	--	--	.94 [24]
YS26L	2/0 AWG	BLACK 13	X26RT (2) W26RT (2) W26VT (2)	X26RT (2) W26RT (2)* W26VT (2)*	1 CRIMP	2 CRIMPS	--	--	1.00 [25]
YS27L	3/0 AWG	ORANGE 14	X27RT (3) W27RT (2) W27VT (2)	X27RT (3) W27RT (2)* W27VT (2)*	1 CRIMP	2 CRIMPS	--	--	1.06 [27]
YS28L	4/0 AWG	PURPLE 15	X28RT (3) W28RT (2) W28VT (2)	X28RT (3) W28RT (2)* W28VT (2)*	1 CRIMP	2 CRIMPS	--	--	1.06 [27]
YS29L	250 kcmil	YELLOW 16	X29RT (4) W29RT (2) W29VT (2)	X29RT (4) W29RT (2)* W29VT (2)*	1 CRIMP	--	--	--	1.12 [28]
YS30L	300 kcmil	WHITE 17	W30RT (2)* W30VT (2)	--	--	--	--	--	1.12 [28]
YS31L	350 kcmil	RED 18	W31RT (2)* W31VT (2)	--	--	--	--	--	1.18 [30]
YS32L	400 kcmil	BLUE 19	W32RT (2)* W32VT (2)	--	--	--	--	--	1.25 [32]
YS33L	450 kcmil	GRAY 326	W33RT (2)* W33VT (2)	--	--	--	--	--	1.25 [32]
YS34L	500 kcmil	BROWN 20	W34RT (2)* W34VT (2)	--	--	--	--	--	1.44 [37]

REV	DATE	DESCRIPTION	ECO	BY	CHK.
M	04/10/2021	NEW DRAWING CREATION	211007013128	YR	WP

TO ORDER BURNDY® PRODUCTS CALL		STANDARD BARREL CODE SPLICES	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: M.P. 08/24/1993	
	CHECKER: R.ROBICHEAU 07/01/1993	DSN APRVL: C.PALAGI 07/06/1993	
	MFG APRVL: --	QA APRVL: --	
	MKT APRVL: --	PROD FAM: C&I COMPRESSION	
		DRAWING NO	
		PROJECT #: --	REV
		DOCUMENT TYPE: SALES	SD..022390-01
		REL LEVEL: Released	M
		SIZE	SHEET 4 OF 5
		C	

## Installation Instructions

1. Select the appropriate connector based on:  
Wire Material, Wire Construction, Wire Size
2. Strip the insulation to the appropriate wire strip length, based on the table's Wire Strip Length recommendation for the selected connector.
3. As a best practice, wire brush the bare conductor to remove any oxides.  
DO NOT wire brush tin-plated connectors.
4. Insert the conductor into the barrel for the full length. If the connector has an inspection window, the conductor end can easily be seen to verify full wire insertion.
5. Apply the proper number of crimps specified by the appropriate illustration.
6. \*Some catalog numbers require overlapping crimps when using the 81K or 4PC Series of installation tools. Please refer to the overlapping crimp image that is applicable based on the number of crimps required. Overlap each consecutive crimp so that the completed installation of all overlapping crimps covers the entire crimp zone.
7. Once all crimps have been completed, the connection can be easily inspected for proper installation.

### NOTES:

- Ink Marked Barrels: Illustrations show black solid bands however this is just a representation of the crimp zones. See individual connector for actual crimp band color code. Example:




### NOTES:


- Metal Stamped Marked Barrels: Illustrations show hatch knurl bands and a black solid color code dot. See individual connector for actual color dot color code.



CATALOG NUMBER DESIGNATION				
YS6CL-	YS4CL-	YS3CL-	YS2CL-	YS1CL-
YS25L-	YS26L-	YS27L-	YS28L-	YS29L-



CATALOG NUMBER DESIGNATION						
YS30L-	YS31L-	YS32L-	YS34L-	YS36L-	YS39L-	YS44L-



2 OVERLAPPING

3 OVERLAPPING

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES  
1-800-346-4175 (LONDONDERRY, NH)

CANADA:  
1-800-361-6975 (QUEBEC)  
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

STANDARD BARREL CODE SPLICES

ITEM NO: SEE TABLE	
CAT. NO: SEE TABLE	
DRAWN BY: M.P. 08/24/1993	
CHECKER: R.ROBICHEAU 07/01/1993	
DSN APRVL: C.PALAGI 07/06/1993	
MFG APRVL: --	
QA APRVL: --	
MKT APRVL: --	
PROD FAM: C&I COMPRESSION	DRAWING NO
PROJECT #: --	SIZE
DOCUMENT TYPE: SALES	SD..022390-01
REL LEVEL: Released	SHEET 5 OF 5



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
M	04/10/2021	NEW DRAWING CREATION	211007013128	YR	WP

REV  
M