
Hose and Cable Protection Systems



Hubbell Safety Solutions



Hose and Cable Protection Systems











Hubbell TrukTrak® non-metallic cable protectors are designed to safeguard electrical cables and cords from vehicle and pedestrian traffic. The TrukTrak interlocking system comes in two, three and five channel sizes and will protect cables up to 3.25 inches (82.6mm) in diameter. It is ideal for the industrial environment where it is necessary to support heavy trucks and fork lifts.

TredTrak® non-metallic cable protectors can also be interlocked to protect cables and cords of any length. The TredTrak system is a five channel modular cable protection system that will protect cable diameters up to 1.28 inches (32.5mm). It is designed to support pedestrian and light vehicle traffic in public, institutional and commercial applications. The Hubbell modular cable protection line also permits compliance with NEC® requirements (Article 525) for insulating electrical cables and cord at carnivals, amusement parks, convention centers and similar public areas.

The AccessTrak® ramping system is a modular cable protection product that enables users to be ADAAG (American Disabilities Act Accessibility Guidelines) compliant and limits the exposure of cables and hoses to people and light vehicles passing over those cables and hoses. AccessTrak is an expandable five channel system that will protect cable and hose diameters up to 1.31 inches (33.0mm). For applications requiring more than five channels, AccessTrak can be expanded by width. In addition, AccessTrak is interlocking and expandable by length to protect cables and hoses of any length. The AccessTrak ramping system provides a safe, flexible means of protecting cables and hoses in areas requiring ADA compliance.


ProTrak[™] non-metallic single channel cable protectors are suitable for lightweight vehicle and pedestrian traffic. Available in both black and yellow. The drop over PROTRK115 series can accommodate up to 0.75 inches (19.0mm), while the PROTRK140 can handle up to 1.50 inches (38.1mm). The hinged covered PROTRK1225 series can accommodate up to 0.75 inches (19.0mm). A unique tread surface provides maximum traction. ProTrak[™] cable protectors can be interlocked as a single color run or as a yellow and black run.

FloorTrak® is a flexible, non-metallic cover for cables that run over the floor when portable cords and cables cannot be concealed or routed away from traffic patterns. FloorTrak protects, organizes and reduces trip hazards. Four different sizes mean it will handle cables of up to 1.25 inches (31.8mm) in diameter. FT2, FT3 and FT4 are available in five PVC colors to blend with the various decors. FT10 is available in black and yellow colors only. The F10 Heavy Duty FloorTrak is ideal for applications such as industrial work areas, food processing plants and abusive areas where cable management is necessary.

TrukTrak® Systems


Ideal for Heavy Vehicle Traffic in Industrial, Commercial or Public Applications


- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- Safety surface pattern reduces slipping and skidding
- High visibility safety blue and yellow colors







TrukTrak® Systems	Α	В	С	D	E		
		Trak			Channel		_
Description	Length Inches (mm)	Width Inches (mm)	Height Inches (mm)	Width Inches (mm)	Height Inches (mm)	Weight lbs. (kg)	Catalog Number
5 Channel TrukTrak®, blue and yellow.	36.0" (914)	20" (508)	2.31" (58.7)	1.25" (31.8)	1.25" (31.8)	30.60 (13.9)	HBLTT5B
5 Channel TrukTrak® end caps (pair only), yellow.	7.50" (190) 5.25" (133)	20" (508) 20" (508)	2.31" (58.7) 2.31" (58.7)	1.25" (31.8) 1.25" (31.8)	1.25" (31.8) 1.25" (31.8)	8.55 (3.9) 8.55 (3.9)	HBLTT5ECB (Female end) (Male end)
5 Channel 45° right turn TrukTrak®, blue and yellow.	25.0" (635)	20" (508)	2.31" (58.7)	1.25" (31.8)	1.25" (31.8)	15.35 (7.0)	HBLTT545RB
5 Channel 45° left turn TrukTrak®, blue and yellow.	25.0" (635)	20" (508)	2.31" (58.7)	1.25" (31.8)	1.25" (31.8)	14.45 (6.6)	HBLTT545LB
3 Channel TrukTrak®, blue and yellow.	36.0" (914)	20" (508)	3.05" (77.5)	2.25" (57.2)	2.25" (57.2)	30.85 (14.0)	HBLTT3B
3 Channel TrukTrak® end caps (pair only), yellow.	8.25" (209) 6.38" (162)	20" (508) 20" (508)	3.05" (77.5) 3.05" (77.5)	2.25" (57.2) 2.25" (57.2)	2.25" (57.2) 2.25" (57.2)	10.25 (4.6) 10.25 (4.6)	HBLTT3ECB (Female end) (Male end)
2 Channel TrukTrak®, blue and yellow.	36.0" (914)	22" (559)	4.13" (104.9)	3.25" (82.6)	3.25" (82.6)	41.00 (18.6)	HBLTT2B









Load Capacity

No. of	Test Fixture Footprint	Measured Loa	d lbs. (N) +/- 20%
Channels	Inches (mm)	70°F (21°C)	120°F (49°C)
5	6.9" x 17.3" (175 X 439)	20,150 (89,627)	9,200 (40,921)
3	6.9" x 17.3" (175 X 439)	14,210 (63,206)	4,653 (20,696)
2	6.9" x 17.3" (175 X 439)	10,880 (48,394)	2,095 (9,318)


Note: Tire load rating shown. Double for axle rating.




TredTrak® Systems Improves Pedestrian Safety by Decreasing Risk of Tripping



- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- Safety surface pattern reduces slipping and skidding
- High visibility safety yellow and blue colors



TredTrak [®] Systems	A	В	С	D	E		
		Trak			Channel		
Description	Length Inches (mm)	Width Inches (mm)	Height Inches (mm)	Width Inches (mm)	Height Inches (mm)	Weight lbs. (kg)	Catalog Number
5 Channel TredTrak®, blue and yellow.	36.0" (914)	17.5" (445)	1.95" (50)	1.30" (33)	1.30" (33)	21.15 (9.6)	HBLTRED5B
5 Channel TredTrak® end caps							HBLTRED5ECB
(pair only), yellow.	5.75" (146)	17.5" (445)	1.95" (50)	1.30" (33)	1.30" (33)	6.40 (2.9)	(Female end)
	5.75" (146)	17.5" (445)	1.95" (50)	1.30" (33)	1.30" (33)	6.40 (2.9)	(Male end)
5 Channel TredTrak® female end caps (2 females), yellow.	5.75" (146)	17.5" (445)	1.95" (50)	1.30" (33)	1.30" (33)	6.40 (2.9)	HBLTRED5ECFB
5 Channel "X" fitting, blue and yellow.	17.5" (445)	17.5" (445)	1.95" (50)	1.30" (33)	1.30" (33)	14.25 (6.5)	HBLTRED5XB
5 Channel "Y" fitting, blue and yellow.	17.5" (445)	17.5" (445)	1.95" (50)	1.30" (33)	1.30" (33)	13.95 (6.3)	HBLTRED5YB



Load Capacity

	Test Fixture Footprint	Measured Load lbs. (N) +/- 20%			
Product	Inches (mm)	70°F (21°C)	120°F (49°C)		
TredTrak	6.9" x 17.3" (175 X 439)	10,500 (46,700)	6,500 (28,900)		
"X" Fitting	6.9" x 17.3" (175 X 439)	2,900 (12,900)	2,300 (10,230)		
"Y" Fitting	6.9" x 17.3" (175 X 439)	2,900 (12,900)	2,300 (10,230)		

Note: Tire load rating shown. Double for axle rating.

AccessTrak® Systems

ADA Compliant Limits Exposure of Cables and Hoses to Pedestrians

- This interlocking system provides a safe, flexible means of protecting cables and hoses in areas requiring ADA compliance
- High density polyurethane construction
- AccessTrak is an expandable five channel system that expands by length or width
- High visibility safety symbols on blue and gray colors







AccessTrak Expanded by Length

AccessTrak Expanded by Width

AccessTrak® Systems	Α	В	С	D	E		
		Trak			Channel		
Description	Length Inches (mm)	Width Inches (mm)	Height Inches (mm)	Width Inches (mm)	Height Inches (mm)	Weight lbs. (kg)	Catalog Number
5 Channel AccessTrak® kit*, blue and gray.	41.06" (1043.0)	42.90" (1090.0)	4.00" (102.0)	1.34" (34.0)	1.31" (33.0)	73.65 (33.41)	HBLAT5KITA
5 Channel AccessTrak® trough, blue and gray.	36.00" (914.0)	13.34" (339.0)	1.94" (49.0)	1.34" (34.0)	1.31" (33.0)	22.35 (10.14)	HBLAT5A
AccessTrak® trough end rails (set), gray.	2.50" (63.0)	13.28" (337.0)	4.00" (102.0)	_	_	6.95 (3.15)	HBLAT5ERA
AccessTrak® ramps (set), blue.	36.00" (914.0)	14.50" (368.0)	1.94" (49.0)	_	_	29.90 (13.56)	HBLAT5RAMPA
AccessTrak® ramp end rails (set), gray.	2.50" (63.5)	14.75" (375.0)	4.00" (102.0)	_	_	8.05 (3.65)	HBLAT5RAMPERA

Note: *Consists of (1) HBLAT5A; (1 set) HBLAT5ERA; (1 set) HBLAT5RAMPA; (2 sets) HBLAT5RAMPERA.


Measured Load lbs. (N) +/- 20%

120°F (49°C)

8,000 (35,584)

70°F (21°C)


10,000 (44,480)




Assembled Kit

Test Fixture Footprint Inches (mm)

7" x 7" (178 x 178)





Trough (side view)

Trough End Rails (side view) Color Light Gray

Ramp End Rails (top view)




ProTrak™ Systems For Pedestrian and Light Vehicle Traffic



- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- · Safety surface pattern reduces slipping and skidding
- High visibility safety yellow and black
- Anti-slip pad kits available



ProTrak™ Systems	Α	В	С	D	E		
		Trak			Channel		
	Length	Width	Height	Width	Height	Weight	
Description	Inches (mm)	Inches (mm)	Inches (mm)	Inches (mm)	Inches (mm)	lbs. (kg)	Catalog Number
1 Channel, drop over, yellow	36.0" (914)	5.25" (133)	.75" (19.0)	1.50" (38.1)	.50" (12.7)	3.00 (1.40)	PROTRK115Y
1 Channel, drop over, black	36.0" (914)	5.25" (133)	.75" (19.0)	1.50" (38.1)	.50" (12.7)	3.00 (1.40)	PROTRK115BK
1 Channel, drop over, yellow	36.0" (914)	10.75" (273)	1.50" (38.1)	4.00" (101.6)	1.00" (25.4)	8.00 (3.60)	PROTRK140Y
1 Channel, drop over, black	36.0" (914)	10.75" (273)	1.50" (38.1)	4.00" (101.6)	1.00" (25.4)	8.00 (3.60)	PROTRK140BK
1 Channel, hinged cover, yellow	36.0" (914)	10.81" (274)	1.25" (31.8)	2.25" (57.2)	.75" (19.0)	7.80 (3.54)	PROTRK1225Y
1 Channel, hinged cover, black	36.0" (914)	10.81" (274)	1.25" (31.8)	2.25" (57.2)	.75" (19.0)	7.80 (3.54)	PROTRK1225BK





Load Capacity


	Test Fixture Footprint	Measured Load lbs. (N) +/- 20%		
Product	Inches (mm)	70°F (21°C)		
PROTRK115	6.9" x 17.3" (175 X 439)	10,500 (46,700)		
PROTRK140	6.9" x 17.3" (175 X 439)	10,500 (46,700)		
PROTRK1225	6.9" x 17.3" (175 X 439)	13,000 (5,896)		

Note: Tire load rating shown. Double for axle rating.

Accessories

ProTrak Series	Anti-Slip Pad Kits*
PROTRK115	PROTRK1ASPK
PROTRK140	PROTRK2ASPK
PROTRK1225	PROTRK3ASPK

*One kit per section



(Side view)

FloorTrak® Floor Cable Cover For Pedestrian Traffic in Office and Public Areas

- Flexible and rigid PVC material
- Protects and reduces trip hazards

• Available in four different sizes and five PVC colors to blend with the various decors

• Withstands temperatures of 0°F to +120°F (-18°C to +49°C)



FT3BK5

FT10BK5

FT4BK5



FloorTrak® 2*

	Le	ngth	Catalog
Color	Feet	(meters)	Number
Black	10.0'	(3.05)	FT2BK10
Brown	10.0'	(3.05)	FT2BR10
Beige	10.0'	(3.05)	FT2BG10
Gray	10.0'	(3.05)	FT2GY10
Yellow	10.0'	(3.05)	FT2Y10



FloorTrak® 4

0.1	Length	Catalog
Color	Feet (meters)	Number
Black	5.0' (1.52)	FT4BK5
Black	25.0' (7.62)	FT4BK25
Gray	25.0' (7.62)	FT4GY25
Yellow	5.0' (1.52)	FT4Y5
Yellow	25.0' (7.62)	FT4Y25



FloorTrak® 3*

Color	Length Feet (meters)	Catalog Number
Black	5.0' (1.52)	FT3BK5
Black	25.0' (7.62)	FT3BK25
Brown	5.0' (1.52)	FT3BR5
Brown	25.0' (7.62)	FT3BR25
Beige	5.0' (1.52)	FT3BG5
Beige	25.0' (7.62)	FT3BG25
Gray	5.0' (1.52)	FT3GY5
Gray	25.0' (7.62)	FT3GY25
Yellow	5.0' (1.52)	FT3Y5
Yellow	25.0' (7.62)	FT3Y25




FloorTrak® 10 (Heavy Duty)

Color	Length Feet (meters)	Catalog Number
00101	T CCT (TTCTCTS)	Number
Black	3.0' (.914)	FT10BK3
Black	5.0' (1.52)	FT10BK5
Yellow	3.0' (.914)	FT10Y3
Yellow	5.0' (1.52)	FT10Y5




Dimensions

FloorTrak®	FT2	FT3	FT4	FT10 (Heavy Duty)
	in. (mm)	in. (mm)	in. (mm)	in. (mm)
Width (A)	2.75" (69.9)	3.00" (76.2)	3.25" (82.6)	5.6" (142.24)
Height (B)	.53" (13.5)	.75" (19.1)	1.10" (27.9)	1.7" (43.18)
Center Hole (CxD)	.60" x .31"	.75" x .50"	1.21" x .75"	1.81" x 1.25"
	(15.2) x (7.9)	(19.1) x (12.7)	(30.7) x (19.1)	(45.98 x 31.75)



Accessories

Description	Catalog Number
1" Wide, 75' Roll Double-Sided Adhesive Tape.	FTT1
2" Wide, 75' Roll Double-Sided Adhesive Tape.	FTT2





^{*}ADA Compliant Section 4.5.2

HUBBELL® Online Tools

Safety eTour



This interactive, virtual tour of a plant takes allows visitors to explore this virtual industrial facility and see the many Hubbell safety solutions that are employed in areas like shipping, plating, molding, automated assembly, manual assembly and maintenance.



Area



Product Page

Selector Apps

Use the New Hubbell Twist-Lock® and Kellems® Apps



Download them today!





Literature Support

Hubbell offers an extensive literature library for product support. Downloadable PDFs are available online at www.hubbell-wiring.com



Insulgrip® Wiring Devices




Hubbell Watertight Wiring Devices



Hubbell Safety Guide



GFCI Receptacles



Temporary Lighting



www.hubbell-wiring.com

