

# INSTALLATION TOOLING FOR COPPER CONNECTORS

## TYPE CHL, CSL AND CSS

### Copper Connectors

Copper Only		Blackburn		Burndy			T & B		Sq. D
Cable Size	Die Color Code	NRG2508 Hand Indent	JB12A Hand Indent	MY29-3 HABD Hydr.	Y35-39 HABD Hydr.	Die Index	TBN12-m Hand Hydr.	TBM15M Elect. Hydr.	VC-y Hand Hydr.
8AWG	RED	X(1)	B71CH	X(1)			21 (1)	21 (1)	X(1)
6AWG	BLUE	X(1)	B73CH	X(1)	U8CART (2)	374	24 (2)	24 (2)	X(1)
4AWG	GREY	X(1)	B74CH	X(1)	U6CART (2)	346	29 (2)	29 (2)	X(1)
3AWG	GREY	X(1)	B74CH	X(1)	U6CART (2)	346	29 (2)	29 (2)	X(1)
2AWG	BROWN	X(1)	B75CH	X(1)	U2CRT (2)	10	33 (2)	33 (2)	X(1)
1/0AWG	GREEN	X(1)	B05CH	X(1)	U4CART (2)	375	37 (2)	37 (2)	X(1)
2/0AWG	PINK	X(1)	B06CI	X(1)	U2CART (1)	348	42H (2)	42H (2)	X(2)
3/0AWG	BLACK	X(1)	B72CH	X(1)	U26RT (1)	13	45 (2)	45 (2)	X(2)
4/0AWG	ORANGE	X(1)	B08CH	X(1)	U27RT (1)	14	50 (2)	50 (2)	X(2)
250MCM	PURPLE	X(1)	B09CH	X(1)	U28RT (1)	15	54H (2)	54H (2)	X(2)
300MCM	YELLOW	X(1)	B26CH	X(1)	U29RT (2)	16	62 (2)	62 (2)	X(2)
350MCM	WHITE		B10CH		U28ART (2)	298	66 (2)	66 (2)	X(2)
250MCM	RED		B10CHI		U29ART (2)	324	71H (2)	71H (2)	X(2)
400MCM	BLUE		B11CH		U30ART (2)	470	76 (2)	76 (2)	X(2)
500MCM	BROWN		B12CH		U31ART (2)	299	87H (2)	87H (2)	X(3)
600MCM	GREEN		B36CH		U32ART (2)	472	94 (3)	94 (3)	
750MCM	BLACK		B39CH		U34ART (2)	300	106H (3)	106H (3)	
1000MCM	WHITE		6044RT		U36ART (2)	473	125H (3)	125H (3)	

*Note: Also can be crimped using the CMCT-12 tool with either Burndy or T & B dies.  
X denotes adjustable tool with non-removable dies.  
(#) figures indicate number of crimps.*