

# Natural Gas Stop Valves

## Lockwing, Brass Valve Core, Tamper-Resistant, 175 PSIG




Hubbell Gas Utility Solutions (HGUS) produces natural gas stop valves for multiple natural gas and liquid propane applications as used by virtually all the gas distribution companies in the U.S. and beyond. Precision machined with the latest technology, the HGUS natural gas stop valve meets or exceeds all gas utility requirements. Each valve is designed for natural gas piping systems up to 175 PSIG and tested to the ASME B16.33 standard prior to shipment.



## + Features & Benefits

- Designed and tested to ASME B16.33 American National Standard for "Manually Operated Metallic Gas Valves for Use in Gas Piping Systems up to 175 psi"
- Pressure ratings: 175 PSIG
- Bubble-tight seal throughout entire pressure and temperature range
- One piece body
- Lockwing
- Shut-off is accomplished with a 90° turn of valve. Full 360° rotation of valve possible
- Tamper-resistant
- Pressure may be applied in either direction as Hubbell's Natural Gas Stop Valve is a nondirectional valve
- Valves are factory lubricated and suitable for use with natural, manufactured and LP gases
- May be re-lubricated while valve is under pressure
- Valve plugs are equipped with top and bottom o-rings for added security against external leakage
- Operating temperature range of -20°F to 150°F
- Port openings sized to accommodate the best-known stop changers
- NPT Threads meet ASME B1.20.1
- Available in Bare Steel and with Zinc Plating

# Natural Gas Stop Valves



## DIMENSIONS

SIZE	A	B	C	D	E
3/4"	3.14"	3.35"	1.61"	3/4" NPT	3/4" NPT
1"	3.36"	3.68"	1.93"	1" NPT	1" NPT
1-1/4"	3.90"	4.65"	2.28"	1-1/4" NPT	1-1/4" NPT
1-1/2"	4.65"	5.35"	2.60"	1-1/2" NPT	1-1/2" NPT
2"	5.59"	5.79"	2.99"	2" NPT	2" NPT



A proud member of the Hubbell family.