

### INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification Scheme for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Certificate No.:

IECEx MSC 14.0010X

Issue No: 1

Certificate history:

Status:

Current

Issue No. 1 (2017-12-05) Issue No. 0 (2014-06-11)

Date of Issue:

2017-12-05

Page 1 of 6

Applicant:

Austdac Pty Ltd

Unit 1/42 Carrington Road, Castle Hill NSW 2154

Australia

Equipment:

Memory Backup Battery Types 3/Li-C/125 and 3/Li-B/125

Optional accessory:

Type of Protection:

Intrinsic Safety

Marking:

Ex ia I/IIC Ma Ga T4

-20 °C ≤ Ta ≤ 80 °C for 3/Li-B/125 and -20 °C ≤ Ta ≤ 50 °C for 3/Li-C/125

Approved for issue on behalf of the IECEx

Certification Body:

Geoff Slater

Position:

Manager

Signature:

(for printed version)

Date:

1. This certificate and schedule may only be reproduced in full.

2. This certificate is not transferable and remains the property of the issuing body.

3. The Status and authenticity of this certificate may be verified by visiting the Official IECEx Website.

Certificate issued by:

MSTC Mine Safety Technology Centre 8 Hartley Drive Thornton NSW 2322 PO Box 343 Australia





Certificate No:

IECEx MSC 14.0010X

Issue No: 1

Date of Issue:

2017-12-05

Page 2 of 6

Manufacturer:

Austdac Pty Ltd

Unit 1/42 Carrington Road, Castle Hill NSW 2154

Australla

Additional Manufacturing location(s):

Dongguan Hubbell Electrical Products Company Limited (DGHAL)

Xincheng Industrial Zone Hengli Town, Dongguan City 523460, Guangdong China

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended.

### STANDARDS:

The electrical apparatus and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards:

IEC 60079-0: 2011

Explosive atmospheres - Part 0: General requirements

Edition:6.0

IEC 60079-11: 2011

Explosive atmospheres - Part 11: Equipment protection by intrinsic safety "i"

Edition:6.0

This Certificate **does not** indicate compliance with electrical safety and performance requirements other than those expressly included in the Standards listed above.

### TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in

Test Report:

AU/MSC/ExTR14.0003/00

Quality Assessment Report:

AU/ITA/QAR06.0001/08 AU/ITA/QAR06.0001/09

AU/ITA/QAR15-0002/02



Certificate No:

IECEx MSC 14.0010X

Issue No: 1

Date of Issue:

2017-12-05

Page 3 of 6

Schedule

### **EQUIPMENT:**

Equipment and systems covered by this certificate are as follows:

The Memory Backup Battery Types 3/Li-C/125 and 3/Li-B/125 each consists of a lithium battery CR1632 or BR1632 respectively, three series Schottky diodes and a current limiting resistor fully encapsulated inside a plastic enclosure. Four header pins are soldered onto the printed circuit board two for each polarity and protrude out of encapsulation to allow connection to unspecified circuits.

SPECIFIC CONDITIONS OF USE: YES as shown below:

It is a condition of safe use that the following parameters are taken into account during any installation:

### Group I

Parameter	Value
Maximum Input Voltage U <sub>i</sub>	20 V
Maximum Internal Capacitance C <sub>i</sub>	Negligible
Maximum Internal Inductance L <sub>i</sub>	Negligible
Maximum Output Voltage U <sub>o</sub>	3.7 V
Maximum Output Current I <sub>O</sub>	3.74 mA
Maximum Output Capacitance C <sub>o</sub>	2000 μF 👙
Maximum Output Inductance L <sub>o</sub>	5 mH
Maximum Output Inductance to Resistance ratio L <sub>o</sub> /R <sub>o</sub>	60 μΗ/Ω



Certificate No:

IECEx MSC 14.0010X

Issue No: 1

Date of Issue:

2017-12-05

Page 4 of 6

### **Group IIC**

Parameter	Value
Maximum Input Voltage U <sub>i</sub>	20 V
Maximum Internal Capacitance C <sub>i</sub>	Negligible
Maximum Internal Inductance L <sub>i</sub>	Negligible
Maximum Output Voltage U <sub>o</sub>	3.7 V
Maximum Output Current I <sub>o</sub>	3.74 mA
Maximum Output Capacitance C <sub>o</sub>	200 μF
Maximum Output Inductance L <sub>o</sub>	1 mH
Maximum Output Inductance to Resistance ratio L <sub>o</sub> /R <sub>o</sub>	60 μH/Ω



Certificate No:

IECEx MSC 14.0010X

Issue No: 1

Date of Issue:

2017-12-05

Page 5 of 6

### DETAILS OF CERTIFICATE CHANGES (for issues 1 and above):

Change to the applicant and manufacturer address and addition of an additional manufacturing location.



Certificate No:

IECEx MSC 14.0010X

Issue No: 1

Date of Issue:

2017-12-05

Page 6 of 6

Additional information:

**Drawing list pertaining to this Certificate:** 

### Manufacturer's Documents

Drawing/Document Number:	Page/s:	Title:	Revision Level:	Date: (yyyy-mm-dd)
61-293-21	3	RTC BACKUP BATTERY TYPE 3/Li-x/125 PCB0335A VER2 ARTWORK DETAILS	02	2014-02-06
61 294 14	2	RTC BACKUP DATTERY TYPE 3/Li-x/125 BILL OF MATERIALS	02	2014-02-07
61-295-04	1	RTC BACKUP BATTERY TYPE 3/Li-x/125 PCB0335A VER2 ASSEMBLY DETAILS	02	2014-06-02
61-296-13	11	RTC BACKUP BATTERY TYPE 3/Li-x/125 LABEL DETAILS	02	2014-05-23
61-297-04	1	RTC BACKUP BATTERY TYPE 3/Li-x/125 HEADER CUTTING DETAILS ASSEMBLY DETAILS		2013-07-15
61-299-07	1	RTC BACKUP BATTERY TYPE 3/Li-x/125 PCB0335A VER2 COMPONENT LOADING DIAGRAM	2	2014-02-07