



REVISIONS

NOTES:

- 1. Dry Type
- 2. Class AA
- 3. Ventilated
- 4. Paint - #61 ANSI



Primary Volts	%	Connect Leads to Tap No.
218	105	1
213	102.5	2
208	100	3
203	97.5	4
198	95	5

Secondary Volts	Connect Leads to Tap No.
208	X1, X2, X3
120	X1 & X0
1 phase	X2 & X0
	X3 & X0

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

KEY: [Hatched Box] DENOTES CONDUIT AREAS

KVA	CATALOG NUMBER	VOLTAGE		K-FACTOR	WEIGHT	PHASE	FREQUENCY
		HIGH	LOW				
45	T3045K0064BK13S	208Δ	208Y/120	13	667 Lbs	3φ	60Hz
Temp Rise:	150°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%	98.60%
Insulation:	220°C	Regulation @ 100% PF	1.40%	Windings:	AL	Typical No Load Losses:	153.53W
NEMA ST20 Standard:	45 dB	Standards:	UL/CSA	Impedance:	3.43%	100% Load (Typ) Load Losses (I ² R)	1190.38W
Electrostatic Shield:	YES	Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:	1343.91W

DATE: 28-Jan-16

TYPE NO:

CASE 2

Meets US DOE 2016 Efficiency