



Commercial, Industrial
and Residential Electrical Products



LL1200 COMMERCIAL GRADE

LED Swivel Floodlight

Warm White
LED
3000K

For Outdoor Use in Wet Locations

Attractive and durable floodlight will bring years of enjoyment, safety and convenience for various architectural or landscape lighting needs.

Features

- **85% less energy consumption***
- Uses only 13W
- 1200 Lumens (equivalent to 75W incandescent)
- Rugged die-cast aluminum heads
- 120/277VAC 50/60Hz
- Unique locking swivel joint for easy light adjustment
- Long life - up to 50,000 hours
- 6" lead wires



LL1200S



NEC &
NEMA 3R
Compliant



LL1200W

LL1200Z

Lighting Specs	
Light Output (Lumens)	1232
Watts	12.6
Lumens per Watt (Efficacy)	97.8
Light Color: Correlated Color Temperature (CCT)	3000 (Warm White)
Warm White	Bright White
2000K	3200K
4500K	6500K

120/277VAC | COMMERCIAL GRADE

*Compared to incandescent bulb with similar light

Catalog Number	Description	Color	Std. Pack	Package Type	UPC-A Bar Code
LL1200S	Weatherproof LED Flood Light 1200 Lumen Warm White / 120/277VAC	Gray	4	Box	050169994771
LL1200W	Weatherproof LED Flood Light 1200 Lumen Warm White / 120/277VAC	White	4	Box	050169994788
LL1200Z	Weatherproof LED Flood Light 1200 Lumen Warm White / 120/277VAC	Bronze	4	Box	050169994795



COMMERCIAL CONSTRUCTION
A Division of Hubbell Incorporated (Delaware)

BELL
Tempe, AZ
800-526-5416
www.hubbell.com/bell/en

