

## Y10MRSA1

Ergonomic Full Cycle Ratchet Hand Tool for J-Dies

#22 - #10 AWG Terminals and Splices

The Y10MRSA1 compression hand tool is specifically designed to accommodate BURNDY® J-dies from #22 - #10 AWG for use on both bare and insulated connectors. J-dies offer a positive connection with terminations exceeding SAE Pullout specifications. The Y10MRSA1 produces the same crimp profile as the Y6NCP1 pneumatic OEM tool making this tool a perfect choice for customers wanting a hand tool to match their production tooling. 5-year limited warranty.



### Features and Benefits

- UL Listed connections when using BURNDY UL Listed connectors
- Ergonomic design requires less handle force reducing user fatigue
- Compact, narrow nose, scissor-action and lightweight at only 1.3 lbs
- Full cycle ratchet mechanism provides complete positive crimp every time
- Emergency release lever in case of misalignment or incorrect die choice

### Features and Benefits (cont.)

- Different die inserts accommodate a range of Small HYDENT™ terminals and HYSPLICE™ splices (see table below for details)
- High-strength steel frame with rubber covered handles for longevity and comfort


### SPECIFICATIONS

**Weight:** 1.3 lbs  
**Length:** 10.75  
**Width:** 3.08 in  
**Warranty:** 5 Years

### FOR USE ON

Die Set (Sold Separately)	Connector Series (#22 - #10 AWG)	Insulation Type
<b>J1022NC1</b>	YAE, YAE-N, YAE-N-F, YAE-Z	Nylon
<b>J1022NC2</b>	YAEV, YAEV-L, YAEV-H, YAEV-RH, YAEV-RS	Nylon
<b>J1022NC3</b>	TN, YAES, TN-F, YAES-F, SN, YSE-HN	Nylon
<b>J1022NC4</b>	TP, BA, TP-F, BA-EF, TP-Z, BA-EZ, TP-LF, BA-EL, SP, BS	Vinyl
<b>J1022NC5</b>	T, YAD, T-F, YAD-F, YAV, YAV-L, YAV-H, YAV-R, YAV-RS, YAV-T-F, YAV-H-F, YAV-Z, YSV, YSV-H, YSV-L	Bare*

\*Wire barrel only



J-DIES  
(sold separately)

