Ground Sentinel® Systems

GM8950 Ground Check Monitor / Ground Fault Relay



Features

- Option of Three Different Frequencies
- Eliminate Monitor Crosstalk
- Remove Multiple Ground Problems
- Extended Cable Lengths Are Possible
- Monitor and Control Over Power Cables









The GAI-TRONICS GM8950 combined Ground Check Monitor / Ground Fault Relay (GFR) consists of a GM8900 Ground Check Monitor (Ground Sentinel®) and a GFR in a shared housing. They are intended to be used on the same three-phase AC mine electrical circuit. The trip contacts of the Ground Sentinel and GFR are internally pre-wired for series or shunt trip of the mine circuit breaker. The GAI-TRONICS Ground Sentinel along with the associated filters is designed to monitor the continuity of the ground circuit of electrical power circuits in mines. The three-phase wires or the pilot wire are used as a return signal path for the Ground Sentinel. If the ground circuit has 15 ohms or less loop resistance, the internal relay will be energized and the circuit breaker that feeds power

to the cable can be energized if the Ground Fault Relay is not tripped. A disruption of the ground circuit that lasts longer than one-fourth of a second will de-energize the relay and trip the circuit breaker. The time delay prevents false trips. Three LED's indicate the condition of the ground check circuit. The three-frequency system is intended for applications on circuits where the ground circuit can't be isolated by ARC TRAPS or elimination of two ARC TRAPS is desired. The GAI-TRONICS GFR along with its associated GAI-TRONICS Current Transformer is designed to trip when ground fault currents exceed preset thresholds. Trip occurs withing a few cycles of the onset of the excessive ground fault current.

Ground Sentinel® Systems





Specifications

Size (LWH) 7.46" x 2.32" x 5.62" (189.5 x 58.9 x 142.7mm) (Fits on a GM1000 Foot Print) Construction......Stainless Steel Serviceability One plug-in board contains all electronics, including relay Supply Voltage 117V \pm 15% 60 Hz (105-135) Supply Voltage Dip For One Minute No Trip w/Good Loop Down to 84V **Transmitter:** (Request Frequency When Ordering) Receiver: Loop Resistance for Trip (over voltage and temperature range). 13 ohms \pm 2 ohms Trip Time Delay (after loop opened)......250 msec (max) Instantaneous Trip......Opens relay coil circuit Output Short Circuit Trip......0-1 ohm Loop Current Indication.......YEL LED brightness proportional to loop resistance **Ground Fault Relay:** Power......84-135 V ac Supply Current82 ma no fault 168 ma tripped

Ordering Information

Ground Sentinel	GM8950/2250 Hz
	GM8950/3125 Hz
	GM8950/4000 Hz
Filter, 3 Phase, 1000V, 2250 Hz	Fl2567
Filter, 3 Phase, 1000V, 3125 Hz	Fl2569
Filter, 3 Phase, 1000V, 4000 Hz	Fl2559
Ground Wire Trap	GM1004
Pilot Wire Filter	Fl2560
Pilot Wire Choke	Fl2558
Current Transformer, 1/0	CO4449
Current Transformer, 500 MCM	CO4450