

Features

- Aluminum Construction Resists Corrosion
- Durable Powder-coated Epoxy Finish
- Standard Colors are Yellow or Silver
- Constant-on, LED Blue Strobe (240 fpm when call is active)
- Model 240WM Series Includes LED Panel Light
- Accommodates RED ALERT® Flush-mount Analog and VoIP Telephones (purchased separately)
- Stainless Steel, Security Hardware
- Easy Installation
- UL 1598 and CSA C22.2 No. 250.0 Luminaires Standard
- Indoor/Outdoor Rated
- 120 V ac Input Required for Strobe and Panel Light Operation
- Custom Colors and Graphics Available



Model 240WM-001
Yellow Wall-mount
Communication Station
w/ LED Strobe & Panel Light
(shown with model
397-00x series telephone
installed; purchased
separately)



Model 241WM-002
Silver Wall-mount
Communication Station
(shown with model
398-00x series telephone
installed; purchased
separately)

GAI-TRONICS' Wall-mount Communication Stations provide a budget-friendly, aesthetically-appealing emergency communications package for indoor or outdoor use. The model series **240WM-00x** and **241WM-00x** wall-mount communication stations both include an integral blue, LED strobe that offers a constant-on feature for easy location of the emergency telephone. The strobe flashes when an emergency call is initiated and remains flashing until the call is terminated. The Model 240WM-00x series additionally includes an integral recessed panel light for telephone panel illumination in dimly-lit areas.

Each model will accommodate any standard size, flush-mount series GAI-TRONICS telephone (purchased separately). Standard colors include yellow or silver, however, custom colors and/or graphics are available upon request.

Specifications

Electrical

Strobe, Model 540-001

Input Voltage..... 120 V ac

Nominal Input Current 39 mA

Panel Light, Model 84503-301

Input Voltage..... 120/240 V ac

Nominal Input Current 25 mA

Mechanical

Dimensions (including strobe) 40.25 H x 10.31 W x 6.81 D inches (1022.4 x 261.9 x 173.0 mm)

Material Aluminum (1/8" thick)

Finish Gloss Powder-coat Epoxy

Weight Approximately 30 lbs.

Approvals

Standards for Luminaires UL 1598 and CSA C22.2 No. 250.0

Environmental

Weather Rating Indoor/Outdoor – Suitable for Wet Locations

Models	Description
240WM-001	Yellow, w/ LED Strobe & Panel Light
240WM-002	Silver, w/ LED Strobe & Panel Light
241WM-001	Yellow, w/ LED Strobe
241WM-002	Silver, w/ LED Strobe

Replacement Parts/ Accessories	Description
84503-301	Panel Light Assembly (120 V ac)
25398-001	"EMERGENCY" Label
25398-012	Phone Symbol Label
540-001	Strobe Assembly, 120 V ac
231-003	Pole Mounting Kit

