




- NOTES:
- 1 CREEPAGE DISTANCE: 880.mm / 34.7"
 - 2 ARC DISTANCE: 372mm / 14.7"
 - 3 NOMINAL VOLTAGE: 26.4kV
 - 4 NOMINAL CURRENT: 3000A
 - 5 WITHSTAND VOLTAGE AT 60 sec.: 50kV
 - 6 B.I.L. : 150kV
 - 7 ROUTINE TEST ACCORDING TO: CEI 60137
 - 8 MAX. TORQUE APPLIED ON FLANGE BOLTS: 54.2 k.N/40 lbf.ft
 - 9 WEIGHT: 52.8 Kg/ 116lbs

REVISIONS					
ZONE	REV.	DESCRIPTION	DRAWN BY	DATE	APPR.
		FOR REVISION "K" SEE "K"			
	L	THE ROD HAS BEEN STRETCHED OF 8mm UP / 576.6 WAS 568.6mm / 1132.4 WAS 1124.4	A.SAVARD	2013-11-28	Y.V.
	M	CHANGE THE SPADE ANGLE	J.N.PILOTTE	2014-05-12	Y.V.



VIEW A-A
SCALE 1 : 10



VIEW B-B
SCALE 1 : 10

This drawing is the proprietary property of Electro Composites (2008) ULC, not part of the public domain, and is issued with the express understanding and agreement that it is not to be reproduced or copied in whole or in part or issued for furnishing information to others, or used directly or indirectly, in any way detrimental to the interest of Electro Composites (2008) ULC and is to be returned upon request by Electro Composites (2008) ULC. All Rights Reserved.

ITEM NO.	QTY	DRAWING NO.	PART NO.	DESCRIPTION	NOTE / MAT'L
5	1	S-1001-2022		CAPACITANCE TAP ASSEMBLY	ALUMINUM
4	1	S-1440-0247		ROD ASSEMBLY	COPPER
3	1	S-1440-0672		SHIELD ASSEMBLY	COPPER
2	1	S-1440-6192		FLANGE	ALUMINUM
1	1	S-1440-0246	-001	CASTING, CYCLOALIPHATIC RESIN	EC-APG-02

PARTS LIST

TOLÉRANCES GÉNÉRALES
(SAUF INDICATIONS CONTRAIRES)

- X. ±3.2
- .X ±2.4
- .XX ±1.6
- .XXX ±0.25
- ANGLES ±0.25°
- RAYONS ±0.8

ARRONDIR LES COINS VIFS
ENLEVER LES BAVURES

LES DIMENSIONS SONT
EN MILLIMÈTRES
(SAUF INDICATIONS CONTRAIRES)

REPLACE:

DRAWN BY: P. ST-AUBIN DATE: 1996/11/28

CHECK BY:

PROJECT ENG.:

PROJECT MANAGER:

Electro Composites
solid HV bushings solution

TITLE: SDC® BUSHING 26.4kV, 3000A
MODEL: 150-030-T-012-00

FORMAT: A	CAGE CODE:	DRAWING NO.: S-1440-0246	REVISION: M
-----------	------------	--------------------------	-------------

SCALE: 1:6	GENERATED BY: SolidWorks 2013	SHEET: 1 of 1
------------	-------------------------------	---------------