

### Features

- **Type 304 Stainless Steel Construction (brushed and passivated)**
- **Accommodates RED ALERT® Flush-mount Analog, VoIP and WiFi Telephones (telephones sold separately)**
- **Weatherproof Rating, Type 3R**
- **True ADA Compliance for Corridor Installation (less than 4 inches depth, including the hands-free telephone)**
- **Includes Constant-on Blue Strobe with Flash During Telephone Activation**
- **Includes Blank Upper Panel for Customer Use (directions, card access, etc.) and Future Options**
- **Security Panel Screws**
- **120 V ac Input (24 V dc Internal Power Supply)**
- **UL/CSA 60950 Certified**



**Model 239WM-001 (pictured left) and Model 239WM-002 (pictured right) Slim Wall-mount Communication Station with Model 397-001 Emergency Telephone (sold separately)**

GAI-TRONICS' Model 239WM-00x Series Slim Wall-mount Communication Station provide an aesthetically appealing package for our RED ALERT® Emergency Telephones. The wall-mount communication station includes a blue LED strobe with a constant-on feature for telephone location identification. The strobe will flash when the emergency telephone has been activated, providing ease of location for first responders.

Each Model 239WM-00x requires a 120/240 V ac input to power the strobe. The integral power supply can also be used to provide 24 V dc power to our VoIP and WiFi Telephones, if installed. The overall depth with a RED ALERT® Emergency Telephone installed is less than 4 inches, which is compliant with ADA corridor installation requirements. The weatherproof rating permits both indoor and outdoor installation and the upper blank panel can be used for installation of a customer-supplied card reader, camera, maps, or general instructions. Factory options for use of this space will be forthcoming.

In addition to true ADA compliance, the 239WM-00x Series Slim Wall-mount Communication Station is UL/CSA 60950 and Type 3R certified. The Model 239WM-001 will accommodate GAI-TRONICS analog and VoIP flush-mount telephones. The Model 239WM-002 includes an integral WiFi antenna with connecting cable to support GAI-TRONICS RED ALERT® WiFi Telephones.

### Specifications

#### Electrical

Input Voltage ..... 120 V ac  
 Input Current ..... 0.3A maximum  
 Power Supply Rating..... 24 V dc / 0.83A, 20W  
 Power Connections ..... screw terminals  
 WiFi Antenna (-002 model only) .... Dual Band 2.4/5.5 GHz

#### Strobe, Model 24701-008 (blue lens)

Power..... 24 V dc  
 Current Draw ..... 45 mA nominal  
 Light Technology ..... LED (100,000 hours)

#### Mechanical

Material (enclosure and panel) ... Type 304 Stainless Steel,  
 (brushed and passivated)  
 Enclosure Dimensions (inches) ..... 24.25 H x 10.125 W x  
 3.125 D (26.54 H includes strobe guard)  
 Blank Panel Dimensions (inches) ..... 12.0 H x 10.0 W  
 Mounting ..... 4 corners (raised bosses)  
 Cable Entry..... Rear (lower) or bottom access,  
 each with two (2) 3/8-inch holes.

#### Environmental

Temperature Range ..... -40° C to +60° C  
 Weatherproof Rating ..... Type 3R


#### Approval Standards

Safety of Information  
 Technology Equipment..... UL / CSA 60950  
 Enclosures for Electrical Equipment..... UL 50, Type 3R

**Note: Gaskets provided for cable entry holes and mounting holes. Hole Caps provided for unused cable entries.**

The following telephone models are supported by the 239WM-001 wall-mount communication station and are sold separately:

Analog	VoIP
392-001	397-700
396-00x	397-701
397-00x	398-701
398-00x	398-702



The following telephone models are supported by the 239WM-002 wall-mount communication station and are sold separately:

WiFi
397-800A
397-801A
398-801A
398-802A