


DRAWING NO.
10009619

CATALOG NUMBER	ITEM NUMBER	L
B3G12NSL	10008971	12.00 [305]
B3G13NSL	10029060	13.00 [330]
B3G14NSL	10029055	14.00 [355]

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
C	12/10/07	ADD NOTE 5 WITH FLAG.	15258	RB	PL



NOTES:

1. MATERIAL: FERRULES - COPPER
BRAID - TINNED COPPER
 2. FINISHED: UNPLATED (FERRULES ONLY)
 3. APPROXIMATE AMP RATING: INDOOR = 960, OUTDOOR = 1150. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
 4. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 5 'UL' SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

FLEXIBLE BRAID

ITEM NO: 10008971, 10029060 & 10029055

CAT NO: B3G12NSL, B3G13NSL & B3G14NSL

SCALE: 1/1	
DRAWN BY: R. BOISVERT	6/24/02
CHECKER: J. MICHAUD	6/25/02
DSN APPVL: J. MICHAUD	6/19/02
MFG APPVL: N/A	--
QC APPVL: J. BRODEUR	6/20/02
MKT APPVL: D. HAMILTON	6/19/02
PROD FAM: --	
PROJECT #: --	SIZE: D
DOCUMENT TYPE: Sales	
REL LEVEL: AUTOCAD	

DRAWING NO: 10009619
SHEET 1 OF 1

BURNDY PRODUCTS