


DRAWING NO.
10039373

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	12/20/07	ADDED FLAGS AND TEXT NOTES #4 & #5	15258	PL	DB



NOTES:

1. APPROXIMATE AMP RATING: INDOOR = 470, OUTDOOR = 560. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

- 3 SUFFIX "TN" DENOTES TIN-PLATED FERRULES.
- 4 "UL" SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.
- 5 "CSA" SYMBOL PER INTERNAL SPEC. L4591, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY®PRODUCTS CALL 1-800-346-4175 MANCHESTER, NH 03109, USA FOR PRODUCT INFO = http://www.fciconnect.com	
BRAID, FLEXIBLE	
ITEM NO: 10031602 & 10038378	
CAT NO: B3D12G64 & B3D12G64TN	
SCALE: 1/1	
DRAWN BY: P LAPONIUS	3/17/04
CHECKER: D BOISVERT	3/18/04
DSN APPVL: J MICHAUD	3/15/04
MFG APPVL: ---	---
QC APPVL: J BRODEUR	3/16/04
MKT APPVL: R BROOKS	3/15/04
PROD FAM: ---	---
PROJECT #: ---	---
DOCUMENT TYPE: Sales	
REL LEVEL: AutoCAD	
BURNDY PRODUCTS	
DRAWING NO	REV
10039373	B
SHEET 1 OF 1	