


PRIMARY VOLTS	%	CONNECT LEADS TO TAP NO.
504	105	1
492	102.5	2
480	100	3
468	97.5	4
456	95	5

PRIMARY LINES TO H1-H2-H3,
SECONDARY LINES TO X0-X1-X2-X3
CAUTION: KEEP 3 TAP CONNECTIONS IN SAME POSITION WHEN TRANSFORMER IS IN OPERATION



KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI
5. UL 1561
6. CSA -C22.2 No 47



KVA	CATALOG NUMBER	VOLTAGE		WEIGHT	PHASE	FREQUENCY			
		HIGH	LOW						
150	H3150K0014BCS	480Δ	208Y/120	1213 Lbs	3φ	60Hz			
Temp Rise:		130°C	TYPICAL PERFORMANCE DATA			Typical Efficiency @ 35%			
Insulation:		220°C				Regulation @ 100% PF	Windings:	CU	Typical No Load Losses:
NEMA ST20 Standard:		50 dB				Standards:	UL/CSA	Impedance:	100% Load (Typ) Load Losses (I²R)
Electrostatic Shield:		YES				Approvals:	DOE-2016	Enclosure:	3R

DATE: 19-Oct-16

TYPE NO:

CASE 4

Meets US DOE 2016 Efficiency