


PRIMARY LINES TO H1-H2-H3
SECONDARY LINES TO X0-X1-X2-X3



KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		K-FACTOR	WEIGHT	PHASE	FREQUENCY			
		HIGH	LOW							
15	T3015K0013BK13SF	480Δ	208Y/120	13	366 Lbs	3φ	60Hz			
Temp Rise:	115°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%				
Insulation:	220°C					Regulation @ 100% PF		Windings:	AL	Typical No Load Losses:
NEMA ST20 Standard:	45 dB					Standards:	UL/CSA	Impedance:		100% Load (Typ) Load Losses (I²R)
Electrostatic Shield:	YES					Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:

DATE: 25-Jan-16

TYPE NO:

CASE 1

Meets US DOE 2016 Efficiency