

DRAWING NO.
10061766


4

3

2

1

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
A	10/6/05	DRAWING RELEASED.	11504	PL	DB



NOTES:

1. APPROXIMATE AMP RATING: 380 INDOOR, 455 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
 2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 SUFFIX LETTER "U" IN CATALOG NUMBER DENOTES FERRULES ARE UNDRILLED.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175 MANCHESTER, NH 03109, USA FOR PRODUCT INFO = http://www.fciconnect.com	
BRAID, FLEXIBLE	
ITEM NO: 10059935 & 10059936	
CAT NO: B2D12G75TN & B2D12G75UTN	
SCALE: 1/1	
DRAWN BY: P LAPONIUS	10/6/05
CHECKER: D BOISVERT	10/7/05
DSN APPVL: J MICHAUD	9/29/05
MFG APPVL: I LEAVITT	9/29/05
QC APPVL: C ACKERMAN	9/30/05
MKT APPVL: R BROOKS	9/29/05
PROD FAM: ---	SIZE: C
PROJECT #: ---	DRAWING NO: 10061766
DOCUMENT TYPE: Sales	SHEET 1 of 1
REL LEVEL: AUTOCAD	REV: A