


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	04/27/2017 13:16:00 PM	LOGO UPDATE	46590	BK	MB



NOTES:

- APPROXIMATE AMP RATING: 380 INDOOR, 455 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES:
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO:	10046525
CAT. NO:	B2D30CG1BR
DRAWN BY:	R. BOISVERT 10/29/07
CHECKER:	P. LAPONIUS 10/29/07
DSN APPVL:	J. PARKER 10/16/07
MFG APPVL:	L. LEAVITT 10/16/07
QA APPVL:	J. BRODEUR 10/15/07
MKT APPVL:	--
PROD FAM:	--
SCALE:	1:2
PROJECT #:	--
DOCUMENT TYPE:	Sales
REL LEVEL:	Released
DRAWING NO	10083352
REV	D
SHEET	1 OF 1



REV: PE0200