

MINIMIZE REACHING FOR PARTS

SOLVE PARTS LOGISTICS PROBLEMS

MOBILE KITS



Workplace Solutions

Here are three ways to supply small parts to the workstation in an ergonomically friendly manner. Properly positioned parts bins at assembly points minimize stretching and reaching which can lead to MSDs. These carts are also great at temporary job task locations.

Place 'n Pick SHELF CART

Complete kits with three 12"(305mm) deep adjustable shelves are available in 30"(762mm), 42"(1067mm), 54"(1372mm), or 66"(1676mm) widths. Or, if you want to build a custom cart, frame kits allow you to install 12"(305mm) or 18"(457mm) deep shelves and other accessories like Bin Bars on which to hang bins, electric power strips or air manifolds, even swing arms (see workstation accessory page in this catalog). Maximum capacity 50 lbs.(22.5 kg) per shelf.



Cart kits include three 12"(305mm) deep x 30"(762mm), 42"(1067mm), 54"(1372mm) or 66"(1676mm) wide steel shelves, sturdy extruded aluminum frame, steel construction brackets, and all hardware. Aluminum frame members and shelves have beige baked polyester finish. Steel brackets, including shelf brackets, are black. Also included are four heavy-duty locking casters, and black end caps.



Shelf carts can easily handle many bin boxes of various sizes. Bins (not included) may be loaded onto shelves from front or rear.

SHELF CART KIT & COMPONENT LISTING

DESCRIPTION	MODEL NO.
Complete Cart Kit-(3) 12"D x 30"W Shelves included	HWP-SC30
Complete Cart Kit-(3) 12"D x 42"W Shelves included	HWP-SC42
Complete Cart Kit-(3) 12"D x 54"W Shelves included	HWP-SC54
Complete Cart Kit-(3) 12"D x 66"W Shelves included	HWP-SC66
INDIVIDUAL COMPONENTS	
Frame Kit*-For 30" Wide Shelves	HWP-SC03
Frame Kit*-For 42" Wide Shelves	HWP-SC04
Frame Kit*-For 54" Wide Shelves	HWP-SC05
Frame Kit*-For 66" Wide Shelves	HWP-SC06
Shelf-12"D x 30"W	WS50-SS03
Shelf-12"D x 42"W	WS50-SS04
Shelf-12"D x 54"W	WS50-SS05
Shelf-12"D x 66"W	WS50-SS06
Shelf-18"D x 30"W	WS50-SS183
Shelf-18"D x 42"W	WS50-SS184
Shelf-18"D x 54"W	WS50-SS185
Shelf-18"D x 66"W	WS50-SS186

*Frame kits include aluminum and steel members, four locking casters, end caps and all assembly hardware. Width shown is inside-to-inside dimension. Shelves fit inside frame uprights. Shelves that hang in front of uprights are available. See catalog for details on shelves and other accessories that can be easily installed on frame.

Rolling Bin Rack



Hang bin boxes on both sides, position cart in the best place for greatest workplace efficiency and ergonomics. Move easily if task or worker changes. Six bin supports may be positioned at desired heights. Bin boxes not included.

- Sturdy extruded aluminum frame with heavy-duty steel brackets.
- Includes six bars for holding bin boxes
- Four locking, swivel casters.
- 300 lb. max capacity.

Dimensions:
77"H x 36"D x 33.6" wide

DESCRIPTION	MODEL NO.
Bin Box Cart with four casters	HWP-BC01

Gravity Feed Rack



Semi-permanent (adjustable glides, not casters) designed for supplying parts bins to work areas. Two conveyor levels, each featuring four roller strips, fully adjustable slope and height. sturdy steel stops prevent bin run-off. Roller strips supported along entire length by WS30 rail.

- Sturdy extruded aluminum frame with heavy-duty steel brackets.
- Adjustable glides, not casters.
- 300 lb. max capacity.

Dimensions:
62"H x 36"D x 30" wide


DESCRIPTION	MODEL NO.
Gravity Feed Rack with Glides	HWP-GFR

Supply 'n Return™ Gravity Feed Cart



Three adjustable conveyors supply full bins to assembly area and return empty bins to aisle. Each level may be easily adjusted for optimum slope and spacing. May also be assembled with all three levels sloped toward work area. Adjustable safety yellow bin stops also protect ends of conveyors. Tough baked polyester finish. Optional adjustable side guides (not shown) may be added to keep bins aligned. Bins not included.

- Sturdy extruded aluminum frame with heavy-duty steel brackets.
- 18 adjustable roller strips.
- 300 lb. max capacity.
- Locking, swivel casters



Dimensions:
48"H x 48"D x 47" wide

DESCRIPTION	MODEL NO.
Supply 'n Return Cart	HWP-GF444
Side Guides (set of two)	HWP-SG4



HEAVY-DUTY SPECIAL PURPOSE CARTS

KEEP YOUR PLANT FLEXIBLE YET SAFE

Push 'n Place™ WORKSTATION


Here's a way to maintain flexibility on the plant floor without sacrificing safety and productivity. The Hubbell Workplace Solutions Push 'n Place portable workstation rolls easily on four heavy-duty locking, swivel casters. Constructed of strong extruded aluminum rail, it measures 36" deep and 90" high, including casters. Frame is 44" wide o.c., perfect for under a 5' conveyor section or 60" bench. Tool bar is 60" long and can be fitted with splice angles to adjoin two or more units. Bin Bar, air manifold and balancer trolley with fitting plus 3/8" hose are standard. Frame is finished with beige baked polyester. Brackets are matte black. Assembly required.



TYPICAL USE
with conveyor


NOTE:
Standard Hubbell Workplace Solutions swing arms and other accessories may be used with this portable workstation.

DESCRIPTION	MODEL NO.
Push 'n Place portable workstation	HWP-0475



WIRE SPOOL CART

Here's the answer to production or maintenance wiring jobs. Roll the wire to the job, unspool what you need, and return the cart to a convenient storage place. WA50 aluminum rail with formed steel brackets, cart measures 54" high, 36" deep and 33.6" wide with a 27" clear space between spool shaft brackets, which are fully adjustable. Available with four heavy-duty casters (two fixed and two swivel with locks), two fixed casters and two glides or, for semi-permanent installation, with four glides. Swivel casters may be installed at either front or back. All components, except hardware, finished with chip-resistant baked polyester coating. Rails are beige and brackets are black. Assembly required. MAXIMUM CAPACITY: 300 lbs.




DESCRIPTION	MODEL NO.
Wire spool cart with four casters.	HWP-RC01
Wire spool cart with four glides.	HWP-RC02
Wire spool cart with two fixed casters and 4 glides.	HWP-RC03

OPTIONAL GLIDES

MOBILE TEST STATION

The Model HWP-TC01 Test Bed Cart represents the ultimate in versatility. Dual support rails adjust to any size electrical box. Box mounts easily with exclusive **EZ-NUT™** Trak Nuts, furnished. Two coil hangers keep cable off floor while cart is being rolled to the job. Heavy duty shelf easily supports even the heaviest technical manuals. Bin Bar holds box bins for miscellaneous storage. Frame is strong extruded aluminum with beige baked polyester finish. All joining brackets are heavy steel with matte black polyester. Includes four locking, swivel casters and all assembly hardware. Bin boxes, electrical box and cables not included. Some assembly required.



DESCRIPTION	MODEL NO.
Mobile test station	HWP-TC01