



**NOTES:**

1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
2. BOX VOLUME: 15.5 IN<sup>3</sup> [254.0 CM<sup>3</sup>]
3. ACCEPTS CEILING FIXTURES UP TO 50 LBS. [22.67 KG] UL LISTED
4. UL LISTED

**LIST OF PARTS**

DESCRIPTION	MATERIAL	FINISH
BOX	STEEL	GALVANIZED
SCREW	STEEL	GALVANIZED
PLASTER EAR	STEEL	GALVANIZED
CLAMP SCREW	STEEL	GALVANIZED
L CLAMP	STEEL	GALVANIZED

**L CLAMP ACCEPTS THE FOLLOWING WIRE TYPES:**  
NONMETALLIC SHEATHED CABLE: #14-2 TO # 10-3 WITH GROUND

INITIAL RELEASE	N.S.	02/26/2016
SYM.	REVISION DESCRIPTION	APP DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:  
**4" OCTAGON BOX 1-1/2" DEEP BOX WITH PLASTER EARS**

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL  $\pm$ .015  
.XXX DECIMAL  $\pm$ .005  
ANGLE  $\pm$ 2°

**RACO**  
South Bend, Indiana

DRAWN BY:	J.R.
APP. BY:	N.S.
DATE:	02/26/2016

SCALE:  
1:2

150 CUS

150

SIZE:

**A**

DIMENSION SHEET FOR CAT. NO.