


NEMA Straight Blade Devices

Rating		15 Ampere		20 Ampere		30 Ampere		50 Ampere		60 Ampere		
		Receptacle / Conn. Body	Plug / Inlet	Receptacle / Conn. Body	Plug / Inlet	Receptacle	Plug	Receptacle	Plug	Receptacle	Plug	
2 Pole / 2 Wire	125V	1	A-37 	A-37 								
	250V	2			A-37 	A-37 						
2 Pole / 3 Wire Grounding	125V	5	A-8 to A-12 to A-28 A-32 A-34 A-35 to A-40 A-46 C-6 AA-35 A-32 A-35 A-40 AA-35 	A-32 A-33 A-35 A-40 AA-35 	A-8 to A-12 to A-28 A-32 A-34 A-35 to A-40 A-46 C-6 AA-37 A-32 A-33 A-35 A-40 AA-37 	A-32 A-33 A-35 A-40 AA-37 	A-41 	A-41 	A-43 	A-43 		
	250V	6	A-9 A-11 A-23 A-32 A-36 C-6 	A-32 A-36 C-6 	A-9 A-11 A-23 A-32 A-36 C-6 	A-32 A-36 C-6 	A-41 	A-41 	A-43 	A-43 		
	277V AC	7	A-37 	A-37 			A-41 	A-41 	A-43 	A-43 		
3 Pole / 3 Wire	125/250V AC	10			A-38 	A-38 	A-41 	A-41 	A-43 	A-43 		
	3Ø 250V AC	11										
3 Pole / 4 Wire Grounding	125/250V AC	14			A-38 	A-38 	A-42 	A-42 	A-44 	A-44 	A-45 	A-45
	3Ø 250V AC	15			A-38 	A-38 	A-42 	A-42 	A-44 	A-44 	A-45 	A-45
4P / 4W	3ØY 120/208V AC	18			A-38 	A-38 	A-42 	A-42 	A-44 	A-44 	A-45 	A-45

HOW TO USE THIS CHART:

For quick reference, this chart shows the configuration, primary catalog section and page number where the devices are shown.



Open Slots indicates Receptacle / Connector Body configurations (female).



Closed Slots indicates Plug / Inlet configurations (male).

NEMA Configuration

Catalog Section and Page Number

A-3
A-7
A-16
C-6
AA-35

5-15R

IMPORTANT NOTICE:

The catalog pages referenced in **BLUE** are Insulgrip®, Valise®, Safety-Shroud® and Watertight Safety-Shroud® devices, in **RED** are Watertight devices, and in **ORANGE** are Marine corrosion resistant devices