



NOTES:

1. DIMENSIONS SUBJECT TO +/- 3% TOLERANCE
2. LEAKAGE DISTANCE (Inches) - 8.5
3. ALTITUDE 0-12000 FT. ABOVE SEA LEVEL
4. WEIGHT OF UNIT INCLUDING HARDWARE - 1.7 LB.
5. MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE 2.55 kV MCOV
6. VOLTAGE RATING 3 kV RMS.



.5 $\mu$ SEC IR kV	10kA kV	500 A SWITCHING SURGE IR kV	MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT				
			1.5 kA	3.0 kA	5 kA	10 kA	20 kA
11.4		7.3	8	8.6	9.1	9.9	11.2

IEEE DISTRIBUTION HEAVY DUTY IEC DISTRIBUTION DH	<p>CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.</p>	 <b>HUBBELL® POWER SYSTEMS</b>			
		TITLE <b>PDV-100 OPTIMA 2.55 KV MCOV</b>			
REV DATE	07/16/18	SIZE S	DWG NO. ALES7XXX	CAT / PART / ASSY NO. 213703-7202	REV 32
DO NOT SCALE THIS DRAWING		DRN BY	PRO	DATE	06/17/00
		SHEET 1		OF 1	