


NOTES:

1. DIMENSIONS SUBJECT TO +/- 5% TOLERANCE
2. LEAKAGE DISTANCE - 1564 mm
3. ALTITUDE 0-3600 m ABOVE SEA LEVEL
4. WEIGHT OF UNIT INCLUDING HARDWARE - 8.3 kg
5. MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE U_c 36.5 kV
6. RATED VOLTAGE U_r 45 kV RMS



10 kA STEEP CURRENT U_{res} kV	500 A SWITCHING SURGE U_{res} kV	MAXIMUM 8/20 RESIDUAL VOLTAGE - kV AT					
		1.5 kA	3.0 kA	5.0 kA	10 kA	20 kA	40 kA
136	95.8	103	108	113	118	133	149

IEC CLASS 2 SURGE ARRESTER	 HUBBELL® POWER SYSTEMS	TITLE PVI-LP ARRESTER 36.5 kV U_c		
		SIZE S	DWG NO. --	CAT / PART / ASSY NO. 214536-C2BC
REV DATE 10/17/2022	CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	DO NOT SCALE THIS DRAWING	DRN BY RVK	DATE 10/17/22
		SHEET 1 OF 1		REV 0