



REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	12/20/07	ADDED FLAG AND TEXT NOTES #3 & #4	15258	PL	DB



NOTES:

1. APPROXIMATE AMP RATING: 340 INDOOR, 405 OUTDOOR
THIS RATING MAY VARY WITH AMBIENT CONDITIONS.
ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
 2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 "UL" SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.
- 4 "CSA" SYMBOL PER INTERNAL SPEC. L4591, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY®PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

BRAID

ITEM NO: 33216D

CAT NO: BE24G112

SCALE: 1/1	
DRAWN BY: R.BOISVERT 08/12/05	
CHECKER: P.LAPONIUS 08/22/05	
DSN APPVL: J.MICHAUD 08/11/05	
MFG APPVL: N/A	
QC APPVL: C.ACKERMAN 08/22/05	
MKT APPVL: R.BROOKS 08/11/05	
PROD FAM: --	
PROJECT #: --	SIZE
DOCUMENT TYPE: Sales	D
REL LEVEL: AutoCAD	

FCJ BURNDY PRODUCTS

DRAWING NO	REV
10059193	B
SHEET 1 OF 1	