


B (SPACER)

(PIGTAIL)

ROBERTSON)

WIRE: #12 AWG STRANDED, 10-1/2" LONG, GREEN INSULATED, U.L. LISTED, 600 VOLT MAX: EXTRA-GRIP RING TERMINAL, 16/12 AWG BRASS: #10-32 X 3/8" GROUND SCREW W/ COMBO HEX WASHER HEAD (SLOTTED. #2 PHILLIPS AND



LIST OF PARTS					
DESCRIPTION	MATERIAL	FINISH			
SPACER	STEEL	GALVANIZED			
SIDE	STEEL	GALVANIZED			
FASTENERS	STEEL	GALVANIZED			
PIGTAIL	INSULATED STRANDED COPPER	N/A			

	INITIAL RELEASE	J.R.	06/22/2015
SYM.	REVISION DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

4-11/16" SQUARE WELDED BOX 2-1/8" DEEP WITH RAISED GROUND AND STRANDED PIGTAIL

NOTES:

- ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS] 1.
- 2.
- BOX VOLUME: 42 IN³ [688.2 CM³] ACCEPTS ALL 4-11/16" COVERS,707RAC & 709 3. PARTITIONS. ALL SOLD SEPARATELY
- 4. **UL LISTED**

KNOCKOUTS				
TRADE SIZE	LOCATION	QTY.		
1/2"	Α	1		
(1/2"-3/4") TKO®	Α	3		
(1/2"-3/4") TKO®	B,C,D,E	3		

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ±.015 .XXX DECIMAL ± .005 ANGLE ±2°

RACO
South Bend, Indian

J.R. DRAWN BY: SCALE: N.S. APP. BY: 1:3 06/22/2015 DATE:

SIZE:

257SM

257SM CUS