



- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 42 IN³ [688.2 CM³]
 3. ACCEPTS ALL 4-11/16" COVERS, 707RAC & 709 PARTITIONS, ALL SOLD SEPARATELY
 4. UL LISTED

B (SPACER)

(PIGTAIL)
 WIRE: #12 AWG STRANDED, 10-1/2" LONG, GREEN INSULATED, U.L. LISTED, 600 VOLT MAX;
 EXTRA-GRIP RING TERMINAL, 16/12 AWG BRASS;
 #10-32 X 3/8" GROUND SCREW W/ COMBO HEX WASHER HEAD (SLOTTED, #2 PHILLIPS AND ROBERTSON)

E (SIDE)

A (SPACER)

C (SIDE)

D (SPACER)

8-32 X 1/2" PHILIPS / SLOT DRIVE (FASTENER)

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
1/2"	A	1
(1/2"-3/4") TKO®	A	3
1"	B,C,D,E	8

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED
PIGTAIL	INSULATED STRANDED COPPER	N/A

SYMBOL	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	K.K.	06/22/2015

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
4-11/16" SQUARE WELDED BOX 2-1/8" DEEP WITH RAISED GROUND AND PIGTAIL ATTACHED

TOLERANCE UNLESS OTHERWISE SPECIFIED
 .XX DECIMAL ±.015
 .XXX DECIMAL ±.005
 ANGLE ±2°

RACO
 South Bend, Indiana

DRAWN BY:	K.K.	SCALE:
APP. BY:	N.S.	1:3
DATE:	06/22/2015	

258SM CUS

258SM DIMENSION SHEET FOR CAT. NO.

SIZE: **A**