


NOTES:

1. DIMENSIONS SUBJECT TO +/- 5% TOLERANCE
2. LEAKAGE DISTANCE (mm) - 1072
3. ALTITUDE 0-3600 m ABOVE SEA LEVEL
4. WEIGHT OF UNIT INCLUDING HARDWARE - 4.2 kg.
5. MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE U_c 24.4 kV
6. RATED VOLTAGE U_r 30 kV RMS.



10 kA STEEP CURRENT U_{res} kV	500 A SWITCHING SURGE U_{res} kV	MAXIMUM 8/20 RESIDUAL VOLTAGE - kV AT					
		1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
105.2	69.6	76.0	81.4	86.2	94.0	106.8	125.9

DISTRIBUTION ARRESTER IEEE HEAVY DUTY IEC DH CLASS	 HUBBELL® POWER SYSTEMS	TITLE			
		PDV-100 OPTIMA ARRESTER 24.4 kV U _c			
	REV DATE	CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	SIZE	DWG NO.	CAT / PART / ASSY NO.
12/04/20	S		--	294224-C2CC	0
		DO NOT SCALE THIS DRAWING	DRN BY RVK	DATE 12/04/20	SHEET 1 OF 1