



BILL OF MATERIAL

ITEM NUMBER	CATALOG NUMBER	TYPE / DESCRIPTION	INSULATION MATERIAL	INSULATION COLOR	WIRE SIZE	STUD SIZE	QTY/BAG	QTY/BOX
A	10101443	YHSS18BG10	SPLICE	HEAT SHRINK	RED	22-18	--	10
B	10101445	YHSS14BG10	SPLICE	HEAT SHRINK	BLUE	16-14	--	10
C	10101447	YHSS10BG10	SPLICE	HEAT SHRINK	YELLOW	12-10	--	10
D	10101444	SP18BG25	SPLICE	VINYL	RED	22-18	--	25
E	10101446	SP14BG25	SPLICE	VINYL	BLUE	16-14	--	25
F	10101448	SP10BG25	SPLICE	VINYL	YELLOW	12-10	--	25
G	10101449	TP188RBG25	RING	VINYL	RED	22-18	#8	5
H	10101451	TP148RBG25	RING	VINYL	BLUE	16-14	#8	5
I	10101453	TP108RBG25	RING	VINYL	YELLOW	12-10	#8	5
J	10101450	TP1810RBG25	RING	VINYL	RED	22-18	#10	5
K	10101452	TP1410RBG25	RING	VINYL	BLUE	16-14	#10	5
L	10101454	TP1010RBG25	RING	VINYL	YELLOW	12-10	#10	5
M	10101462	QP18F25X03BG25	QUICK DISCONNECT	VINYL	RED	22-18	.250 FQC	5
N	10101464	QP14F25X03BG25	QUICK DISCONNECT	VINYL	BLUE	16-14	.250 FQC	5
O	10101466	QP10F25X03BG25	QUICK DISCONNECT	VINYL	YELLOW	12-10	.250 FQC	5
P	10101455	TP186FBG25	FORK	VINYL	RED	22-18	#6 SPADE	5
Q	10101457	TP146FBG25	FORK	VINYL	BLUE	16-14	#6 SPADE	5
R	10101459	TP106FBG25	FORK	VINYL	YELLOW	12-10	#6 SPADE	5
S	10101461	TP188FBG25	FORK	VINYL	RED	22-18	#8 SPADE	5
T	10101458	TP148FBG25	FORK	VINYL	BLUE	16-14	#8 SPADE	5
U	10101460	TP108FBG25	FORK	VINYL	YELLOW	12-10	#8 SPADE	5
V	10101456	TP1810FBG25	FORK	VINYL	RED	22-18	#10 SPADE	5
W	10101463	TP1410FBG25	FORK	VINYL	BLUE	16-14	#10 SPADE	5
X	10101465	TP1010FBG25	FORK	VINYL	YELLOW	12-10	#10 SPADE	5
8	10101118	22WHITESPINNER	22 INCH EMPTY SPINNER	--	--	--	--	--
5	10101442	22WHITESPINNERFL	22 INCH FULLY LOADED SPINNER	--	--	--	--	--

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
F	05/04/2018	CHANGE THE CONTROL # ON LABELS	49020	PP	VS




SIDE 1 OF RACK
SCALE: 1/4




SIDE 2 OF RACK
SCALE: 1/4

- NOTES:
- ALL CONNECTORS TO BE PACKAGED IN 4-1/2" X 3-3/4" BAGS WITH THE QTY'S SHOWN ON PAGES 2 & 3.
 - REFER TO SHEETS 2 & 3 FOR BAG DETAILS.
 - CONNECTORS TO BE PLACED ON RACK IN COLUMNS. SUGGESTED ORDER SHOWN IN DISPLAY RACK DETAIL.
 - EACH HOOK TO CARRY 5 BAGS.
 - FULL DISPLAY RACK (10101442) COMPRISES AN EMPTY DISPLAY RACK (10101118). REORDER CARDS, (SEE SHEET 4) AND 5 PACKAGES OF EACH CONNECTOR SHOWN ON TABLE (120 PACKAGES TOTAL).
 - INDIVIDUAL ITEMS AVAILABLE FOR REORDER.
 - HEAT SHRINK SPLICES ARE NOT UL/CSA CERTIFIED. BAGS WILL NOT SHOW UL/CSA LOGOS.
 - INDIVIDUAL REORDER CARDS ARE INCLUDED WITH EACH BOX OF CONNECTORS. (SEE SHEET 4)



FRONT



BACK

BAG DETAIL

<p>TO ORDER BURNDY® PRODUCTS CALL</p> <p>UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)</p> <p>CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)</p> <p>FOR PRODUCT INFO: http://www.burndy.com</p>	DISPLAY RACK/BAG PRINTING	
	ITEM NO: SEE TABLE	
	CAT NO: SEE TABLE	
	SCALE: 1/1	DRAWN BY: R. BOISVERT 07/23/09
	CHECKER: J. MICHAUD 07/30/09	DSN APPVL: J. MICHAUD 07/30/09
MFG APPVL: --	QC APPVL: J. BRODEUR 07/31/09	
MKT APPVL: R. CAVANAUGH 07/30/09	PROJECT #: --	SIZE: D
PROD FAM: --	DOCUMENT TYPE: Sales	REL LEVEL: AutoCAD
DRAWING NO 10104489		REV F
SHEET 1 OF 4		

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
F	05/04/2018	CHANGE THE CONTROL # ON LABELS	49020	PP	VS


3 "A"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
YHSS18BG10
#22-#18 AWG
H/S Splice/Manchon Thermoretractable

QTY: 10 PCS



7 81810 48667 2

"B"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
YHSS14BG10
#16-#14 AWG
H/S Splice/Manchon Thermoretractable

QTY: 10 PCS



7 81810 48665 8

"C"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
YHSS10BG10
#12-#10 AWG
H/S Splice/Manchon Thermoretractable

QTY: 10 PCS



7 81810 48663 4



"D"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
SP18BG25
#22-#18 AWG
Vinyl Splice/Manchon Vinyle

LISTED QTY: 25 PCS

7 81810 48631 3



"E"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
SP14BG25
#16-#14 AWG
Vinyl Splice/Manchon Vinyle

LISTED QTY: 25 PCS

7 81810 48629 0

"F"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
SP10BG25
#12-#10 AWG
Vinyl Splice/Manchon Vinyle

LISTED QTY: 25 PCS




7 81810 48627 6



"G"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP188RBG25
#22-#18 AWG, #8 Screw/Vis
Ring Terminal/Cosse pré-isolée à oeil

LISTED QTY: 25 PCS

7 81810 48661 0



"H"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP148RBG25
#16-#14 AWG, #8 Screw/Vis
Ring Terminal/Cosse pré-isolée à oeil

LISTED QTY: 25 PCS

7 81810 48651 1



"I"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP108RBG25
#12-#10 AWG, #8 Screw/Vis
Ring Terminal/Cosse pré-isolée à oeil

LISTED QTY: 25 PCS

7 81810 48641 2



"J"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP1810RBG25
#22-#18 AWG, #10 Screw/Vis
Ring Terminal/Cosse pré-isolée à oeil

LISTED QTY: 25 PCS

7 81810 48655 9



"K"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP1410RBG25
#16-#14 AWG, #10 Screw/Vis
Ring Terminal/Cosse pré-isolée à oeil

LISTED QTY: 25 PCS

7 81810 48645 0



"L"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY


Catalog No./Numéro de cat.:
TP1010RBG25
#12-#10 AWG, #10 Screw/Vis
Ring Terminal/Cosse pré-isolée à oeil

LISTED QTY: 25 PCS

7 81810 48635 1

SEE SHEET ONE FOR NOTES.

BAG PRINTING	
ITEM NO: SEE TABLE (SHEET 1)	
CAT NO: SEE TABLE (SHEET 1)	
SCALE: 1/1	
DRAWN BY: R. BOISVERT 07/23/09	
CHECKER: J. MICHAUD 07/30/09	
DSN APPVL: J. MICHAUD 07/30/09	
MFG APPVL: -- --	DRAWING NO
QC APPVL: J. BRODEUR 07/31/09	
MKT APPVL: R. CAVANAUGH 07/30/09	REV
PROD FAM: --	F
PROJECT #: --	SIZE
DOCUMENT TYPE: Sales	D
REL LEVEL: AutoCAD	SHEET 2 OF 4

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

D

C

B

A

D

C

B

A

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
F	05/04/2018	CHANGE THE CONTROL # ON LABELS	49020	PP	VS

3 "M"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
QP18F25X03BG25
#22-#18 AWG, .250" Width/Large
Female Disconnect/Cosse Femelle
LISTED QTY: 25 PCS (U) (S)
46DE 207131

7 81810 48625 2

"N"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
QP14F25X03BG25
#16-#14 AWG, .250" Width/Large
Female Disconnect/Cosse Femelle
LISTED QTY: 25 PCS (U) (S)
46DE 207131

7 81810 48623 8

"O"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
QP10F25X03BG25
#12-#10 AWG, .250" Width/Large
Female Disconnect/Cosse Femelle
LISTED QTY: 25 PCS (U) (S)
46DE 207131

7 81810 48621 4

"P"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP186FBG25
#22-#18 AWG, #6 Screw/Vis
Fork Terminal/Cosse a Fourche
LISTED QTY: 25 PCS (U) (S)
17YL 246519

7 81810 48657 3

"Q"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP146FBG25
#16-#14 AWG, #6 Screw/Vis
Fork Terminal/Cosse a Fourche
LISTED QTY: 25 PCS (U) (S)
17YL 246519

7 81810 48647 4

"R"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP106FBG25
#12-#10 AWG, #6 Screw/Vis
Fork Terminal/Cosse a Fourche
LISTED QTY: 25 PCS (U) (S)
17YL 246519

7 81810 48637 5

"S"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP188FBG25
#22-#18 AWG, #8 Screw/Vis
Fork Terminal/Cosse a Fourche
LISTED QTY: 25 PCS (U) (S)
17YL 246519

7 81810 48659 7

"T"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP148FBG25
#16-#14 AWG, #8 Screw/Vis
Fork Terminal/Cosse a Fourche
LISTED QTY: 25 PCS (U) (S)
17YL 246519

7 81810 48649 8

"U"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP108FBG25
#12-#10 AWG, #8 Screw/Vis
Fork Terminal/Cosse a Fourche
LISTED QTY: 25 PCS (U) (S)
17YL 246519

7 81810 48639 9

"V"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP1810FBG25
#22-#18 AWG, #10 Screw/Vis
Fork Terminal/Cosse a Fourche
LISTED QTY: 25 PCS (U) (S)
17YL 246519

7 81810 48653 5

"W"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP1410FBG25
#16-#14 AWG, #10 Screw/Vis
Fork Terminal/Cosse a Fourche
LISTED QTY: 25 PCS (U) (S)
17YL 246519

7 81810 48643 6

"X"

Made in U.S.A.
Fabriqué aux E.U.

BURNDY

Catalog No./Numéro de cat.:
TP1010FBG25
#12-#10 AWG, #10 Screw/Vis
Fork Terminal/Cosse a Fourche
LISTED QTY: 25 PCS (U) (S)
17YL 246519

7 81810 48633 7

SEE SHEET ONE FOR NOTES.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	BAG PRINTING	
	ITEM NO: SEE TABLE (SHEET 1)	
	CAT NO: SEE TABLE (SHEET 1)	
	SCALE: 1/1	
	DRAWN BY: R. BOISVERT 07/23/09	
	CHECKER: J. MICHAUD 07/30/09	
	DSN APPVL: J. MICHAUD 07/30/09	
	MFG APPVL: -- --	DRAWING NO
	QC APPVL: J. BRODEUR 07/31/09	
	MKT APPVL: R. CAVANAUGH 07/30/09	REV
PROD FAM: --	F	
PROJECT #: --	SIZE	
DOCUMENT TYPE: Sales	D	
REL LEVEL: AutoCAD	SHEET 3 OF 4	

REORDER CARD INFORMATION		CARD INFORMATION		SEE SHEETS 2 & 3
ITEM NUMBER	CATALOG NUMBER	ITEM NUMBER	CATALOG NUMBER	LETTER
10104465	YHSS18BG10RC	10101443	YHSS18BG10	A
10104466	YHSS14BG10RC	10101445	YHSS14BG10	B
10104467	YHSS10BG10RC	10101447	YHSS10BG10	C
10104468	SP18BG25RC	10101444	SP18BG25	D
10104469	SP14BG25RC	10101446	SP14BG25	E
10104470	SP10BG25RC	10101448	SP10BG25	F
10104471	TP188RBG25RC	10101449	TP188RBG25	G
10104472	TP148RBG25RC	10101451	TP148RBG25	H
10104473	TP108RBG25RC	10101453	TP108RBG25	I
10104474	TP1810RBG25RC	10101450	TP1810RBG25	J
10104475	TP1410RBG25RC	10101452	TP1410RBG25	K
10104476	TP1010RBG25RC	10101454	TP1010RBG25	L
10104484	QP18F25X03BG25RC	10101462	QP18F25X03BG25	M
10104486	QP14F25X03BG25RC	10101464	QP14F25X03BG25	N
10104488	QP10F25X03BG25RC	10101466	QP10F25X03BG25	O
10104480	TP148FBG25RC	10101458	TP148FBG25	P
10104479	TP146FBG25RC	10101457	TP146FBG25	Q
10104481	TP106FBG25RC	10101459	TP106FBG25	R
10104483	TP188FBG25RC	10101461	TP188FBG25	S
10104477	TP186FBG25RC	10101455	TP186FBG25	T
10104482	TP108FBG25RC	10101460	TP108FBG25	U
10104478	TP1810FBG25RC	10101456	TP1810FBG25	V
10104485	TP1410FBG25RC	10101463	TP1410FBG25	W
10104487	TP1010FBG25RC	10101465	TP1010FBG25	X

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
F	05/04/2018	CHANGE THE CONTROL # ON LABELS	49020	PP	VS



Catalog No./Numéro de cat.:
 2 SP18BG25
 #22-#18 AWG
 2 Vinyl Splice/Manchon Vinyle
 QTY: 25 PCS

LISTED  17YL   246519
 7 81810 48631 3


TIME TO REORDER
HEURE DE COMMANDER
À NOUVEAU

Made in U.S.A./Fabriqué aux E.U.

FORM 1

NOTES:

- LAYOUT ON REORDER CARD TO MATCH BAGS WITH THE ADDITION OF "TIME TO REORDER, HEURE DE COMMANDER À NOUVEAU" AS SHOWN.
- CATALOG NUMBER AND DESCRIPTION TO COINCIDE WITH LETTERS A-X ON SHEETS 2 & 3.
- REORDER CARDS TO BE PACKAGED WITH EACH BOX OF CONNECTORS ORDERED.
- REORDER CARDS TO BE APPROXIMATELY THE SAME HEIGHT AND WIDTH AS BAGS. (3-3/4" WIDE X 4-1/2" TALL)

REORDER CARD			
TO ORDER BURNDY® PRODUCTS CALL		UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)	
CANADA: 1-800-361-6975 (QUEBEC)		1-800-387-6487 (ALL OTHER PROVINCES)	
FOR PRODUCT INFO: http://www.burndy.com			
ITEM NO: SEE TABLE		CAT NO: SEE TABLE	
SCALE: 1/1	DRAWN BY: R. BOISVERT 07/23/09		
CHECKER: J. MICHAUD 07/30/09	DSN APPVL: J. MICHAUD 07/30/09		
MFG APPVL: --	QC APPVL: J. BRODEUR 07/31/09	DRAWING NO	REV
MKT APPVL: R. CAVANAUGH 07/30/09	PROD FAM: --	10104489	F
PROJECT #: --	SIZE	SHEET 4 OF 4	
DOCUMENT TYPE: Sales	REL LEVEL: AutoCAD		