

DRAWING NO. 30003952				7		6			5			4			3			2			1			
CATALOG NUMBER	FIG. NO.	CONDUCTOR		STUD HOLE SIZE	DIMENSIONS								DIELESS (# OF CRIMPS)	INSTALLATION TOOLING										WIRE STRIP LENGTH
		AWG	MM ²		O.D.	B	C	D MIN.	K DIA.	L	N	T		MECHANICAL	HYDRAULIC							COLOR CODE	DIE INDEX	
															MD6, OUR840, MD7-34R	BCT500HS, Y500CTHS	Y35, Y39, Y750, PAT750	Y46 PAT46	Y45	Y48	Y60			
YA27LNT14	I	3/0 AWG	--	1/4"	.62 [16]	1.00 [25]	.76 [19]	.67 [17]	.27 [7]	2.10 [53]	.31 [8]	.13 [3]	Y644HS (1) Y81KFT(2) Y81KFTMBH (2) PAT81KFT-18V (2) PAT644 (1) PAT444 (1)	W27VT(2)	X27RT(3)	U27RT(1)	U27RT(1)	U27RT(1)	--	--	ORANGE	14	1-1/16"	
YA27LNT516	I			5/16"	.62 [16]	1.00 [25]	.60 [15]	.77 [20]	.33 [8]	2.17 [55]	.34 [9]	.12 [3]												
YA27LNT38	I			3/8"	.62 [16]	1.00 [25]	.73 [19]	1.14 [29]	.41 [10]	2.64 [67]	.41 [10]	.12 [3]												
YA28LNT14	I	4/0 AWG	--	1/4"	.69 [18]	.88 [22]	.76 [19]	1.07 [27]	.27 [7]	2.60 [66]	.31 [8]	.14 [4]		W28VT(2)	X28RT(3)	U28RT(1)	U28RT(1)	U28RT(1)	C28R(1)	L28RT(1)	PURPLE	15	1-1/8"	
YA28LNT516	I			5/16"	.69 [18]	.88 [22]	.70 [18]	.77 [20]	.33 [8]	2.09 [53]	.34 [9]	.14 [4]												
YA28LNT38	I			3/8"	.69 [18]	.88 [22]	.76 [19]	1.14 [29]	.41 [10]	2.67 [68]	.41 [10]	.14 [4]												
YA29LENT516	I	250 kcmil	--	5/16"	.75 [19]	1.06 [27]	.76 [19]	.72 [18]	.33 [8]	2.48 [63]	.34 [9]	.16 [4]		W29VT(2)	X29RT(4)	U29RT(1)	U29RT(1)	U29RT(1)	L29R(1)	L29RT(1)	YELLOW	16	1-1/8"	
YA29LENT38	I			3/8"	.75 [19]	1.06 [27]	.76 [19]	1.20 [30]	.41 [10]	2.96 [75]	.41 [10]	.16 [4]												
YA29LNT38	I			3/8"	.75 [19]	1.06 [27]	.96 [24]	1.20 [30]	.41 [10]	2.96 [75]	.41 [10]	.16 [4]												
YA29LNT12	I			1/2"	.75 [19]	1.06 [27]	.96 [24]	1.20 [30]	.53 [13]	3.08 [78]	.53 [13]	.16 [4]												
YA30LNT14	I	300 kcmil	150	1/4"	.81 [21]	1.03 [26]	.83 [21]	.71 [18]	.27 [7]	2.26 [57]	.31 [8]	.16 [4]		W30VT(4)	----	U30RT(2)	U30RT(2)	U30RT(2)	C30R(2)	L30RT(1)	WHITE	17	1-1/8"	
YA30LNT38	I			3/8"	.81 [21]	1.03 [26]	.96 [24]	1.20 [30]	.41 [10]	2.97 [75]	.41 [10]	.16 [4]												
YA30LNT12	I			1/2"	.81 [21]	1.03 [26]	.96 [24]	1.20 [30]	.53 [13]	3.09 [78]	.53 [13]	.16 [4]												
YA31LNT38	I	350 kcmil	185	3/8"	.88 [22]	1.06 [27]	.96 [24]	1.45 [37]	.41 [10]	3.31 [84]	.41 [10]	.18 [4]		W31VT(4)	----	U31RT(2)	U31RT(2)	U31RT(2)	C31R(2)	L31RT(1)	RED	18	1-3/16"	
YA31LNT12	I			1/2"	.88 [22]	1.06 [27]	.88 [22]	1.14 [29]	.53 [13]	2.75 [70]	.53 [13]	.18 [4]												
YA32LNT38	I	400 kcmil	--	3/8"	.95 [24]	1.19 [30]	.96 [24]	1.20 [30]	.41 [10]	3.21 [82]	.41 [10]	.20 [5]		W32VT(4)	----	U32RT(2)	U32RT(2)	U32RT(2)	C32R(2)	L32RT(1)	BLUE	19 OR 470	1-1/4"	
YA32LNT12	I			1/2"	.95 [24]	1.19 [30]	.96 [24]	1.20 [30]	.53 [13]	3.21 [82]	.53 [13]	.19 [5]												
YA34LNT38	I	500 kcmil	240	3/8"	1.06 [27]	1.27 [32]	.96 [24]	1.45 [37]	.41 [10]	3.65 [93]	.41 [10]	.23 [6]		W34VT(4)	----	U34RT(2)	U34RT(2)	U34RT(2)	C34R(1)	L34RT(1)	BROWN	20 OR 299	1-7/16"	
YA34LNT12	I			1/2"	1.06 [27]	1.27 [32]	.96 [24]	1.45 [37]	.53 [13]	3.65 [93]	.53 [13]	.23 [6]												
YA36LNT38	I	600 kcmil	300	3/8"	1.18 [30]	1.38 [35]	1.12 [28]	1.70 [43]	.41 [10]	4.09 [104]	.50 [13]	.27 [7]	----	----	U36RT(2)	U36RT(2)	U36RT(2)	C36R(1)	L36RT(1)	GREEN	22	1-3/4"		
YA36LNT12	I			1/2"	1.188 [30]	1.38 [35]	1.00 [25]	1.17 [30]	.53 [13]	3.29 [84]	.53 [13]	.27 [7]												
YA39LNT38	I	750 kcmil	--	3/8"	1.300 [33]	1.42 [36]	1.12 [28]	1.70 [36]	.41 [10]	4.24 [108]	.50 [13]	.27 [7]	Y81KFT (3) Y81KFTMBH (3) PAT81KFT-18V (3) PAT644 (1) PAT444 (1)	----	----	U39RT(2)	U39RT(2)	U39RT(2)	C39R(1)	L39RT(1)	BLACK	24	1-15/16"	
YA39LNT12	I			1/2"	1.300 [33]	1.42 [36]	1.63 [41]	1.70 [36]	.56 [14]	4.24 [108]	.53 [13]	.27 [7]												
YA39LNT58	I			5/8"	1.300 [33]	1.42 [36]	1.30 [33]	1.43 [36]	.69 [10]	3.67 [93]	.66 [17]	.27 [7]												

TOLERANCE BLOCK

CONNECTOR SIZE	TOLERANCES						
	B	C	E	K DIA.	L	N	O.D.
-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01
-26 THRU -34	±.08	±.04	±.02	±.02	±.12	±.03	±.01
-35 AND UP	±.09	±.06	±.02	±.02	±.15	±.06	±.01

NOTES:

1. MATERIAL: COPPER TUBING.
2. FINISH: TIN PLATED.
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
4. INSTALLATION TOOLING AND DIES ARE CONSTANTLY BEING UPDATED. FOR THE LATEST INSTALLATION TOOLING INFORMATION REFER TO THE MASTER CATALOG ON THE BURNDY WEBSITE.

FIG. 1

REV	DATE	DESCRIPTION	ECO	BY	C'H*K.
AC	2023-06-28 00:00:00 EDT	UPDATED AS PER MARKUP	230627031433	YR	RA

TO ORDER BURNDY@PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

HYLUG™ COPPER (NARROW TONGUE)

ITEM NO: N/A
CAT. NO: YA-L-NT- (TABLE)
DRAWN BY: AUGUSTIN.S 07/03/10
CHECKER: --
DSN APPVL: J MICHAUD 06/11/11
MFG APPVL: T THRELFALL 06/23/11
QA APPVL: T WATTS 06/13/11
MKT APPVL: J SYLVIA 06/13/11
PROD FAM: CM&R COMPRESSION
DRAWING NO
PROJECT #: --
SIZE
DOCUMENT TYPE: Sales
REL LEVEL: Released

SCALE: 1:1
30003952
SHEET 2 OF 12
AC

DRAWING NO. 30003952				7		6		5		4		3		2		1									
CATALOG NUMBER	FIG. NO.	CONDUCTOR		STUD HOLE SIZE	DIMENSIONS									INSTALLATION TOOLING										WIRE STRIP LENGTH	
		AWG	MM ²		O.D.	B	C	D MIN.	E	K DIA.	L	N	T	DIELESS (# OF CRIMPS)	MECHANICAL MD6, OUR840, MD7-34R	HYDRAULIC							COLOR CODE		DIE INDEX
																BCT500HS, Y500CTHS	Y35, Y39, Y750, PAT750	Y46 PAT46	Y45	Y48	Y60				
YA2CL2NT14	2	#2 AWG	35	1/4"	.42 [11]	.88 [22]	.48 [12]	1.26 [32]	.63 [16]	.27 [7]	2.47 [63]	.31 [8]	.11 [3]	Y122CMR (2) MRC840(1) MY29-3(1) MY29-11(1) Y644HS(1) Y1MRTC(2) Y81KFT(1) Y81KFTMBH(1) PAT81KFT-18V(1) PAT644 (1) PAT444 (1)	W2CVT(1)	W2CVT(1)	U2CRT(1)	U2CRT(1)	U2CRT(1)	--	--	BROWN	10	15/16"	
YA2CL2NT14E2	2			1/4"	.42 [11]	.88 [22]	.48 [12]	1.39 [35]	.75 [19]	.27 [7]	2.60 [66]	.31 [8]	.11 [3]												
YA2CL2NT14E1	2			1/4"	.42 [11]	.88 [22]	.48 [12]	1.64 [42]	1.00 [25]	.27 [7]	2.84 [72]	.31 [8]	.11 [3]												
YA1CL2NT14	2	#1 AWG	50	1/4"	.46 [12]	.88 [22]	.50 [13]	1.26 [32]	.63 [16]	.27 [7]	2.55 [65]	.31 [8]	.11 [3]	MRC840(1) MY29-3(1) MY29-11(1) Y1MRTC(2) Y644HS(1) Y81KFT(1) PAT444 (1) PAT81KFT-18V(1)	W1CVT(1)	X1CRT-1(1)	U1CRT-1 (1)	U1CRT-1 (1)	U1CRT-1 (1)	--	--	GREEN	11	15/16"	
YA1CL2NT14E2	2			1/4"	.46 [12]	.88 [22]	.50 [13]	1.39 [35]	.75 [19]	.27 [7]	2.68 [68]	.31 [8]	.10 [3]												
YA25L2NT14	2	1/0 AWG	--	1/4"	.51 [13]	.88 [22]	.48 [12]	1.30 [33]	.63 [16]	.27 [7]	2.56 [65]	.31 [8]	.10 [3]	MRC840(2) MY29-3(1) MY29-11(1) Y644HS(1) Y81KFT(1) PAT444 (1) PAT81KFT-18V(1)	W25VT(2)	W25VT(2)	U25RT(1)	U25RT(1)	U25RT(1)	--	--	PINK	12	15/16"	
YA25L2NT14E1	2			1/4"	.51 [13]	.88 [22]	.48 [12]	1.94 [49]	1.00 [25]	.27 [7]	3.28 [83]	.25 [6]	.12 [3]												
YA26L2NT14	2	2/0 AWG	70	1/4"	.56 [14]	.94 [24]	.48 [12]	1.22 [31]	.63 [16]	.27 [7]	2.66 [68]	.25 [6]	.12 [3]	MRC840(2) MY29-3(1) MY29-11(1) Y644HS(1) Y81KFT(1) PAT444 (1) PAT81KFT-18V(1)	W26VT(1)	W26VT(2) X26RT(2)	U26RT(1)	U26RT(1)	U26RT(1)	--	--	BLACK	13	1"	
YA26L2NT14E1	2		--	1/4"	.56 [14]	.94 [24]	.48 [12]	1.60 [41]	1.00 [25]	.27 [7]	3.03 [77]	.25 [6]	.12 [3]												

TOLERANCE BLOCK

CONNECTOR SIZE	TOLERANCES						
	B	C	E	K DIA.	L	N	O.D.
-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01
-26 THRU -34	±.08	±.04	±.02	±.02	±.12	±.03	±.01
-35 AND UP	±.09	±.06	±.02	±.02	±.15	±.06	±.01

K DIA.
(2 PLACES)

CRIMP OVER COLOR
CODED AREA

FIG.2

NOTES:

1. MATERIAL: COPPER TUBING.

2. FINISH: TIN PLATED.

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED,AND ARE FOR REFERENCE ONLY.

4. INSTALLATION TOOLING AND DIES ARE CONSTANTLY BEING UPDATED. FOR THE LATEST INSTALLATION TOOLING INFORMATION REFER TO THE MASTER CATALOG ON THE BURNDY WEBSITE.

TO ORDER BURNDY@PRODUCTS CALL

UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

HYLUG™ COPPER (NARROW TONGUE)

ITEM NO: N/A

CAT. NO: YA-L-NT-(TABLE)

DRAWN BY: AUGUSTIN.S 07/03/10

CHECKER: -- --

DSN APPVL: J MICHAUD 06/11/11

MFG APPVL: T THRELFALL 06/23/11

QA APPVL: T WATTS 06/13/11

MKT APPVL: J SYLVIA 06/13/11

PROD FAM: CM&R COMPRESSION

PROJECT #: --

DOCUMENT TYPE: Sales

REL LEVEL: Released

DRAWING NO

30003952

SHEET 3 OF 12

REV

AC

DATE

2023-06-28 00:00:00 EDT

DESCRIPTION

UPDATED AS PER MARKUP

ECO

230627031433

BY

YR

C'H'K.

RA

DRAWING NO. 30003952				7				6		5				4		3		2		1					
CATALOG NUMBER	FIG. NO.	CONDUCTOR		STUD HOLE SIZE	DIMENSIONS									DIELESS (# OF CRIMPS)	INSTALLATION TOOLING										WIRE STRIP LENGTH
		AWG	MM ²		O.D.	B	C	D MIN.	E	K DIA.	L	N	T		MECHANICAL MD6, OUR840, MD7-34R	HYDRAULIC							COLOR CODE	DIE INDEX	
																BCT500HS, Y500CTHS	Y35, Y39, Y750, PAT750	Y46 PAT46	Y45	Y48	Y60				
YA27L2NT14	2	3/0 AWG	--	1/4"	.62 [16]	1.00 [25]	.76 [19]	1.30 [33]	.63 [16]	.27 [7]	2.73 [69]	.31 [8]	.13 [3]	MY29-3(1) MY29-11(1) MRC840(2) Y644HS(1) Y81KFT(1) Y81KFTMBH(1) PAT81KFT-18V(1) PAT644 (1) PAT444 (1)	W27VT(2) W27RT(2) X27RT(3)	W27VT(2) W27RT(2) X27RT(3)	U27RT(1)	U27RT(1)	U27RT(1)	--	--	ORANGE	14	1-1/16"	
YA27L2NT38	2			3/8"	.62 [16]	1.00 [25]	.60 [15]	1.74 [44]	1.00 [25]	.41 [10]	3.30 [84]	.41 [10]	.13 [3]												
YA27L2NT516	2			5/16"	.62 [16]	1.00 [25]	.60 [15]	1.73 [44]	1.00 [25]	.33 [8]	3.26 [83]	.31 [8]	.13 [3]												
YA28L2NT14	2	4/0 AWG	--	1/4"	.69 [18]	.88 [22]	.76 [19]	1.30 [33]	.63 [16]	.27 [7]	2.65 [67]	.31 [8]	.13 [3]	MY29-3(1) MY29-11(1) Y644HS(1) Y81KFT(1) PAT444 (1) PAT81KFT-18V(1)	W27RT(2)	W28RT(2) X28RT(3)	U28RT(1)	U28RT(1)	U28RT(1)	C28R(1)	L28RT(1)	PURPLE	15	1-1/16"	
YA29L2NT38	2	250 kcmil	--	3/8"	.75 [19]	1.00 [25]	.80 [20]	1.83 [47]	1.00 [25]	.41 [10]	3.43 [87]	.41 [10]	.16 [4]												
YA29L2NT38E16	2			3/8"	.75 [19]	1.06 [27]	.80 [20]	1.83 [47]	1.75 [44]	.41 [10]	4.18 [106]	.41 [10]	.16 [4]												
YA31L2NT38	2	350 kcmil	185	3/8"	.88 [22]	1.06 [27]	.96 [24]	1.82 [46]	1.00 [25]	.41 [10]	3.51 [89]	.41 [10]	.18 [4]	Y644HS(1) Y81KFT(1) Y81KFTMBH(1) PAT81KFT-18V(1) PAT644 (1) PAT444 (1)	W31VT(2)	W31VT(2) W31RT(2)	U31RT(2) U29ART(2)	U31RT(2) U29ART(2)	U31RT(2) U29ART(2)	C31R(2) C29AR(2)	L31RT(1) L29ART(1)	RED	18	1-1/8"	
YA31L2NT38E16	2			3/8"	.88 [22]	1.06 [27]	.88 [22]	2.59 [66]	1.75 [44]	.41 [10]	4.36 [111]	.41 [10]	.18 [4]												
YA31L2NNT	2			1/2"	.88 [22]	1.06 [27]	.88 [22]	3.00 [76]	1.75 [44]	.53 [13]	4.77 [121]	.63 [16]	.18 [4]												
YA34L2NT38	2	500 kcmil	240	3/8"	1.06 [27]	1.27 [32]	.96 [24]	1.82 [46]	1.00 [25]	.41 [10]	3.65 [93]	.41 [10]	.23 [6]	Y644HS(1) Y81KFT(1) Y81KFTMBH(1) PAT81KFT-18V(1) PAT644 (1) PAT444 (1)	W34VT(4)	W34VT(4)	U34RT(2)	U34RT(2)	U34RT(2)	C34R(1)	L34RT(1)	BROWN	20 OR 22	1-7/16"	
YA34L2NT38E16	2			3/8"	1.06 [27]	1.27 [32]	.96 [24]	2.58 [66]	1.75 [44]	.41 [10]	4.63 [117]	.41 [10]	.23 [6]												
YA34L2NT12E1	2			1/2"	1.06 [27]	1.27 [32]	.96 [24]	2.08 [53]	1.00 [25]	.53 [13]	4.13 [105]	.53 [13]	.23 [6]												
YA36L2NNT	2	600 kcmil	300	1/2"	1.19 [30]	1.38 [35]	1.12 [28]	3.00 [76]	1.75 [44]	.53 [13]	5.43 [138]	.63 [16]	.27 [16]	----	----	U36RT(2)	U36RT(2)	U36RT(2)	C36R(1)	L36RT(1)	GREEN	472	1-3/4"		
YA39L2NT38	2	750 kcmil	--	3/8"	1.30 [33]	1.42 [36]	1.63 [41]	2.06 [52]	1.00 [25]	.41 [10]	4.34 [110]	.50 [13]	.27 [16]												
YA39L2NT38E16	2			3/8"	1.30 [33]	1.42 [36]	1.30 [33]	2.78 [71]	1.75 [44]	.41 [10]	5.11 [130]	.50 [13]	.27 [16]												
YA39L2NT12E1	2			1/2"	1.30 [33]	1.42 [36]	1.30 [33]	2.08 [53]	1.00 [25]	.53 [13]	4.42 [112]	.53 [13]	.27 [16]												

TOLERANCE BLOCK

CONNECTOR SIZE	TOLERANCES						
	B	C	E	K DIA.	L	N	O.D.
-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01
-26 THRU -34	±.08	±.04	±.02	±.02	±.12	±.03	±.01
-35 AND UP	±.09	±.06	±.02	±.02	±.15	±.06	±.01

K DIA.
(2 PLACES)

CRIMP OVER COLOR
CODED AREA

FIG.2

NOTES:

1. MATERIAL: COPPER TUBING.

2. FINISH: TIN PLATED.

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED,AND ARE FOR REFERENCE ONLY.

4. INSTALLATION TOOLING AND DIES ARE CONSTANTLY BEING UPDATED. FOR THE LATEST INSTALLATION TOOLING INFORMATION REFER TO THE MASTER CATALOG ON THE BURNDY WEBSITE.

TO ORDER BURNDY@PRODUCTS CALL

UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

HYLUG™ COPPER (NARROW TONGUE)

ITEM NO: N/A
CAT. NO: YA-L-NT-(TABLE)
DRAWN BY: AUGUSTIN.S 07/03/10
CHECKER: -- --
DSN APPVL: J MICHAUD 06/11/11
MFG APPVL: T THRELFALL 06/23/11
QA APPVL: T WATTS 06/13/11
MKT APPVL: J SYLVIA 06/13/11

SCALE: 3:1

PROD FAM: CM&R COMPRESSION

DRAWING NO

REV

PROJECT #: --

SIZE

30003952

DOCUMENT TYPE: Sales

D

SHEET 4 OF 12

AC

8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---

DRAWING NO. 30003952		7			6			5			4			3			2			1				
CATALOG NUMBER	FIG. NO.	CONDUCTOR		STUD HOLE SIZE	DIMENSIONS							INSTALLATION TOOLING											WIRE STRIP LENGTH	
		AWG	MM ²		O.D.	B	C	D MIN.	K DIA.	L	N	T	DIELESS (# OF CRIMPS)	MECHANICAL MD6, OUR840, MD7-34R	HYDRAULIC							COLOR CODE		DIE INDEX
															BCT500HS, Y500CTHS	Y35, Y39, Y750, PAT750	Y46 PAT46	Y45	Y48	Y60				
YAV4CLNT10FX	3	4 AWG CLASS B,C FLEX CLASS G,H,I,K,M DLO 105/24	---	#10	.38 [10]	.50 [13]	.41 [10]	.52 [13]	.21 [5]	1.32 [34]	.25 [6]	.09 [2]	MY29-11(1) YIMRTC(2) Y81KFT(1) Y122CMR (2) PAT81KFT-18V(1)	W4CRT(1) X4CRT(1) W4CVT(1)	W4CRT(1) W4CVT(1) X4CRT(1)	U4CRT(1)	U4CRT(1)	U4CRT(1)	--	--	GRAY	8	1/2"	
YAV2CLNT14FX	3	2 AWG CLASS B,C FLEX CLASS G,H,I,K,M DLO 150/24	35	1/4"	.46 [12]	.63 [16]	.46 [12]	.64 [16]	.27 [7]	1.71 [43]	.31 [8]	.10 [3]	YIMRTC(2) MY29-11(1) Y81KFT(1) Y644(1) Y444(1)	W2CVT(1) W2CRT(1) X2CRT(1)	W2CVT(1) W2CRT(1) X2CRT(1)	U2CRT(1)	U2CRT(1)	U2CRT(1)	--	--	BROWN	10	11/16"	
YAV2CLNT516FX	3			5/16"	.46 [12]	.63 [16]	.44 [11]	.70 [18]	.33 [8]	1.78 [45]	.34 [9]	.10 [3]												
YAV25LNT14FX	3	1/0 AWG CLASS B,C FLEX CLASS G,H,I,K,M DLO 275/24	50	1/4"	.56 [14]	.69 [18]	.67 [17]	.64 [16]	.27 [7]	1.75 [44]	.31 [8]	.12 [3]		W25VT(2) W25RT(2) X25RT(2)	W25VT(2) W25RT(2) X25RT(2)	U25RT(1)	U25RT(1)	U25RT(1)	--	--	PINK	12	11/16"	
YAV25LNT516FX	3			5/16"	.56 [14]	.69 [18]	.67 [17]	.70 [18]	.33 [8]	1.81 [46]	.34 [9]	.12 [3]												
YAV25LNT38FX	3			3/8"	.56 [14]	.69 [18]	.76 [21]	.83 [21]	.41 [10]	1.94 [49]	.41 [10]	.13 [3]												
YAV26LNT516FX	3	2/0 AWG CLASS B,C FLEX CLASS G,H,I,K,M DLO 325/24	70	5/16"	.63 [16]	.81 [21]	.87 [22]	.70 [18]	.33 [8]	1.98 [50]	.34 [9]	.13 [3]	MY29-11(1) Y81KFT(1) PAT81KFT(1) Y644(1) PAY644(1) Y444(1) PAT444(1)	W26VT(2) W26RT(2) X26RT(2)	W26VT(2) W26RT(2) X26RT(2)	U26RT(1)	U26RT(1)	U26RT(1)	--	--	BLACK	13	13/16"	
YAV26LNT38FX	3			3/8"	.63 [16]	.81 [21]	.87 [22]	.83 [21]	.41 [10]	2.11 [54]	.41 [10]	.13 [3]												
YAV26LNT12FX	3			1/2"	.63 [16]	.81 [21]	.87 [22]	1.08 [27]	.53 [13]	2.36 [60]	.53 [13]	.13 [3]												
YAV28LNT516FX	3	4/0 AWG CLASS B,C FLEX CLASS G,H,I,K,M DLO 550/24	---	5/16"	.77 [20]	1.03 [26]	.94 [24]	.70 [18]	.33 [8]	2.29 [58]	.34 [9]	.15 [4]		W28VT(2) W28RT(2) X28RT(3)	W28VT(2) W28RT(2) X28RT(3)	U28RT(1)	U28RT(1)	U28RT(1)	C28R(1)	L28RT(1)	PURPLE	15	1-1/16"	
YAV28LNT38FX	3			3/8"	.77 [20]	1.03 [26]	.76 [19]	.83 [21]	.41 [10]	2.42 [61]	.41 [10]	.15 [4]												
YAV28LENT38FX	3			1/2"	.77 [20]	1.03 [26]	.76 [19]	1.08 [27]	.53 [13]	2.67 [68]	.53 [13]	.15 [4]												
YAV28LNT12FX	3							.62 [16]	.27 [7]	2.23 [56]	.31 [8]													
YAV28LNT14FX	3			1/4"																				
YA30LNT516FX	3	250 FLEX CLASS G: 259 STR CLASS H: 427 STR 4/0 FLEX CLASS I, 532 STR CLASS K, 2107 STR CLASS M, 5320 STR DLD, 550/24	---	5/16"	.81 [21]	1.03 [26]	.96 [24]	.72 [18]	.33 [8]	2.49 [63]	.34 [9]	.16 [4]	Y81KFT(1) PAT81KFT(1) Y644(1) PAY644(1) Y444(1) PAT444(1)	W29VT(2)	W29VT(1)	U29RT(1)	U29RT(1)	U29RT(1)	--	--	YELLOW	16	1-1/8"	
YA30LNT38FX	3			3/8"				1.20 [30]	.41 [10]	2.97 [75]	.41 [10]													
YA31LNT12FX	3	250 FLEX DLO 650/24 CLASS I,K,M	150	1/2"	.88 [22]	1.06 [27]	.96 [24]	1.20 [30]	.53 [13]	2.75 [70]	.53 [13]	.18 [4]		W30VT(2)	W30VT(2) W30RT(2)	U30RT(2)	U30RT(2)	U30RT(2)	C30R(1)	L30RT(1)	WHITE	17	1-1/8"	

TOLERANCE BLOCK							
CONNECTOR SIZE	TOLERANCES						
	B	C	E	K DIA.	L	N	O.D.
-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01
-26 THRU -34	±.08	±.04	±.02	±.02	±.12	±.03	±.01
-35 AND UP	±.09	±.06	±.02	±.02	±.15	±.06	±.01

NOTES:

1. MATERIAL: COPPER TUBING.
2. FINISH: TIN PLATED.
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
4. INSTALLATION TOOLING AND DIES ARE CONSTANTLY BEING UPDATED. FOR THE LATEST INSTALLATION TOOLING INFORMATION REFER TO THE MASTER CATALOG ON THE BURNDY WEBSITE.

5>YA30LNT-FX IS NOT UL/CSA LISTED USING ANY CLASS OF 4/0 FLEX COPPER CONDUCTOR.





FIG. 3

REV	DATE	DESCRIPTION	ECO	BY	C'K'K.
AC	2023-06-28 00:00:00 EDT	UPDATED AS PER MARKUP	230627031433	YR	RA

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	HYLUG™ COPPER (NARROW TONGUE)			
	ITEM NO:		N/A	
	CAT. NO: YA-L-NT-(TABLE)			
	DRAWN BY: AUGUSTIN.S		07/03/10	
	CHECKER: --		--	
	DSM APPVL: J MICHAUD		06/11/11	
	MFG APPVL: T THRELFALL		06/23/11	
	QA APPVL: T WATTS		06/13/11	
	MKT APPVL: J SYLVIA		06/13/11	
	PROJ FAM: CM&R COMPRESSION		DRAWING NO	
PROJECT #: --		SIZE		AC
DOCUMENT TYPE: Sales		30003952		
REL LEVEL: Released		SHEET 5 OF 12		

DRAWING NO. 30003952				7		6		5		4		3		2		1								
CATALOG NUMBER	FIG. NO.	CONDUCTOR		STUD HOLE SIZE	DIMENSIONS								INSTALLATION TOOLING										WIRE STRIP LENGTH	
		AWG	MM ²		O.D.	B	C	D MIN.	K DIA.	L	N	T	DIELESS (# OF CRIMPS)	MECHANICAL MD6, OUR840, MD7-34R	HYDRAULIC							COLOR CODE		DIE INDEX
															BCT500HS, Y500CTHS	Y35, Y39, Y750, PAT750	Y46 PAT46	Y45	Y48	Y60				
YA32LNT516FX	3	313.1 kcmil 775/24 300 FLEX	185	5/16"	.95 [24]	1.19 [30]	.96 [24]	.70 [18]	.33 [8]	2.65 [65]	.34 [9]	.19 [5]	Y644HS(1) Y81KFT(1) Y81KFTMBH(1) PAT81KFT-18V(1) PAT644 (1) PAT444 (1)	W31VT(2)	W31VT(2) W31RT(2)	U31RT(2)	U31RT(2)	U31RT(2)	C31R(1)	L31RT(1)	RED	18	1-1/4"	
YA32LNT38FX	3			3/8"	.95 [24]	1.19 [30]	.96 [24]	.83 [21]	.41 [10]	2.68 [68]	.41 [10]	.19 [5]												
YA32LNT12FX	3			1/2"	.95 [24]	1.19 [30]	.96 [24]	1.05 [27]	.52 [13]	2.93 [74]	.53 [13]	.19 [5]												
YA34LNT38FX	3	373.7 kcmil 925/24 350 FLEX	240	3/8"	1.06 [27]	1.27 [32]	.96 [24]	.85 [22]	.41 [10]	2.87 [73]	.41 [10]	.23 [6]	Y644HS(1) Y81KFT(1) Y81KFTMBH(1) PAT81KFT-18V(1) PAT644 (1) PAT444 (1)	W32VT(2)	W32VT(2) W32RT(2)	U32RT(2)	U32RT(2)	U32RT(2)	C32R(2)	L32RT(1)	BLUE	19	1-5/16"	
YA34LNT12FX	3			1/2"	1.06 [27]	1.27 [32]	.96 [24]	1.10 [28]	.53 [13]	3.12 [79]	.53 [13]	.23 [6]												
YA38LNT12FX	3	535.3 kcmil 1325/24 500 FLEX	300	1/2"	1.25 [32]	1.45 [37]	1.63 [41]	1.08 [27]	.53 [13]	3.41 [87]	.53 [13]	.27 [7]	Y644HS(1) Y81KFT(1) Y81KFTMBH(1) PAT81KFT-18V(1) PAT644 (1) PAT444 (1)	---	---	U38XRT(2)	U38XRT(2)	U38XRT(2)	--	L38RT(1)	PINK	L99	1-7/16"	
YA38LNTM20FX	3			M20	1.25 [32]	1.45 [37]	1.63 [41]	1.51 [38]	.85 [22]	3.84 [98]	.75 [19]	.27 [7]												
YA44LNT38FX	3	777.7 kcmil 1925/24 750 FLEX	500	3/8"	1.50 [38]	1.65 [42]	1.50 [38]	1.20 [30]	.41 [10]	3.79 [96]	.53 [13]	.33 [8]	Y644HS(1) Y81KFT(2) Y81KFTMBH(2) PAT81KFT-18V(2) PAT644 (1) PAT444 (1)	---	---	U44ZRT(2)	U44ZRT(2)	U44ZRT(2)	C44R(1)	L44RT(1)	YELLOW	L115	1-5/8"	
YA44LNT12FX	3			1/2"	1.50 [38]	1.65 [42]	1.62 [41]	1.26 [32]	.56 [14]	3.98 [101]	.62 [16]	.33 [8]												
YA44LNT58FX	3			5/8"	1.50 [38]	1.65 [42]	1.50 [38]	1.30 [33]	.69 [18]	4.04 [103]	.66 [17]	.33 [8]												

TOLERANCE BLOCK

CONNECTOR SIZE	TOLERANCES						
	B	C	E	K DIA.	L	N	O.D.
-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01
-26 THRU -34	±.08	±.04	±.02	±.02	±.12	±.03	±.01
-35 AND UP	±.09	±.06	±.02	±.02	±.15	±.06	±.01

K DIA.

CRIMP OVER COLOR
CODED AREAS

FIG. 3

NOTES:
1. MATERIAL: COPPER TUBING.
2. FINISH: TIN PLATED.
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
4. INSTALLATION TOOLING AND DIES ARE CONSTANTLY BEING UPDATED. FOR THE LATEST INSTALLATION TOOLING INFORMATION REFER TO THE MASTER CATALOG ON THE BURNDY WEBSITE.

REV	DATE	DESCRIPTION	ECO	BY	CHECK
AC	2023-06-28 00:00:00 EDT	UPDATED AS PER MARKUP	230627031433	YR	RA

TO ORDER BURNDY@PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

HYLUG™ COPPER (NARROW TONGUE)	
ITEM NO:	N/A
CAT. NO:	YA-L-NT-(TABLE)
DRAWN BY:	AUGUSTIN.S 07/03/10
CHECKER:	--
DSN APPVL:	J MICHAUD 06/11/11
MFG APPVL:	T THRELFALL 06/23/11
QA APPVL:	T WATTS 06/13/11
MKT APPVL:	J SYLVIA 06/13/11
PROD FAM:	CM&R COMPRESSION
PROJECT #:	--
DOCUMENT TYPE:	Sales
REL LEVEL:	Released

DRAWING NO	30003952
REV	AC
SHEET 6 OF 12	

8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---


DRAWING NO. 30003952				7		6		5		4		3		2		1								
CATALOG NUMBER	FIG. NO.	CONDUCTOR		STUD HOLE SIZE	DIMENSIONS								INSTALLATION TOOLING										WIRE STRIP LENGTH	
		AWG	MM ²		O.D.	B	C	D MIN.	E	K DIA.	L	N	T	DIELESS (# OF CRIMPS)	MECHANICAL MD6, OUR840, MD7-34R	HYDRAULIC						COLOR CODE		DIE INDEX
																BCT500HS, Y500CTHS	Y35, Y39, Y750, PAT750	Y46 PAT46	Y45	Y48	Y60			
YAV29L2NT38FX	4	4/0 AWG 4/0 WELD 550/24	---	3/8"	.80 [20]	1.03 [26]	.94 [24]	1.84 [47]	1.00 [25]	.41 [10]	3.43 [87]	.41 [10]	.16 [4]	Y644 (1) PAT644 (1) PAT444 (1) Y81KFT (1) PAT81KFT (1)	W29VT(2) X29RT(4)	W29VT(2) W29RT(2) X29RT(4)	U29RT(1)	U29RT(1)	U29RT(1)	C29R(1)	L29RT(1)	YELLOW	16	1-1/16"
YA31L2NT38FX	4	250 FLEX 637/24 CLASS I,K,M	150	3/8"	.88 [22]	1.06 [27]	.96 [24]	1.84 [47]	1.00 [25]	.41 [10]	3.51 [89]	.41 [10]	.18 [4]		W30VT(2)	W30VT(2) W30RT(2)	U30RT(2)	U30RT(2)	U30RT(2)	C30R(2)	L30RT(1)	WHITE	17	1-1/8"
YA32L2NT38FX	4	313.1 kcmil 775/24 300 FLEX	185	3/8"	.95 [24]	1.19 [30]	.96 [24]	1.84 [47]	1.00 [25]	.41 [10]	3.69 [94]	.41 [10]	.20 [5]		W31VT(2)	W31VT(2) W31RT(2)	U31RT(2)	U31RT(2)	U31RT(2)	C31R(2)	L31RT(1)	RED	18	1-1/4"
YA34L2NT38FX	4	373.7 kcmil 925/24 350 FLEX	240	3/8"	1.06 [27]	1.27 [32]	.96 [24]	2.58 [66]	1.00 [25]	.41 [10]	3.88 [99]	.41 [10]	.23 [6]		W32VT(2)	W32VT(2) W32RT(2)	U32RT(2)	U32RT(2)	U32RT(2)	C32R(2)	L32RT(1)	BLUE	19	1-5/16"
YA36L2ENT38E10FX	4	444.4 kcmil 1100/24 450 FLEX	---	3/8"	1.19 [30]	1.38 [35]	1.50 [38]	2.30 [58]	1.25 [32]	.41 [10]	4.49 [114]	.50 [13]	.27 [7]		----	----	U34RT(2)	U34RT(2)	U34RT(2)	C34R(1)	L34RT(1)	BROWN	20	1-7/16"
YA36L2NT38FX	4			3/8"	1.19 [30]	1.38 [35]	1.63 [41]	2.03 [51]	1.00 [25]	.41 [10]	4.24 [108]	.50 [13]	.27 [7]				U38XRT(2)	U38XRT(2)	U38XRT(2)	--	L38RT(1)	PINK	L99	1-7/16"
YA38L2ENT38FX	4	535.3 kcmil 1325/24 500 FLEX	300	3/8"	1.25 [32]	1.45 [37]	1.50 [38]	2.03 [51]	1.00 [25]	.41 [10]	4.35 [110]	.50 [13]	.27 [7]		----	----	U39RT(2)	U39RT(2)	U39RT(2)	C39R(1)	L39RT(1)	BLACK	24	1-5/16"
YA38L2NT38FX	4			3/8"	1.25 [32]	1.45 [37]	1.63 [41]	2.03 [51]	1.00 [25]	.41 [10]	4.35 [110]	.50 [13]	.27 [7]											
YA38L2NNTFX	4			1/2"	1.25 [32]	1.45 [37]	1.63 [41]	3.03 [77]	1.75 [44]	.56 [14]	5.35 [136]	.63 [16]	.27 [7]											
YA40L2NNTFX	4	646 kcmil 1600/24 650 FLEX	400	1/2"	1.35 [34]	1.42 [36]	1.63 [41]	3.03 [77]	1.75 [44]	.56 [14]	5.38 [137]	.63 [16]	.30 [8]	Y644 (1) PAT644 (1) PAT444 (1) Y81KFT (2) PAT81KFT (2)	----	----	U39RT(2)	U39RT(2)	U39RT(2)	C39R(1)	L39RT(1)	BLACK	24	1-5/16"
YA44L2NNTFX	4	777.7 kcmil 1925/24 750 FLEX	500	1/2"	1.50 [38]	1.65 [42]	1.63 [41]	3.03 [77]	1.75 [44]	.56 [14]	5.74 [146]	.63 [16]	.33 [8]		----	----	U44XRT(2)	U44XRT(2)	U44XRT(2)	C44R(1)	L44RT(1)	YELLOW	L115	1-5/8"
YA44L2NT38FX	4			3/8"	1.50 [38]	1.65 [42]	1.63 [41]	2.03 [51]	1.00 [25]	.41 [10]	4.74 [120]	.50 [13]	.33 [8]											
YA45L2NT38FX	4	929 kcmil 2300/24	---	3/8"	1.69 [43]	2.00 [51]	1.70 [43]	2.02 [51]	1.00 [25]	.41 [10]	5.18 [132]	.50 [13]	.38 [10]	----	----	----	P44RT(2)	S44RT(2)	C44R(1)	L44RT(1)	WHITE	27	2-1/16"	

TOLERANCE BLOCK							
CONNECTOR SIZE	TOLERANCES						
	B	C	E	K DIA.	L	N	O.D.
-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01
-26 THRU -34	±.08	±.04	±.02	±.02	±.12	±.03	±.01
-35 AND UP	±.09	±.06	±.02	±.02	±.15	±.06	±.01

NOTES:

1. MATERIAL: COPPER TUBING.
2. FINISH: TIN PLATED.
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
4. INSTALLATION TOOLING AND DIES ARE CONSTANTLY BEING UPDATED. FOR THE LATEST INSTALLATION TOOLING INFORMATION REFER TO THE MASTER CATALOG ON THE BURNDY WEBSITE.

5> ADD SUFFIX "NK" FOR NICKEL PLATING AND "SV" FOR SILVER PLATING.



REV	DATE	DESCRIPTION	ECO	BY	C'HECK
AC	2023-06-28 00:00:00 EDT	UPDATED AS PER MARKUP	230627031433	YR	RA



TO ORDER BURNDY@PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

HYLUG™ COPPER (NARROW TONGUE)				
ITEM NO:	N/A			
CAT. NO:	YA-L-NT-(TABLE)			
DRAWN BY:	AUGUSTIN.S	07/03/10	 	
CHECKER:	--	--		
DSN APPVL:	J MICHAUD	06/11/11		
MFG APPVL:	T THRELFALL	06/23/11		
QA APPVL:	T WATTS	06/13/11		
MKT APPVL:	J SYLVIA	06/13/11	SCALE: 3:1	
PROD FAM:	CM&R COMPRESSION	DRAWING NO	REV	
PROJECT #:	--	SIZE	30003952	AC
DOCUMENT TYPE:	Sales	D	SHEET 7 OF 12	
REL LEVEL:	Released			

AC

DRAWING NO.				7		6		5		4		3		2		1								
30003952																								
CATALOG NUMBER	FIG. NO.	CONDUCTOR		STUD HOLE SIZE	DIMENSIONS								INSTALLATION TOOLING										WIRE STRIP LENGTH	
		AWG	MM ²		O.D.	B	C	D MIN.	E	K DIA.	L	N	T	DIELESS (# OF CRIMPS)	MECHANICAL MD6, OUR840, MD7-34R	HYDRAULIC						COLOR CODE		DIE INDEX
																Y35, Y39, Y750 PAT750	Y46 PAT46	Y45	Y48	Y60				
YAV4CL2NT10E1FX	4	#4 AWG #4 WELD 91/24 105/24	---	#10	.38 [10]	.50 [13]	.41 [10]	1.52 [37]	1.00 [25]	.21 [5]	2.33 [59]	.25 [6]	.09 [2]	Y122CMR (2) MY29-11(1) Y1MRTC(2) Y81KFT(1) Y81KFTMBH(1) PAT81KFT-18V(1)	W4CVT(1) W4CRT(1) X4CRT(1)	W4CVT(1) W4CRT(1) X4CRT(1)	U4CRT(1)	U4CRT(1)	U4CRT(1)	--	--	GRAY	8	9/16"
YAV4CL2NT10E2FX	4				.38 [10]	.50 [13]	.41 [10]	1.52 [37]	.75 [19]	.21 [5]	2.08 [53]	.25 [6]	.09 [2]											
YAV4CL2NT10FX	4				.38 [10]	.50 [13]	.41 [10]	1.15 [29]	.63 [16]	.21 [5]	1.95 [50]	.25 [6]	.09 [2]											
YAV4CL2NT14FX	4			1/4"	.38 [10]	.50 [13]	.45 [11]	1.26 [32]	.63 [16]	.27 [7]	2.08 [53]	.31 [8]	.09 [2]											
YAV2CL2NT10FX	4	#2 AWG #2 WELD 125/24 150/24	35	#10	.46 [12]	.63 [16]	.48 [12]	1.15 [29]	.63 [16]	.21 [5]	2.14 [54]	.25 [6]	.10 [3]	Y122CMR (2) MY29-11(1) Y1MRTC(2) Y81KFT(1) PAT644 (1) PAT81KFT-18V(1) PAT444 (1)	W2CVT(1) W2CRT(1) X2CRT(1)	W2CVT(1) W2CRT(1) X2CRT(1)	U2CRT(1)	U2CRT(1)	U2CRT(1)	--	--	BROWN	10	11/16"
YAV2CL2NT14E1FX	4			1/4"	.46 [12]	.63 [16]	.48 [12]	1.65 [42]	1.00 [25]	.27 [7]	2.63 [67]	.31 [8]	.10 [3]											
YAV2CL2NT14FX	4				.46 [12]	.63 [16]	.48 [12]	1.28 [33]	.63 [16]	.27 [7]	2.26 [57]	.31 [8]	.10 [3]											
YAV1CL2NT14FX	4	#1 AWG #1 WELD 175/24 225/24	---	1/4"	.51 [13]	.62 [16]	.50 [13]	1.28 [33]	.63 [16]	.27 [7]	2.28 [58]	.31 [8]	.12 [3]	W1CVT(1) W1CRT-1(1) X1CRT-1(1)	W1CVT(1) W1CRT-1(1) X1CRT-1(1)	U1CRT-1(1)	U1CRT-1(1)	U1CRT-1(1)	--	--	GREEN	11	11/16"	
YAV1CL2NT516FX	4			5/16"	.51 [13]	.63 [16]	.58 [15]	1.70 [43]	1.00 [25]	.33 [8]	2.72 [69]	.34 [9]	.12 [3]											
YAV25L2NT14E1FX	4	1/0 AWG 1/0 WELD 275/24	50	1/4"	.56 [14]	.69 [18]	.64 [16]	1.65 [42]	1.00 [25]	.27 [7]	2.76 [70]	.31 [8]	.12 [3]	MY2911 (1) Y81KFT (1) PAT81KFT (1) Y644 (1) PAT644 (1) PAT444 (1)	W25VT(2) W25RT(2) X25RT(2)	W25VT(2) W25RT(2) X25RT(2)	U25RT(1)	U25RT(1)	U25RT(1)	--	--	PINK	12	11/16"
YAV25L2NT14FX	4			1/4"	.56 [14]	.69 [18]	.64 [16]	1.28 [33]	.63 [16]	.27 [7]	2.39 [61]	.31 [8]	.12 [3]											
YAV25L2NT516FX	4			5/16"	.56 [14]	.69 [18]	.58 [15]	1.71 [44]	1.00 [25]	.33 [8]	2.82 [72]	.34 [9]	.12 [3]											
YAV26L2NT14FX	4	2/0 AWG 2/0 WELD 325/24	70	1/4"	.63 [16]	.81 [21]	.76 [19]	1.28 [33]	.63 [16]	.27 [7]	2.56 [65]	.31 [8]	.13 [3]	W26VT(2) W26RT(2) X26RT(2)	W26VT(2) W26RT(2) X26RT(2)	U26RT(1)	U26RT(1)	U26RT(1)	--	--	BLACK	13	13/16"	
YAV26L2NT516FX	4			5/16"	.63 [16]	.81 [21]	.58 [15]	1.71 [44]	1.00 [25]	.33 [8]	2.99 [76]	.34 [9]	.13 [3]											
YAV26L2NT38FX	4			3/8"	.63 [16]	.81 [21]	.63 [16]	1.84 [47]	1.00 [25]	.41 [10]	3.23 [82]	.41 [10]	.13 [9]											
YAV28L2ENT14FX	4	4/0 AWG 4/0 WELD 550/24	---	1/4"	.77 [20]	1.03 [19]	.76 [19]	1.28 [33]	.63 [16]	.27 [7]	2.86 [73]	.31 [8]	.15 [4]	W28VT(2) W28RT(2) X28RT(3)	W28VT(2) W28RT(2) X28RT(3)	U28RT(1)	U28RT(1)	U28RT(1)	C28R(1)	L28RT(1)	PURPLE	15	1-1/16"	
YAV28L2NT38FX	4			3/8"	.77 [20]	1.03 [19]	.94 [24]	1.84 [47]	1.00 [25]	.40 [10]	3.43 [87]	.41 [10]	.15 [4]											

TOLERANCE BLOCK							
CONNECTOR SIZE	TOLERANCES						
	B	C	E	K DIA.	L	N	O.D.
-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01
-26 THRU -34	±.08	±.04	±.02	±.02	±.12	±.03	±.01
-35 AND UP	±.09	±.06	±.02	±.02	±.15	±.06	±.01



NOTES:

1. MATERIAL: COPPER TUBING.
2. FINISH: TIN PLATED.
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
4. INSTALLATION TOOLING AND DIES ARE CONSTANTLY BEING UPDATED. FOR THE LATEST INSTALLATION TOOLING INFORMATION REFER TO THE MASTER CATALOG ON THE BURNDY WEBSITE.

REV	DATE	DESCRIPTION	ECO	BY	C'H'K'
AC	2023-06-28 00:00:00 EDT	UPDATED AS PER MARKUP	230627031433	YR	RA

TO ORDER BURNDY@PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	HYLUG™ COPPER (NARROW TONGUE)				
	ITEM NO:		N/A		
	CAT. NO: YA-L-NT-(TABLE)				
	DRAWN BY: AUGUSTIN.S		07/03/10		
	CHECKER: --		--		
	DSN APPLV: J MICHAUD		06/11/11		
	MFG APPLV: T TRITHEFALL		06/23/11		
	QA APPLV: T WAITS		06/13/11		
	MKT APPLV: J SYLVIA		06/13/11		
	 				
[SCALE: 3:1]					
PROD FAM: C&R COMPRESSION		DRAWING NO		REV	
PROJECT #:		SIZE	30003952	AC	
DOCUMENT TYPE: Sales		D			
REL LEVEL: Released		SHEET 8 OF 12			

DRAWING NO. 30003952				7				6				5				4				3				2				1	
CATALOG NUMBER	FIG. NO.	CONDUCTOR		STUD HOLE SIZE	DIMENSIONS									DIELESS (# OF CRIMPS)	MECHANICAL		INSTALLATION TOOLING								WIRE STRIP LENGTH				
		AWG	MM²		O.D.	B	C	D MIN.	E	K DIA.	L	N	T		MD6, OUR840, MD7-34R	BCT500HS, Y500CTHS	HYDRAULIC									COLOR CODE	DIE INDEX		
																	Y35, Y39, Y750, PAT750	Y46 PAT46	Y45	Y48	Y60								
YAZ382NNTFX	5	535.3 kcmil 1325/24 500 FLEX	300	1/2"	1.25 [32]	2.81 [71]	1.62 [41]	3.02 [77]	1.75 [44]	.56 [14]	6.72 [171]	.62 [16]	.27 [7]	Y644 (1) PAT644 (1) PAT444 (1) Y81KFT (1) PAT81KFT (1)	----	----	U38XRT(4)	U38XRT(4)	U38XRT(4)	--	L38RT(2)	PINK	L99	2-7/8"					
YAZ382NT38FX	5	535.3 kcmil 1325/24 500 FLEX	300	3/8"	1.25 [32]	2.81 [71]	1.62 [41]	2.03 [51]	1.00 [25]	.41 [10]	5.72 [145]	.50 [13]	.27 [7]	Y644 (1) PAT644 (1) PAT444 (1) Y81KFT (1) PAT81KFT (1)	----	----	U38XRT(4)	U38XRT(4)	U38XRT(4)	--	L38RT(2)	PINK	L99	2-7/8"					
YAZ442NT38FX	5	777.7 kcmil 1925/24 750 FLEX	500	3/8"	1.50 [38]	3.00 [76]	1.62 [41]	2.03 [51]	1.00 [25]	.40 [10]	6.09 [155]	.50 [13]	.33 [8]	PAT644 (1) PAT444 (1) Y81KFT (2) PAT81KFT (2)	----	----	U44XRT(4)	U44XRT(4)	U44XRT(4)	C44RT(2)	L44RT(2)	YELLOW	L115	3-1/16"					

TOLERANCE BLOCK

CONNECTOR SIZE	TOLERANCES						
	B	C	E	K DIA.	L	N	O.D.
-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01
-26 THRU -34	±.08	±.04	±.02	±.02	±.12	±.03	±.01
-35 AND UP	±.09	±.06	±.02	±.02	±.15	±.06	±.01

DRAWING NO. 30003952		7			6			5			4			3			2			1				
CATALOG NUMBER	FIG. NO.	CONDUCTOR		STUD HOLE SIZE	DIMENSIONS									DIELESS (# OF CRIMPS)	MECHANICAL	INSTALLATION TOOLING								WIRE STRIP LENGTH
		AWG	MM ²		O.D.	B	C	D MIN.	H REF.	K DIA.	L	N	T			HYDRAULIC								
															MD6, OUR840, MD7-34R	BCT500HS, Y500CTHS	Y35, Y39, Y750, PAT750	Y46 PAT46	Y45	Y48	Y60	COLOR CODE	DIE INDEX	
YA32LNT3890	I	400 kcmil	--	3/8" [M10]	.95 [24]	1.19 [30]	.96 [24]	.85 [26]	2.19 [56]	.41 [10]	1.45 [37]	.41 [10]	.19 [5]	Y644HS (1) Y81KFT(2) PAT444 (1) PAT81KFT-18V (2)	W32VT(4)	----	U32RT(2)	U32RT(2)	U32RT(2)	C32R(1)	L32RT(1)	BLUE	19 OR 470	1-1/4"

TOLERANCE BLOCK

CONNECTOR SIZE	TOLERANCES						
	B	C	E	K DIA.	L	N	O.D.
-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01
-26 THRU -34	±.08	±.04	±.02	±.02	±.12	±.03	±.01
-35 AND UP	±.09	±.06	±.02	±.02	±.15	±.06	±.01

K DIA.

TYPICAL
LETTERING

C

N

L

O.D.

B

H

D

(T)

(90°)

NOTES:

1. MATERIAL: COPPER TUBING.

2. FINISH: TIN PLATED.

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

4. INSTALLATION TOOLING AND DIES ARE CONSTANTLY BEING UPDATED. FOR THE LATEST INSTALLATION TOOLING INFORMATION REFER TO THE MASTER CATALOG ON THE BURNDY WEBSITE.

TO ORDER BURNDY@PRODUCTS CALL

UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

HYLUG™ COPPER (NARROW TONGUE)

ITEM NO: N/A

CAT. NO: YA-L-NT- (TABLE)

DRAWN BY: AUGUSTIN.S 07/03/10

CHECKER: --

DSN APPVL: J MICHAUD 06/11/11

MFG APPVL: T THRELFALL 06/23/11

QA APPVL: T WATTS 06/13/11

MKT APPVL: J SYLVIA 06/13/11

PROD FAM: CM&R COMPRESSION

PROJECT #: --

DOCUMENT TYPE: Sales

REL LEVEL: Released

HUBBELL

BURNDY

SCALE: 2:1

DRAWING NO

30003952

SHEET 12 OF 12

REV

AC

REV	DATE	DESCRIPTION	ECO	BY	CHECK
AC	2023-06-28 00:00:00 EDT	UPDATED AS PER MARKUP	230627031433	YR	RA