



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	05/04/2017 11:15:00 AM	LOGO UPDATION	46659	BK	MB

CATALOG NUMBER	CONDUCTOR RANGE		WIRE STRIP LENGTH	DIE INDEX
	BARREL 'A'	BARREL 'B'		
YRB31U2	350 kcmil	#1 STR #2 STR	1/8"	21AB 299

INSTALLATION TOOLING (# OF CRIMPS OR INDENTS PER END)								
COLOR CODE	DIE INFORMATION		HYDRAULIC				DIELESS (# OF CRIMPS)	
	DIE INDEX	TYPE	Y35, Y39 Y750, BAT35 BAT750	Y46	Y45	Y488		Y60BHU
----	21AB	---	---	---	---	---	---	---
		NEST INDENTOR	---	P350(1) P48PR-1	---	C350(1) Y48PRI	---	---
BROWN	299	BROWN DIE SET	U31ART(2)	U31ART(2)	U31ART(2)	U31AR(1)	L31ART(1)	HYDRAULIC Y644M(1) BAT644M(1)
		NEST	---	P350(1)	---	C350(1)	---	
		INDENTOR	---	P48PR-1	---	Y48PRI	---	



- NOTES:
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
 - MATERIAL: ALUMINUM.
 - FINISH: TIN PLATED.
 - NOT FOR USE WITH COPPER TO COPPER APPLICATIONS.
 - BARRELS ARE PARTIALLY FILLED WITH PENETROX™ AND SEALED.
 - SCRATCH BRUSHING OF ALL CONDUCTORS BEFORE MAKING INSTALLATION IS RECOMMENDED.

TO ORDER BURNDY® PRODUCTS CALL		HYREDUCER™	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 10102096	CAT. NO: YRB31U2
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		DRAWN BY: I. ANBALAGAN 08-19-09	CHECKER: --
FOR PRODUCT INFO: http://www.burndy.com		DSN APPVL: --	MFG APPVL: --
		QA APPVL: J.BRODEUR	MKT APPVL: --
		PROJ #:	SCALE: 3:1
		DOCUMENT TYPE: Sales	DRAWING NO: 10105522
		REL LEVEL: Released	REV: B

REV: PE0200