



CATALOG NUMBER	I.D EXPANDED	I.D AFTER RECOVERY	WALL THICKNESS	CONDUCTOR RANGE		STANDARD REEL SIZE [FEET]
				CODE	FLEX	
HSC18FR	.125 (3)	.062 (2)	0.025 (6)	#16 - #14	#16 - #14	50
HSC316FR	0.1875 (5)	.094 (2)	0.025 (6)	#18-#12	#18-#12	50
HSC14FR	.250 (6)	.125 (3)	0.025 (6)	#12 - #8	#12 - #10	50
HSC38FR	.375 (10)	.187 (5)	0.025 (6)	#6 - #4	#8 - #6	50
HSC12FR	.500 (13)	.250 (6)	0.025 (6)	#4 - #1	#6 - #4	50
HSC34FR	.750 (19)	.375 (10)	0.030 (0.8)	1/0 - 3/0	#2 - 1/0	50
HSC100FR	1.00 (25)	.500 (13)	.035 (0.9)	4/0 - 3/0	1/0 - 4/0	25
HSC112FR	1.50 (38)	.750 (19)	0.040 (1)	350 - 750	250 - 500	25
HSC200FR	2.00 (51)	1.00 (25)	0.045 (1)	800 - 1000	500 - 750	25

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	06/01/2012	CREATE SALES DRAWING	27652	TS	MA



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- SHRINK TEMPERATURE IS 135°C (275°F)
- FOR BEST RESULTS MOVE HEAT GUN ALONG THE LENGTH OF HEAT SHRINK TO AVOID CONCENTRATIONS.
- FOR EXTEND END USEFUL LIFE, STORE MATERIAL BELOW 70°F.
- OPERATING TEMPERATURE RANGE FROM - 20° TO 105°.

TO ORDER BURNDY® PRODUCTS CALL		HEAT SHRINK TUBING	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: --	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: HS--(SEE TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: T.SATHISH 6/1/2012	
		CHECKER: J.MICHAUD 7/11/2012	
		DSN APRVL: J.MICHAUD 7/11/2012	
		MFG APRVL: 7/10/2012	
		QA APRVL: C.KOWALCZYK 7/10/2012	
		MKT APRVL: R.CAVANAUGH 7/10/2012	
PROJ #:	SIZE	DRAWING NO	REV
50003077	B	50003077	A
DOCUMENT TYPE: SALES		SHEET 1 OF 1	
REL LEVEL: Released			