


CONDUCTOR		BOLT SIZE	DIE INFORMATION			INSTALLATION TOOLING (# CRIMPS)										WIRE STRIP LENGTH	
CODE (AWG)	NAVY		COLOR CODE	DIE INDEX	TYPE	MECHANICAL				HYDRAULIC				DIELESS (# CRIMPS)			
						Y1MRTC	OUR 840	MD6 MD7	MD6--R2 MD7-34R	PATMD6 PAT600 Y500CT	Y34A Y34B Y34BH	Y35, Y39 Y750, PAT750	Y46 PAT46	Y45	MECHANICAL		HYDRAULIC
#4	40	3/8 [M10]	GRAY	8 346	GRAY DIE SET	GRAY (4)	X4CRT (2)	W4CRT(2) W4CVT(2)	W4CRT(2) W4CVT(2)	W4CRT(2) W4CVT(2)	--	U4CRT(2) U6CABT(2)	U4CRT(2) U6CABT(2)	U4CRT(2) U6CABT(2)	MY29-3(2) MY29-11(2) MRC840(2)	PAT81KFT(1) Y81KFT(1) PAT4PC834(1) Y4PC834(1) PAT644(1) Y644 (1)	1-3/16"
					NEST	--	--	--	--	--	B4CD(1) A4CD(1)	U4CD-1(1)	U4CD-1(1)	U4CD-1(1)			
					INDENTOR	--	--	--	--	--	Y34PR	Y34PR	Y34PR	Y34PR			

REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	07/25/2012	SALES DRAWING RELEASE	28210	DK	MA



NOTES:

- MATERIAL: COPPER TUBING.
- FINISH: ELECTRO-TIN PLATED.
- CATALOG # PT6515 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y45 SERIES TOOLS.
- CATALOG # PUADP-1 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y46 SERIES TOOLS.
- Y35P3 INDENTOR ADAPTOR REQUIRED FOR Y34PR INDENTOR.
- PERMANENT DIE IN TOOLING.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- FOR USE BY CUSTOMERS THAT HAVE THIS HYPRESS™. NO NEW Y34A HYPRESS™ TOOLS ARE BEING PROCESSED. Y34A USED A--D NEST DIES ONLY.
- "UL" LISTED AND "CSA" CERTIFIED WIRE CONNECTOR.

TO ORDER BURNDY® PRODUCTS CALL		HYLUG™	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50240K	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: YA4CG27	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: N.D.KANNAN 7/24/2012	
		CHECKER: R.ROMAN 8/3/2012	
		DSN APRVL: R.ROMAN 8/3/2012	
		MFG APRVL: --	
		QA APRVL: T.WATTS	
		MKT APRVL: J.SLYVIA 8/2/2012	
		PROD FAM: CM&R Compression	
		DRAWING NO	
		50007038	
		REV	
		A	
		SHEET 1 OF 1	