


ITEM NUMBER	5 CATALOG NO.	Length (L)
50007528	BD6T14	6.00 [152]
50007529	BD9T14	9.00 [229]
50050620	BD10T14	10.00 [254]
50050621	BD12T14	12.00 [305]
50050622	BD14T14	14.00 [356]
50086391	BD18T14	18.00[457]
50086392	BD24T14	24.00[609]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
F	06/15/2021	AMP RATING UPDATED IN NOTE 1	210615009191	PB	RG



NOTES:

1. APPROXIMATE AMP RATING: 190A(INDOOR), 225A(OUTDOOR). THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 ALL SIZE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

4 ALL SIZE LISTED TO CSA 22.2 NO. 41 GROUNDING & BONDING EQUIPMENT STANDARDS.

5 CAN BE ORDERED WITH PLATED FERRULES BY ADDING A SUFFIX AS SHOWN BELOW:

- "NK" - FOR NICKEL PLATING
- "SV" - FOR SILVER PLATING
- "TN" - FOR TIN PLATING
- "W" - FOR HOT TIN DIPPED.

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-387-6487

FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO: SEE TABLE	
CAT. NO: BD--T14 (TABLE)	
DRAWN BY: SENTHIL	08/24/2012
CHECKER: E.MARTIN	08/17/2012
DSN APRVL: E.MARTIN	08/17/2012
MFG APRVL: M.STEVENS	09/11/2017
QA APRVL: C.LINDQUIST	09/15/2017
MKT APRVL: K.ROBICHEAU	09/15/2017
PROD FAM: MECHANICAL GROUNDING	DRAWING NO
PROJECT #: EPI4466	SIZE
DOCUMENT TYPE: SALES	50007530
REL LEVEL: Released	B
	SHEET 1 OF 1
	REV F

