


REV.	DATE	DESCRIPTION	BY	C.K.D.
0	12/22/94	SHEET ADDED PER (SPN 2097)	JWA	JLM

EP. 15HPFC SERIES 1 1/2 HORSEPOWER (FIGURE 3, SHEET 3)

CATALOG NUMBER	DESCRIPTION	OPERATING OUTPUT PRESSURE (POUNDS/SQUARE INCH)
EP1015HPFC	ELECTRIC HYDRAULIC PUMP WITH STEEL ROLL CAGE. REMOTE FOOT PEDAL CONTROL SWITCH AND 1 1/2 HP 115 VOLT, 60HZ MOTOR	10,000 PSI
EP815HPFC	ELECTRIC HYDRAULIC PUMP WITH STEEL ROLL CAGE. REMOTE FOOT PEDAL CONTROL SWITCH AND 1 1/2 HP 115 VOLT, 60HZ MOTOR	8,800 PSI
EP615HPFC	ELECTRIC HYDRAULIC PUMP WITH STEEL ROLL CAGE. REMOTE FOOT PEDAL CONTROL SWITCH AND 1 1/2 HP 115 VOLT, 60HZ MOTOR	6,000 PSI

EP SERIES ELECTRIC HYDRAULIC PUMPS

CAT NO.	EP---HPFC	SCALE	N/A
DRAWN	J AYER	12/23/94	CHECKED, J MICHAUD 12/27/94
DSGN APPVL.	J LEFAVOUR	11/8/94	HRG APPVL. N/A
O.A. APPVL.	D VARIO	12/22/94	HRG APPVL. M BLAKE 12/27/94
CAD FILE	N/A	PH. REF.	N/A
 U.S. ELECTRICAL DIVISION MANCHESTER, NH 03108		PROJECT	
		DRAWING NO.	SE207894
		SHEET	5 OF 5
		REV	0