



NOTES:

1. DIMENSIONS SUBJECT TO +/- 3% TOLERANCE
2. LEAKAGE DISTANCE (Inches) - 25.5
3. ALTITUDE 0-12000 FT. ABOVE SEA LEVEL
4. WEIGHT OF UNIT INCLUDING HARDWARE - 2 LB.
5. MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE 15.3 kV MCOV
6. VOLTAGE RATING 18 kV RMS.



.5 μ SEC IR kV	5kA SURGE IR kV	MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT				
		15 kA	30 kA	5 kA	10 kA	20 kA
59.7	42.2	47.2	50.3	53.6	60.3	69.7

IEEE DISTRIBUTION NORMAL DUTY ARRESTER	CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	 HUBBELL® POWER SYSTEMS		
		TITLE PDV-65 ARRESTER 15.3 kV MCOV		
REV DATE 07/26/18	SIZE S	DWG NO. ALES7XXX	CAT / PART / ASSY NO. 213265-7202	REV 31
DO NOT SCALE THIS DRAWING		DRN BY PRO	DATE 06/17/00	SHEET 1 OF 1