



NOTES:

1. DIMENSIONS SUBJECT TO +/- 3% TOLERANCE
2. LEAKAGE DISTANCE (Inches) - 25.2
3. ALTITUDE 0-12000 FT. ABOVE SEA LEVEL
4. WEIGHT OF UNIT INCLUDING HARDWARE - 6 LB.
5. MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE 12.7 kV MCOV
6. VOLTAGE RATING 15 kV RMS.



MAXIMUM DISCHARGE VOLTAGE (kV)						
FDW	SWITCHING SURGE	8/20 LIGHTNING IMPULSE				
		1.5 kA	3.0 kA	5 kA	10 kA	20 kA
10 kA	500 A	53.8	41.4	43.8	47.8	54.3
53.8	35.4	38.7	41.4	43.8	47.8	54.3

DISTRIBUTION ARRESTER IEEE HEAVY DUTY IEC DH CLASS	 HUBBELL® POWER SYSTEMS	TITLE PDV-100 OPTIMA 12.7 KV MCOV			
		CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	SIZE S	DWG NO. ALES7XXX	CAT / PART / ASSY NO. 213713-7333
REV DATE 07/14/22	DO NOT SCALE THIS DRAWING		DRN BY NON	DATE 06/17/00	SHEET 1 OF 1