



CONDUCTOR			BOLT SIZE	BURNDY® INSTALLATION TOOLING (# CRIMPS)					
FLEX	CODE (AWG)	NAVY ⁵		COLOR CODE	DIE INDEX	HYDRAULIC		DIELESS (# CRIMPS)	WIRE STRIP LENGTH
						Y35, Y39 Y750, Y46 ⁴	Y45 ³		
777.7 kcmil 1925/24 (750 kcmil/FLEX)	---	---	1/2	YELLOW	L115	U44XRT (2)	U44XRT UR4141WE (2)	Y644HS(1) Y81KFT(2) Y81KFTMBH(2) PAT81KFT-18V(2)	1-5/8"

REV	DATE	DESCRIPTION	ECO	BY	C'HK.
A	03/17/2014	DRAWING RELEASED	35299	RK	MB



NOTES:

1. MATERIAL : COPPER.
2. FINISH: TIN PLATED.
3. CATALOG # PT6515 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y45 SERIES TOOLS.
4. CATALOG # PUADP-1 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y46 SERIES TOOLS.
5. NAVY CABLE SIZE MAY BE OMITTED ON SOME SIZES BECAUSE OF SPACE LIMITATIONS.
6. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		HYLUG™	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 10079859	CAT. NO: YA44L2NNTFXSL
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		DRAWN BY: rkonathala 03/17/2014	CHECKER: B.MANTIKANDAN 03/17/2014
FOR PRODUCT INFO: http://www.burndy.com		DSN APRVL: K.BOUTIN 04/02/2014	MFG APRVL: --
		QA APRVL: C.KOWALCZYK 04/02/2014	MKT APRVL: J.SYLVIA 04/01/2014
		PROJ #:	SIZE
		DOCUMENT TYPE: SALES	DRAWING NO: 50040328
		REL LEVEL: Released	REV: A
			SHEET 1 OF 1