


CONDUCTOR		BOLT SIZE	COLOR CODE	DIE INDEX	BURNDY® INSTALLATION TOOLING (# OF CRIMPS)				WIRE STRIP LENGTH
					MECHANICAL	HYDRAULIC		DIELESS (# CRIMPS)	
CODE (AWG)	MM²				MD6, OUR840, MD7-34R	BCT500HS, Y500CTHS	Y35, Y39 Y750, Y46 \triangleleft 3 PAT750		
#3 STR #2 SOL	25	5/16 [M8]	WHITE	9	W3CRT (1)	W3CRT (1)	U3CRT (1)	Y1MRTC (2) MY29-3 (1) MY29-11 (1) MRC840 (1) Y644HSXT (1) Y81KFT (1) Y81KFTMBH (1) PAT81KFT-18V (1)	15/16"

REV	DATE	DESCRIPTION	ECO	BY	C'HK.
A	05/08/2014	DRAWING RELEASED	36016	MVP	MB



NOTES:

1. MATERIAL : COPPER TUBING.
2. FINISH: TIN PLATED
3. CATALOG # PUADP-1 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y46 SERIES TOOLS.
4. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		HYLUG™	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 000815	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: YA3CLTC14	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: MANIMEKALA 05/08/2014	
		CHECKER: J MICHAUD 05/13/2014	
		DSN APRVL: J MICHAUD 05/14/2014	
		MFG APRVL: J PASSARELLI 05/15/2014	
		QA APRVL: C KOWALCZYK 05/13/2014	
		MKT APRVL: K BOUTIN 05/13/2014	
		PROJ #: --	
		DRAWING NO	
		50043192	
		REV	
		A	
		SHEET 1 OF 1	