



NOTES:

1. DIMENSIONS SUBJECT TO +/- 3% TOLERANCE
2. LEAKAGE DISTANCE (Inches) - 28.1
3. ALTITUDE 0-12000 FT. ABOVE SEA LEVEL
4. WEIGHT OF UNIT INCLUDING HARDWARE - 4.9 LB.
5. MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE 17.0 kV MCOV
6. VOLTAGE RATING 21 kV RMS.



.5 μ SEC IR	10kA kV	500 A SURGE	MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT				
			1.5 kA	3.0 kA	5 kA	10 kA	20 kA
70.4		47	51.4	55	58.2	63.5	72.1

IEEE DISTRIBUTION HEAVY DUTY IEC DISTRIBUTION DH	CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.			HUBBELL® POWER SYSTEMS			
		TITLE PDV-100 OPTIMA 17.0 KV MCOV					
REV DATE	07/16/18	SIZE	DWG NO.	CAT / PART / ASSY NO.	REV		
		S	ALES7XXX	213717-7214	32		
DO NOT SCALE THIS DRAWING		DRN BY NONE		DATE 06/17/00	SHEET 1 OF 1		